

FL IF MEM 2TX-D - Memory modul



2832483

<https://www.phoenixcontact.com/us/products/2832483>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Memory module, 2 port twisted pair module for saving the switch configuration



Commercial data

Item number	2832483
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	DNN123
GTIN	4017918974497
Weight per piece (including packing)	91.8 g
Weight per piece (excluding packing)	91.8 g
Customs tariff number	85176200
Country of origin	DE

FL IF MEM 2TX-D - Memory modul



2832483

<https://www.phoenixcontact.com/us/products/2832483>

Technical data

Product properties

Product type	Storage medium
Type	fine granularity

System properties

Functionality

Basic functions	Configuration memory (plug-in)
-----------------	--------------------------------

Electrical properties

Supply

Supply voltage	via head station
Power supply connection	from FL SWITCH MM HS or MXT
Typical current consumption	10 mA

Interfaces

Ethernet 10/100Base T

Connection method	RJ45 jack
Transmission speed	10/100 Mbps
Transmission physics	Copper
Transmission length	100 m
No. of channels	2

Dimensions

Width	31 mm
Height	78 mm
Depth	72.5 mm

Material specifications

Color	green
Housing material	PA

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	0 °C ... 55 °C (non-condensing)
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Permissible humidity (operation)	10 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	10 % ... 95 % (non-condensing)

EMC data

FL IF MEM 2TX-D - Memory modul



2832483

<https://www.phoenixcontact.com/us/products/2832483>

Electromagnetic compatibility	Conformance with EMC Directive 2004/108/EC
Conformance with EMC directives	IEC 61000-6-2 IEC 61000-4-2 (ESD) Criterion B
	IEC 61000-4-3 (immunity to radiated interference) Criterion A
	IEC 61000-4-4 (burst) Criterion A
	IEC 61000-4-5 (surge) Criterion A
	IEC 61000-4-6 (immunity to conducted interference) Criterion A
	IEC 61000-4-8 (immunity to magnetic fields) Criterion A
	EN 55022 (emitted interference) Criterion A
Noise immunity	EN 61000-6-2:2005
Noise emission	
Standards/regulations	EN 61000-6-3/-4

Mounting

Mounting type	In the host system
---------------	--------------------

FL IF MEM 2TX-D - Memory modul



2832483

<https://www.phoenixcontact.com/us/products/2832483>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-25
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com