

FL IF TX/HCS 100-D - Media module



2832739

<https://www.phoenixcontact.com/us/products/2832739>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Interface module, one port twisted pair, one port PCF, exit downward



Commercial data

Item number	2832739
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	DNN123
GTIN	4017918957001
Weight per piece (including packing)	91.6 g
Weight per piece (excluding packing)	91.6 g
Customs tariff number	84718000
Country of origin	DE

FL IF TX/HCS 100-D - Media module



2832739

<https://www.phoenixcontact.com/us/products/2832739>

Technical data

Product properties

Product type	Extension module
Type	fine granularity

System properties

Functionality

Basic functions	Media module for modular managed switch
-----------------	---

Electrical properties

Transmission medium	Copper
	FO

Supply

Supply voltage	via head station
Power supply connection	from FL SWITCH MM HS or MXT
Typical current consumption	60 mA

Brake to be connected

Connection method	Can be plugged onto FL SWITCH MM HS or FL MXT
-------------------	---

Connection data

Connection method	Can be plugged onto FL SWITCH MM HS or FL MXT
-------------------	---

Interfaces

Ethernet 100Base-T

Connection method	RJ45 jack
Transmission speed	100 Mbps
Transmission physics	Copper
Transmission length	100 m
No. of channels	1

Ethernet FO

Connection method	FSMA plugs
Transmission speed	100 Mbps
Transmission physics	FO
Transmission length	100 m (PCF fiber with F-S 200/230 10 dB/km)
Wavelength	650 nm
No. of channels	1


Dimensions

FL IF TX/HCS 100-D - Media module



2832739

<https://www.phoenixcontact.com/us/products/2832739>

Dimensional drawing	
Width	31 mm
Height	75.7 mm
Depth	72.5 mm

Material specifications

Color	green
Flammability rating according to UL 94	V0
Housing material	PA

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	0 °C ... 55 °C (non-condensing)
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Permissible humidity (operation)	10 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	10 % ... 95 % (non-condensing)

EMC data

Electromagnetic compatibility	Conformance with EMC directive 89/336/EC
Noise immunity	EN 61000-6-2:2005

Noise emission

Standards/regulations	EN 61000-6-3/-4
-----------------------	-----------------

Mounting

Mounting type	In the host system
---------------	--------------------

FL IF TX/HCS 100-D - Media module




2832739

<https://www.phoenixcontact.com/us/products/2832739>

Drawings

Dimensional drawing



The figure shows a version of the interface module with the head station FL SWITCH MM HS

FL IF TX/HCS 100-D - Media module



2832739

<https://www.phoenixcontact.com/us/products/2832739>

Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com