

# IB IL 24 DI 2-PAC/10 - Inline terminal



2897334

<https://www.phoenixcontact.com/us/products/2897334>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Inline, Digital input terminal, Digital inputs: 2, 24 V DC, connection technology: 4-conductor, transmission speed in the local bus: 500 kbps, degree of protection: IP20, including Inline connector and labeling field

## Product description

The terminal is designed for use within an Inline station. It is used to acquire digital signals.

## Commercial data

Item number	2897334
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	DR19
Product key	DRI131
GTIN	4046356138970
Weight per piece (including packing)	66.376 g
Weight per piece (excluding packing)	53 g
Customs tariff number	85389091
Country of origin	DE

# IB IL 24 DI 2-PAC/10 - Inline terminal



2897334

<https://www.phoenixcontact.com/us/products/2897334>

## Technical data

### Notes

#### Note on application

Note on application	Only for industrial use
---------------------	-------------------------

### Material specifications

Color (Housing)	green (RAL 6021)
-----------------	------------------

### Interfaces

#### Inline local bus

Connection method	Inline data jumper
Transmission speed	500 kbps

### Input data

#### Digital:

Input name	Digital inputs
Description of the input	IEC 61131-2 type 1
Number of inputs	2
Connection method	Spring-cage connection
Connection technology	4-conductor
Input voltage	24 V DC
Input voltage range "0" signal	-3 V DC ... 5 V DC
Input voltage range "1" signal	15 V DC ... 30 V DC
Nominal input voltage $U_{IN}$	24 V DC
Typical response time	< 1 ms
Protective circuit	Short-circuit and overload protection

### Product properties

Product type	I/O component
Product family	Inline
Type	modular
Scope of supply	including Inline connector and labeling field

### Connection data

#### Connection technology

Connection name	Inline connector
-----------------	------------------

#### Inline connector

Connection method	Spring-cage connection
Stripping length	8 mm

# IB IL 24 DI 2-PAC/10 - Inline terminal



2897334

<https://www.phoenixcontact.com/us/products/2897334>

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
----------------------	------

## Mounting

Mounting type	DIN rail mounting
---------------	-------------------

# IB IL 24 DI 2-PAC/10 - Inline terminal



2897334

<https://www.phoenixcontact.com/us/products/2897334>

## Classifications

### ECLASS

ECLASS-13.0	27242604
ECLASS-15.0	27242604

### ETIM

ETIM 10.0	EC001599
-----------	----------

### UNSPSC

UNSPSC 21.0	32151600
-------------	----------

# IB IL 24 DI 2-PAC/10 - Inline terminal



2897334

<https://www.phoenixcontact.com/us/products/2897334>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)