

PR1-RSP3-LDP-24DC/21 - Relay module



2834407

<https://www.phoenixcontact.com/us/products/2834407>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Pre-assembled relay modules with spring-cage connection, consisting of: relay base, power contact relay, plug-in display/interference suppression module, and retaining bracket. Input voltage: 24 V DC, 1 changeover contact, 10 A

Your advantages

- Safe isolation between coil and contact side
- Logical contact arrangement thanks to 1/3-level relay base
- Operational reliability thanks to sealed relay

Commercial data

Item number	2834407
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	C463
Product key	DK6329
GTIN	4046356044295
Weight per piece (including packing)	72.28 g
Weight per piece (excluding packing)	66.06 g
Customs tariff number	85364900
Country of origin	CN

PR1-RSP3-LDP-24DC/21 - Relay module



2834407

<https://www.phoenixcontact.com/us/products/2834407>

Set consists of

PR1-BSP3/2X21 - Relay base

2833534

<https://www.phoenixcontact.com/us/products/2833534>

PR1... relay base, for miniature power relays or miniature switching relays with 1 or 2 changeover contacts or solid-state relays with the same design, 1/3-level version, spring-cage connections, plug-in option for input/interference suppression modules



REL-MR- 24DC/21HC - Single relay

2961312

<https://www.phoenixcontact.com/us/products/2961312>

Plug-in miniature power relay, with power contact for high continuous currents, 1 changeover contact, input voltage 24 V DC



PR1-RSP3-LDP-24DC/21 - Relay module

2834407

<https://www.phoenixcontact.com/us/products/2834407>

LDP- 12- 24DC - Plug-in module

2833657

<https://www.phoenixcontact.com/us/products/2833657>



Plug-in module, with freewheeling diode and yellow LED, polarity: **A1+**, **A2-**,
input voltage: 12 ... 24 V DC ± 20 %

EL1-P16 - Retaining bracket

2833547

<https://www.phoenixcontact.com/us/products/2833547>



Relay retaining bracket, with eject function and integrated equipment marking
area (7.5 x 15 mm), to suit relay base PR1, for 16 mm high miniature power relay
and solid-state relay

Technical data

Product properties

Product type	Relay Module
Application	Universal
Operating mode	100% operating factor
Mechanical service life	3x 10 ⁷ cycles

Insulation characteristics

Overvoltage category	III
Pollution degree	3

Data management status

Date of last data management	01.04.2026
------------------------------	------------

Electrical properties

Service life electrical	see diagram
Maximum power dissipation for nominal condition	0.46 W
Test voltage (Winding/contact)	4 kV (50 Hz, 1 min., winding/contact)

Input data

Coil side

Nominal input voltage U_N	24 V DC
Input voltage range	15.6 V DC ... 57.6 V DC
Drive and function	monostable
Typical input current at U_N	19 mA
Typical response time	8 ms
Typical release time	10 ms
Protective circuit	Freewheeling diode
Operating voltage display	Yellow LED

Output data

Switching

Contact switching type	1 changeover contact
Type of switch contact	Single contact
Contact material	AgNi
Maximum switching voltage	250 V AC/DC
Minimum switching voltage	12 V (at 10 mA)
Limiting continuous current	10 A
Maximum inrush current	30 A (300 ms)
Min. switching current	10 mA (at 12 V)
Interrupting rating (ohmic load) max.	3000 W (for 250 V AC) 50 W (at 110 V DC)

PR1-RSP3-LDP-24DC/21 - Relay module



2834407

<https://www.phoenixcontact.com/us/products/2834407>

	80 W (at 220 V DC)
	288 W (at 24 V DC)
	at 440 V AC
	58 W (at 48 V DC)
	48 W (at 60 V DC)
Switching capacity	2 A (at 24 V, DC13)
	0.2 A (at 110 V, DC13)
	0.2 A (at 250 V, DC13)
	6 A (at 24 V, AC15)
	6 A (at 120 V, AC15)
	6 A (at 250 V, AC15)

Connection data

Coil side

Connection method	Spring-cage connection
Stripping length	10 mm
Conductor cross-section rigid	0.2 mm ² ... 1.5 mm ²
Conductor cross-section flexible	0.2 mm ² ... 1.5 mm ²
Conductor cross-section AWG	24 ... 16

Contact side

Connection method	Spring-cage connection
Stripping length	10 mm
Conductor cross-section rigid	0.2 mm ² ... 1.5 mm ²
Conductor cross-section flexible	0.2 mm ² ... 1.5 mm ²
Conductor cross-section AWG	24 ... 16

Dimensions

Width	16 mm
Height	97 mm
Depth	72 mm

Material specifications

Color	green (RAL 6021)
-------	------------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 60 °C
Ambient temperature (storage/transport)	-25 °C ... 85 °C

Standards and regulations

Standards/regulations	IEC 60664
	EN 50178

PR1-RSP3-LDP-24DC/21 - Relay module



2834407


<https://www.phoenixcontact.com/us/products/2834407>

Mounting

Mounting type	DIN rail mounting
Assembly note	in rows with zero spacing
Mounting position	any

Drawings

Diagram




- ① DC coils
- ② AC coils

Operating voltage range of the relay



Interrupting rating

Diagram



Service life reduction factor with various cos phi

Diagram



- 1 250 V AC, ohmic load (DC coils)
- 2 250 V AC, ohmic load (AC coils)


Electrical service life

PR1-RSP3-LDP-24DC/21 - Relay module

2834407

<https://www.phoenixcontact.com/us/products/2834407>

Circuit diagram



DC coils

PR1-RSP3-LDP-24DC/21 - Relay module



2834407

<https://www.phoenixcontact.com/us/products/2834407>

Classifications

UNSPSC

UNSPSC 21.0	39122334
-------------	----------

PR1-RSP3-LDP-24DC/21 - Relay module



2834407

<https://www.phoenixcontact.com/us/products/2834407>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com