

# VIP-CAB-FLK50/FR/OE/0,14/1,5M - Cable



2900148

<https://www.phoenixcontact.com/us/products/2900148>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Round cable set; connection 1: Single wires (50-position) (The wires are marked and fitted with ferrules); connection 2: IDC/FLK socket strip (1x 50-position, 90 °-out put); cable length: 1.5 m

## Your advantages

- 20 and 50-pos.
- Connector in accordance with IEC 60603-13
- 1:1 connection
- Open end at one end

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 2900148                        |
| Packing unit                         | 1 pc                           |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | C423                           |
| Product key                          | DK2223                         |
| GTIN                                 | 4046356477024                  |
| Weight per piece (including packing) | 282.5 g                        |
| Weight per piece (excluding packing) | 282.5 g                        |
| Customs tariff number                | 85444290                       |
| Country of origin                    | DE                             |

## Technical data

### Product properties

|              |              |
|--------------|--------------|
| Product type | System cable |
|--------------|--------------|

### Environmental and real-life conditions

#### Ambient conditions

|   |  |
|---|--|
| Degree of protection                                    | IP00                                     |
| Degree of protection (Installation location)            | ≥ IP54 (Installation location)           |
| Ambient temperature (operation) (fixed installation)    | -40 °C ... 70 °C (fixed installation)    |
| Ambient temperature (operation) (flexible installation) | -10 °C ... 70 °C (flexible installation) |
| Ambient temperature (storage/transport)                 | -40 °C ... 80 °C                         |
| Altitude  | ≤ 2000 m                                 |

### Electrical properties

|                          |                                  |
|--------------------------|----------------------------------|
| Operating voltage (AC)   | ≤ 30 V AC                        |
| Operating voltage (DC)   | ≤ 60 V DC                        |
| Nominal operating mode   | 100% operating factor            |
| Current (Per path, 50°C) | ≤ 1 A (Uncoiled, see derating)   |
| Current (Per path, 70°C) | ≤ 0.6 A (Uncoiled, see derating) |

### Cable/line

|              |       |
|--------------|-------|
| Cable length | 1.5 m |
|--------------|-------|

#### 50X0.14 [PVC]

|   |   |
|---|---|
| UL AWM Style                                  | 2464/1061   |
| Number of positions                           | 50  |
| Shielded                                      | no  |
| Cable type                                    | 50X0.14 [PVC]   |
| Conductor type                                | Round cable set   |
| Conductor structure signal line               | 7x 0.16 mm  |
| AWG signal line                               | 26  |
| Conductor cross-section                       | 50x 0.14 mm <sup>2</sup>  |
| Wire diameter incl. insulation                | 1 mm ±0.03 mm   |
| External cable diameter                       | 10.30 mm ±0.4 mm  |
| Outer sheath, material                        | Semi-rigid PVC  |
| External sheath, color                        | gray  |
| Conductor material                            | Tin-plated Cu litz wires  |
| Cable resistance                              | ≤ 145 Ω/km (20 °C)  |
| Insulation resistance                         | ≥ 20 MΩ*km (20 °C)  |
| Smallest bending radius, fixed installation   | 86 mm   |
| Smallest bending radius, movable installation | 161 mm  |
| Dynamic load capacity (bending)               | Max. bending cycles: 5000 (at a radius of ≥ 15x outside diameter) |

# VIP-CAB-FLK50/FR/OE/0,14/1,5M - Cable




2900148

<https://www.phoenixcontact.com/us/products/2900148>

|                   |   |
|-------------------|---|
| Halogen-free      | no  |
| Flame resistance  | IEC 60332-1-2 (raw cable)                     |
|                   | VDE 0842, Part 332-1-2 (raw cable)            |
|                   | IEC 60332-3-22 (raw cable)                    |
|                   | UL VW-1                                       |
|                   | CSA FT-1                                      |
| Resistance to oil | can withstand occasional splashes (raw cable) |
| Cable type        | Cable for one module                          |

## Connection data

### Connection 1

|                           |  |
|---------------------------|--|
| Connection method         | Single wires   |
| Stripping length (Sheath) | ≈  mm |
| Number of positions       | 50   |
| Note                      | The wires are marked and fitted with ferrules  |

### Connection 2

|                                  |                              |
|----------------------------------|------------------------------|
| Connection in acc. with standard | IEC 60603-13 (in compliance) |
| Connection method                | IDC/FLK socket strip         |
| Number of connections            | 1                            |
| Number of positions              | 50                           |
| Exit angle                       | 90 °                         |
| Pitch                            | 2.54 mm                      |

## Notes

|                    |  |
|--------------------|--|
| Notes on operation | For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met. |
|--------------------|--|

Drawings

Diagram



Maximum permissible current per path in uncoiled state

# VIP-CAB-FLK50/FR/OE/0,14/1,5M - Cable



2900148

<https://www.phoenixcontact.com/us/products/2900148>

## Classifications

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 26121600 |
|-------------|----------|

# VIP-CAB-FLK50/FR/OE/0,14/1,5M - Cable



2900148

<https://www.phoenixcontact.com/us/products/2900148>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)