

# ME B-17,5 MKDSO KMGY - Filler plug



2854115

<https://www.phoenixcontact.com/us/products/2854115>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail housing, Filler plug for unoccupied terminal points (MKDSO), width: 16 mm, height: 17.05 mm, depth: 8.55 mm, color: light gray (similar RAL 7035)

## Your advantages

- Easy, tool-free mounting
- Flammability rating V0 in accordance with UL 94

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2854115       |
| Packing unit                         | 10 pc         |
| Minimum order quantity               | 10 pc         |
| Sales key                            | AC08          |
| Product key                          | ACHAAZ        |
| GTIN                                 | 4017918458997 |
| Weight per piece (including packing) | 1.07 g        |
| Weight per piece (excluding packing) | 0.854 g       |
| Customs tariff number                | 39269097      |
| Country of origin                    | DE            |

# ME B-17,5 MKDSO KMGY - Filler plug



2854115

<https://www.phoenixcontact.com/us/products/2854115>

## Technical data

### Product properties

|                              |                  |
|------------------------------|------------------|
| Product type                 | Filler plug      |
| Housing type                 | DIN rail housing |
| Housing series               | ME               |
| Product family               | ME 17,5..        |
| Ventilation openings present | no               |

### Dimensions

|        |          |
|--------|----------|
| Width  | 16 mm    |
| Height | 17.05 mm |
| Depth  | 8.55 mm  |

### Material specifications

|  |                       |
|--|-----------------------|
| Color (Filler plug)                    | light gray (RAL 7035) |
| Material Filler plug                   | PA                    |
| Flammability rating according to UL 94 | V0                    |
| CTI according to IEC 60112             | 600                   |

### Environmental and real-life conditions

#### Vibration test

|                        |                             |
|------------------------|-----------------------------|
| Specification          | IEC 60068-2-6:2007-12       |
| Frequency              | 10 - 150 - 10 Hz            |
| Sweep speed            | 1 octave/min                |
| Amplitude              | 0.15 mm (10 Hz ... 58.1 Hz) |
| Acceleration           | 2g (58.1 Hz ... 150 Hz)     |
| Test duration per axis | 2.5 h                       |
| Test directions        | X-, Y- and Z-axis           |

#### Glow-wire test

|                  |                        |
|------------------|------------------------|
| Specification    | IEC 60695-2-11:2014-02 |
| Temperature      | 850 °C                 |
| Time of exposure | 30 s                   |

#### Thermal stability / ball thrust test

|               |                        |
|---------------|------------------------|
| Specification | IEC 60695-10-2:2014-02 |
| Temperature   | 125 °C                 |
| Test duration | 1 h                    |
| Force         | 20 N                   |

#### Mechanical strength / tumbling barrel

|                |                     |
|----------------|---------------------|
| Specification  | IEC 60998-1:2002-12 |
| Height of fall | 50 cm               |

# ME B-17,5 MKDSO KMGY - Filler plug



2854115

<https://www.phoenixcontact.com/us/products/2854115>

|           |    |
|-----------|----|
| Frequency | 10 |
|-----------|----|

## Shocks

|                                |                                   |
|--------------------------------|-----------------------------------|
| Specification                  | IEC 60068-2-27:2008-02            |
| Pulse shape                    | Half-sine                         |
| Acceleration                   | 15g                               |
| Shock duration                 | 11 ms                             |
| Number of shocks per direction | 3                                 |
| Test directions                | X-, Y- and Z-axis (pos. and neg.) |

## Degree of protection (IP code)

|               |   |
|---------------|---|
| Specification | IEC 60529:1989-11 + AMD 1:1999-11 + AMD 2:2013-08 |
|---------------|---|

## Ambient conditions

|   |  |
|---|--|
| Max. IP code to attain                  | IP20   |
| Ambient temperature (operation)         | -40 °C ... 105 °C (depending on power dissipation) |
| Ambient temperature (storage/transport) | -40 °C ... 55 °C                                   |
| Ambient temperature (assembly)          | -5 °C ... 100 °C                                   |
| Relative humidity (storage/transport)   | 80 %   |

## Mounting

|               |          |
|---------------|----------|
| Mounting type | Latching |
|---------------|----------|

# ME B-17,5 MKDSO KMGY - Filler plug



2854115

<https://www.phoenixcontact.com/us/products/2854115>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2854115>



**UL Recognized**

Approval ID: E240868

# ME B-17,5 MKDSO KMGY - Filler plug



2854115

<https://www.phoenixcontact.com/us/products/2854115>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27190605 |
| ECLASS-15.0 | 27190605 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002779 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

# ME B-17,5 MKDSO KMGY - Filler plug



2854115

<https://www.phoenixcontact.com/us/products/2854115>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)