

PT 1X2-24DC-ST - Surge protection plug



2856032

<https://www.phoenixcontact.com/us/products/2856032>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



PT protective connector with protective circuit for a 2-wire floating signal circuit. HART-compatible.

Your advantages

- Easy testing and documentation with CHECKMASTER 2 with pluggable protective modules
- Maximum ease of maintenance, thanks to the 2-piece design
- Easy selection for all possible demands in MCR applications with a complete product portfolio
- The signal is not influenced during maintenance work, thanks to the impedance-neutral insertion and removal of protective plugs

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2856032 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | CL21 |
| Product key | CL2111 |
| GTIN | 4017918599201 |
| Weight per piece (including packing) | 23.4 g |
| Weight per piece (excluding packing) | 20 g |
| Customs tariff number | 85363010 |
| Country of origin | DE |

PT 1X2-24DC-ST - Surge protection plug



2856032

<https://www.phoenixcontact.com/us/products/2856032>

Technical data

Notes

General

| | |
|------|--|
| Note | Technical data is valid in association with the following specified base elements: |
| | PT 1X2+F-BE 2856126 |
| | PT 1X2-BE 2856113 |

Product properties

| | |
|--|-------------------------------------|
| Product type | Surge protection for MCR technology |
| Product family | PLUGTRAB PT |
| IEC test classification | C1 |
| | C2 |
| | C3 |
| | D1 |
| Type | Male |
| Arrester can be tested with CHECKMASTER from software version: | From SW rev. 1.00 |
| Wire pairs per module | 1 |

Insulation characteristics

| | |
|----------------------|-----|
| Overvoltage category | III |
| Pollution degree | 2 |


Electrical properties

| | |
|-----------------------|---------|
| Nominal voltage U_N | 24 V DC |
|-----------------------|---------|

Connection data

| | |
|----------------------------------|--|
| Connection method | Screw connection (in connection with the base element) |
| Screw thread | M3 |
| Tightening torque | 0.5 Nm |
| Conductor cross-section flexible | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section rigid | 0.2 mm ² ... 4 mm ² |
| Conductor cross-section AWG | 24 ... 12 |

Dimensions

| | |
|---------------------|--|
| Dimensional drawing |  |
| Width | 17.7 mm |
| Height | 45 mm |

PT 1X2-24DC-ST - Surge protection plug



2856032

<https://www.phoenixcontact.com/us/products/2856032>

| | |
|------------------------|---------|
| Depth | 52 mm |
| Horizontal pitch | 1 Div. |
| Complete module width | 17.7 mm |
| Complete module height | 90 mm |
| Complete module depth | 65.5 mm |

Material specifications

| | |
|--|------------------|
| Color | black (RAL 9005) |
| | copper color |
| Flammability rating according to UL 94 | V-0 |
| Housing material | PA 6.6 |

Mechanical properties

Mechanical data

| | |
|-----------------|----|
| Open side panel | No |
|-----------------|----|

Protective circuit

| | |
|--|--|
| Direction of action | Line-Line & Line-Signal Ground/Shield & optional Signal Ground/Shield-Earth Ground |
| Nominal voltage U_N | 24 V DC |
| Maximum continuous operating voltage U_C | 28 V DC |
| | 20 V AC |
| Rated current | 450 mA (45 °C) |
| Operating effective current I_C at U_C | $\leq 5 \mu A$ |
| Protective conductor current I_{PE} | $\leq 1 \mu A$ (with PT 1X2+F-BE) |
| | $\leq 2 \mu A$ (with PT 1X2-BE) |
| Nominal discharge current I_n (8/20) μs (line-line) | 10 kA |
| Nominal discharge current I_n (8/20) μs (line-ground) | 10 kA |
| Pulse discharge current I_{imp} (10/350) μs | 2.5 kA |
| Total discharge current I_{Total} (8/20) μs | 20 kA |
| Max. discharge current I_{max} (8/20) μs maximum (line-line) | 10 kA |
| Max. discharge current I_{max} (8/20) μs maximum (line-earth) | 10 kA |
| Nominal pulse current I_{an} (10/1000) μs (line-line) | 30 A |
| Output voltage limitation at 1 kV/ μs (line-line) spike | $\leq 45 V$ |
| Output voltage limitation at 1 kV/ μs (line-earth) spike | $\leq 450 V$ (with PT 1X2-BE) |
| | $\leq 1 kV$ (with PT 1X2+F-BE) |
| Output voltage limitation at 1 kV/ μs (line-line) static | $\leq 40 V$ |
| Output voltage limitation at 1 kV/ μs (line-earth) static | $\leq 25 V$ (with PT 1X2-BE) |
| | $\leq 50 V$ (with PT 1X2+F-BE) |
| Residual voltage at I_n (conductor-conductor) | $\leq 40 V$ |
| Residual voltage with I_{an} (10/1000) μs (line-line) | $\leq 50 V$ |
| Voltage protection level U_p (line-line) | $\leq 70 V$ (C1 - 1 kV / 500 A) |
| | $\leq 70 V$ (C2 - 10 kV / 5 kA) |
| | $\leq 60 V$ (C2 - 6 kV / 3 kA) |

PT 1X2-24DC-ST - Surge protection plug



2856032

<https://www.phoenixcontact.com/us/products/2856032>

| | |
|--|---|
| | ≤ 50 V (C3 - 25 A) |
| Voltage protection level U_p (line-earth) | ≤ 450 V (C1 - 1 kV / 500 A with PT 1X2-BE) |
| | ≤ 550 V (C2 - 10 kV / 5 kA with PT 1X2-BE) |
| | ≤ 1000 V (C2 - 10 kV / 5 kA with PT 1X2+F-BE) |
| | ≤ 500 V (C2 - 6 kV / 3 kA with PT 1X2-BE) |
| Voltage protection level U_p static (line-line) | ≤ 40 V (C2 - 10 kV / 5 kA) |
| Voltage protection level U_p static (line-earth) | ≤ 50 V (C2 - 10 kV / 5 kA with PT 1X2-BE) |
| | ≤ 100 V (C2 - 10 kV / 5 kA with PT 1X2+F-BE) |
| Response time t_A (line-line) | ≤ 1 ns |
| Response time t_A (line-earth) | ≤ 100 ns |
| Input attenuation aE, sym. | typ. 0.5 dB (≤ 1 MHz / 50 Ω) |
| | typ. 0.2 dB (≤ 400 kHz / 150 Ω) |
| | typ. 0.1 dB (≤ 70 kHz/600 Ω) |
| Cut-off frequency f_g (3 dB), sym. in 50 Ω system | typ. 4.5 MHz |
| Cut-off frequency f_g (3 dB), sym. in 150 Ω system | typ. 1.5 MHz |
| Cut-off frequency f_g (3 dB), sym. in 600 Ω system | typ. 600 kHz |
| Capacity (Core-Core) | typ. 1.4 nF |
| Capacity (Core-Earth) | typ. 4 pF (with PT 1X2-BE) |
| | typ. 2 pF (with PT 1X2+F-BE) |
| Resistance per path | 2.2 Ω ±10 % |
| Surge protection fault message | none |
| Max. required back-up fuse | 500 mA (T) |
| Impulse durability (line-line) | C1 - 1 kV / 500 A |
| | C2 - 6 kV / 3 kA |
| | C2 - 10 kV / 5 kA |
| | C3 - 25 A |
| Impulse durability (line-earth) | C1 - 1 kV / 500 A |
| | C2 - 6 kV / 3 kA |
| | C2 - 10 kV / 5 kA |
| | D1 - 2.5 kA |

Environmental and real-life conditions

Ambient conditions

| | |
|---|------------------|
| Degree of protection | IP20 |
| Ambient temperature (operation) | -40 °C ... 85 °C |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C |
| Altitude | ≤ 2000 m (amsl) |

Standards and regulations

| | |
|--------------------------|---|
| Standards/specifications | IEC 61643-21 |
| Note | 2000 + corrigendum 2001 + A1:2008, modified + A2:2012 |
| Standards/specifications | EN 61643-21 |
| Note | 2001 + A1:2009 + A2:2013 |
| Standards/specifications | GB/T 3836.1 |

PT 1X2-24DC-ST - Surge protection plug



2856032

<https://www.phoenixcontact.com/us/products/2856032>

| | |
|--------------------------|-------------|
| Note | 2021 |
| Standards/specifications | GB/T 3836.3 |
| Note | 2021 |

Mounting

| | |
|---------------|-----------------|
| Mounting type | on base element |
|---------------|-----------------|

PT 1X2-24DC-ST - Surge protection plug

2856032

<https://www.phoenixcontact.com/us/products/2856032>


Drawings

Dimensional drawing



The figure shows the complete module consisting of a base element and connector

Diagram




PT 1X2-24DC-ST - Surge protection plug



2856032

<https://www.phoenixcontact.com/us/products/2856032>

Circuit diagram



PT 1X2-24DC-ST - Surge protection plug



2856032

<https://www.phoenixcontact.com/us/products/2856032>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2856032>



DNV GL

Approval ID: TAE00001N6



UL Listed

Approval ID: FILE E 138168

| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
|-------|-----------------------|-----------------------|-------------------|----------------------|
| keine | | | | |
| | 24 V | 0.45 A | - | - |



CCC

Approval ID: 2020322316003150



cUL Listed

Approval ID: FILE E 333250



UL Listed

Approval ID: FILE E 333250



ATEX

Approval ID: DEKRA 22ATEX0044 X



IECEx

Approval ID: IECEx DEK 22.0031X



UKCA-EX

Approval ID: DEKRA 22UKEX6005X



NEPSI-EX

Approval ID: GYJ20.1180X

PT 1X2-24DC-ST - Surge protection plug



2856032

<https://www.phoenixcontact.com/us/products/2856032>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27171501 |
| ECLASS-15.0 | 27171501 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001466 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121600 |
|-------------|----------|

PT 1X2-24DC-ST - Surge protection plug



2856032

<https://www.phoenixcontact.com/us/products/2856032>

Environmental product compliance

EU RoHS

| | |
|---|--------------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 7(a), 7(c)-I |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | 00872e2b-d282-471d-9794-6763708abd3e |

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.462 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com