


# IB IL 24 DI 8/T2 - Digital module

2860439

<https://www.phoenixcontact.com/us/products/2860439>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Inline, Digital input terminal, Digital inputs: 8, 24 V DC, connection technology: 4-conductor, degree of protection: IP20

## Product description

The terminal is designed for use within an Inline station. It is used to acquire digital signals.

## Your advantages

- Diagnostic and status indicators
- Maximum permissible load current from the terminal: 2 A
- Maximum permissible load current per sensor: 250 mA
- Connection of sensors in 2-, 3-, and 4-conductor technology
- 8 digital inputs as per type 2 limit values in accordance with EN 61131-2

## Commercial data

Item number	2860439
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	DRI131
GTIN	4017918861087
Weight per piece (including packing)	136.8 g
Weight per piece (excluding packing)	109.81 g
Customs tariff number	85389091
Country of origin	DE

# IB IL 24 DI 8/T2 - Digital module



2860439

<https://www.phoenixcontact.com/us/products/2860439>

## Technical data

### Product properties

Type	modular
No. of channels	8

### System properties

#### Module

ID code (dec.)	190
ID code (hex)	BE
Length code (hex)	81
Length code (dec)	129
Process data channel	8 bit
Input address area	1 Byte
Output address area	0 Byte
Register length	8 bit
Required parameter data	1 Byte

### Electrical properties

#### Potentials: Communications power ( $U_L$ )

Supply voltage	7.5 V DC (via voltage jumper)
Current draw	max. 50 mA

#### Potentials: Segment circuit supply ( $U_S$ )

Supply voltage	24 V DC (via voltage jumper)
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)
Current draw	max. 2 A

#### Electrical isolation/isolation of the voltage ranges

Test voltage: 5 V supply, incoming remote bus/7.5 V supply (bus logics)	500 V AC, 50 Hz, 1 min
Test voltage: 5 V supply, outgoing remote bus/7.5 V supply (bus logics)	500 V AC, 50 Hz, 1 min
Test voltage: 7.5 V supply (bus logics)/24 V supply (I/O)	500 V AC, 50 Hz, 1 min
Test voltage: 24 V supply (I/O) / functional ground	500 V AC, 50 Hz, 1 min

### Input data

#### Digital:

Input name	Digital inputs
Description of the input	IEC 61131-2 Type 2
Number of inputs	8
Connection method	Spring-cage connection
Connection technology	4-conductor
Input voltage	24 V DC (via voltage jumper)

# IB IL 24 DI 8/T2 - Digital module

2860439

<https://www.phoenixcontact.com/us/products/2860439>

Input voltage range "0" signal	-3 V DC ... 5 V DC
Input voltage range "1" signal	15 V DC ... 30 V DC
Nominal input voltage $U_{IN}$	24 V DC
Typical response time	< 1 ms
Protective circuit	Short-circuit and overload protection

## Connection data

### Inline connector

Connection method	Spring-cage connection
Conductor cross-section, rigid	0.08 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section, flexible	0.08 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section AWG	28 ... 16

## Interfaces

### Inline local bus

Connection method	Inline data jumper
-------------------	--------------------

## Dimensions

Dimensional drawing	
Width	48.8 mm
Height	119.8 mm
Depth	71.5 mm
Note on dimensions	Housing dimensions

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-25 °C ... 55 °C
Degree of protection	IP20
Air pressure (operation)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Air pressure (storage/transport)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Ambient temperature (storage/transport)	-25 °C ... 85 °C
Permissible humidity (operation)	10 % ... 95 % (according to DIN EN 61131-2)
Permissible humidity (storage/transport)	10 % ... 95 % (according to DIN EN 61131-2)

## Standards and regulations

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

## Mounting

# IB IL 24 DI 8/T2 - Digital module

2860439

<https://www.phoenixcontact.com/us/products/2860439>



Mounting type	DIN rail mounting
---------------	-------------------

# IB IL 24 DI 8/T2 - Digital module

2860439

<https://www.phoenixcontact.com/us/products/2860439>

## Drawings

Dimensional drawing



Connection diagram



# IB IL 24 DI 8/T2 - Digital module



2860439

<https://www.phoenixcontact.com/us/products/2860439>

## Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)