

IB IL 24 SEG/F-PAC - Segmentation module



2861373

<https://www.phoenixcontact.com/us/products/2861373>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Inline segment terminal, complete with accessories (connector and labeling field), 24 V DC, with fuse

Product description

The terminal is designed for use within an Inline station. This terminal can be used to create a protected partial circuit (segment circuit) within a main circuit. The internal fuse protects the segment circuit. The terminal is not used for voltage supply. It therefore does not have any elements for protection against polarity reversal and surge voltage.

Your advantages

- Automatic creation of a segment circuit in the main circuit
- Segment circuit protected by an internal fuse
- Diagnostic and status indicators

Commercial data

Item number	2861373
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR01
Product key	DRI122
GTIN	4017918894313
Weight per piece (including packing)	75.2 g
Weight per piece (excluding packing)	59 g
Customs tariff number	85389099
Country of origin	DE


IB IL 24 SEG/F-PAC - Segmentation module

2861373

<https://www.phoenixcontact.com/us/products/2861373>

Technical data

Dimensions

Dimensional drawing	
Width	12.2 mm
Height	119.8 mm
Depth	71.5 mm

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Utilization restriction

CCCex note	Use in potentially explosive areas is not permitted in China.
------------	---

Material specifications

Color (Housing)	green (RAL 6021)
-----------------	------------------

Interfaces

Inline local bus

Number of interfaces	2
Connection method	Inline data jumper
Transmission speed	500 kbps / 2 Mbps

System properties

Programming data

ID code (dec.)	none
Register length (bus)	0 Byte

Fieldbus data telegram

Required parameter data	0 Byte
Required configuration data	0 Byte

Product properties

Product type	I/O component
Product family	Inline
Type	modular

IB IL 24 SEG/F-PAC - Segmentation module



2861373

<https://www.phoenixcontact.com/us/products/2861373>

Installation location	Control cabinet
Number of plugs	1

Insulation characteristics

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

Electrical properties

Maximum power dissipation for nominal condition	0 W
Test section	5 V supply, incoming remote bus/7.5 V supply (bus logics) 500 V AC 50 Hz 1 min
	5 V supply, outgoing remote bus/7.5 V supply (bus logics) 500 V AC 50 Hz 1 min
	7.5 V supply (bus logics)/24 V supply (I/O) 500 V AC 50 Hz 1 min
	24 V supply (I/O) / functional ground 500 V AC 50 Hz 1 min
Protective circuit	Overload protection; Fuse
Fuse	SI 5 x 20 6, 300 AT (in scope of delivery)

Supply

I/O voltage	24 V DC
I/O voltage range	19.2 V DC ... 30 V DC
Residual ripple	± 1.2 V
Max. current consumption	6 A

Potentials: Main circuit supply (U_M)

Supply voltage	24 V DC
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)
Current draw	max. 8 A (nominal value)
	typ. 6 A (The terminal is supplied with a 6.3 A slow-blow fuse. In the event of an increased total current in the potential jumpers U_M and U_S , the circuit must be protected through the use of higher rated fuses (max. 8 A, slow-blow).)

Potentials: Segment circuit supply (U_S)

Supply voltage	24 V DC
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)
Power supply	max. 6 A (nominal value)

Connection data

Connection technology

Connection name	Inline connector
-----------------	------------------

Inline connector

Connection method	Spring-cage connection
Conductor cross-section, rigid	0.08 mm ² ... 1.5 mm ²
Conductor cross-section, flexible	0.08 mm ² ... 1.5 mm ²
Conductor cross-section AWG	28 ... 16
Stripping length	8 mm

IB IL 24 SEG/F-PAC - Segmentation module



2861373

<https://www.phoenixcontact.com/us/products/2861373>

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 55 °C
Ambient temperature (storage/transport)	-25 °C ... 85 °C
Permissible humidity (operation)	10 % ... 95 % (according to DIN EN 61131-2)
Permissible humidity (storage/transport)	10 % ... 95 % (according to DIN EN 61131-2)
Air pressure (operation)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Air pressure (storage/transport)	70 kPa ... 106 kPa (up to 3000 m above sea level)

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

IB IL 24 SEG/F-PAC - Segmentation module

2861373


<https://www.phoenixcontact.com/us/products/2861373>

Drawings

Dimensional drawing



Connection diagram



U_M and U_S connected internally via fuse


IB IL 24 SEG/F-PAC - Segmentation module

2861373

<https://www.phoenixcontact.com/us/products/2861373>



Block diagram



IB IL 24 SEG/F-PAC - Segmentation module



2861373

<https://www.phoenixcontact.com/us/products/2861373>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2861373>



DNV GL

Approval ID: TAA00000BN



BV

Approval ID: 21725/C1 BV

BSH

Approval ID: 658a



RINA

Approval ID: ELE121121XG

ABS

Approval ID: 22-2226444-PDA



cULus Recognized

Approval ID: E140324



cULus Listed

Approval ID: E199827

IB IL 24 SEG/F-PAC - Segmentation module



2861373

<https://www.phoenixcontact.com/us/products/2861373>

Classifications

ECLASS

ECLASS-13.0	27242610
ECLASS-15.0	27242610

ETIM

ETIM 10.0	EC001600
-----------	----------

UNSPSC

UNSPSC 21.0	32151600
-------------	----------

2861373

<https://www.phoenixcontact.com/us/products/2861373>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	ea30fd33-8312-4f5d-81fa-99c21bfc0b85

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com