

# IB IL DOR LV-SET-PAC - Disconnect terminal block



2861645

<https://www.phoenixcontact.com/us/products/2861645>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Inline distance terminal, complete with accessories



## Product description

The terminal is designed for use within an Inline station. Within an Inline station, a relay terminal can be used to switch voltages that are not available in the segment in which the terminal is used (e.g., switching 230 V AC in a 24 V DC segment). In this case, place a distance terminal before and after the relay terminal. This maintains the isolating distance between the individual areas. The distance terminals interrupt the potential jumpers for the main and segment voltage, ground, and functional ground. Cables are not connected to these terminals.

## Commercial data

Item number	2861645
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR01
Product key	DRI1Z4
GTIN	4017918894481
Weight per piece (including packing)	123.5 g
Weight per piece (excluding packing)	32 g
Customs tariff number	85389099
Country of origin	DE

# IB IL DOR LV-SET-PAC - Disconnect terminal block



2861645

<https://www.phoenixcontact.com/us/products/2861645>

## Technical data

### Notes

#### Note on application

Note on application	Only for industrial use
---------------------	-------------------------

### Product properties

Product type	Distance terminal
Product family	Inline
Type	modular

#### Insulation characteristics

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

### System properties

#### Programming data (LocalbusSlave)

ID code (dec.)	none
Register length (bus)	0 Byte

#### Fieldbus data telegram

Required parameter data	0 Byte
Required configuration data	0 Byte

### Electrical properties

Test section	24 V supply (I/O) / functional ground 500 V AC 50 Hz 1 min
--------------	--

### Connection data

#### Inline connector


Connection method	Spring-cage connection
Stripping length	8 mm

### Interfaces

#### Inline local bus

Connection method	Inline data jumper
-------------------	--------------------

### Dimensions

Dimensional drawing	
---------------------	--

# IB IL DOR LV-SET-PAC - Disconnect terminal block



2861645

<https://www.phoenixcontact.com/us/products/2861645>

Width	24.4 mm
Height	119.8 mm
Depth	71.5 mm

## Material specifications

Color (Housing)	gray (RAL 7042)
-----------------	-----------------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 55 °C
Ambient temperature (storage/transport)	-25 °C ... 85 °C
Permissible humidity (operation)	75 % ... 85 %
Permissible humidity (storage/transport)	75 % ... 85 %

## Mounting

Mounting type	DIN rail mounting
---------------	-------------------

# IB IL DOR LV-SET-PAC - Disconnect terminal block




2861645

<https://www.phoenixcontact.com/us/products/2861645>

## Drawings

Dimensional drawing




# IB IL DOR LV-SET-PAC - Disconnect terminal block



2861645


<https://www.phoenixcontact.com/us/products/2861645>

Connection diagram



Schematic diagram

- 1 24 V area consisting of station head and I/O terminals
- 2 Relay terminal block separated by inline distance terminals
- 3 24 V area consisting of power terminal and I/O terminals



# IB IL DOR LV-SET-PAC - Disconnect terminal block



2861645

<https://www.phoenixcontact.com/us/products/2861645>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2861645>



**DNV GL**

Approval ID: TAA00000BN



**LR**

Approval ID: LR23398855TA



**BV**

Approval ID: 21725/C1 BV

**ABS**

Approval ID: 22-2226444-PDA



**cULus Recognized**

Approval ID: E140324

# IB IL DOR LV-SET-PAC - Disconnect terminal block



2861645

<https://www.phoenixcontact.com/us/products/2861645>

## Classifications

### ECLASS

ECLASS-13.0	27242692
ECLASS-15.0	27242692

### ETIM

ETIM 10.0	EC002584
-----------	----------

### UNSPSC

UNSPSC 21.0	32151600
-------------	----------

2861645

<https://www.phoenixcontact.com/us/products/2861645>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	1.676 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)