

# ILB DN 24 DI16 DO16 - I/O module



2862602

<https://www.phoenixcontact.com/us/products/2862602>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Inline, Block IO, DeviceNet™, TWIN COMBICON, Digital inputs: 16, 24 V DC, connection technology: 3-conductor, Digital outputs: 16, 24 V DC, connection technology: 3-conductor, degree of protection: IP20, including Inline connector

## Your advantages

- 2 x 5-pos. TWIN-COMBICON male connector
- 16 outputs, 24 V DC, 500 mA
- 16 inputs, 24 V DC

## Commercial data

Item number	2862602
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	DR01
Product key	DRI1A4
GTIN	4017918929084
Weight per piece (including packing)	517.1 g
Weight per piece (excluding packing)	500 g
Customs tariff number	85389091
Country of origin	DE


# ILB DN 24 DI16 DO16 - I/O module

2862602

<https://www.phoenixcontact.com/us/products/2862602>

## Technical data

### Dimensions

Dimensional drawing	
Width	156 mm
Height	141 mm
Depth	57 mm
Note on dimensions	Specifications with connectors

### Notes

Note on application	
Note on application	Only for industrial use

### Interfaces

DeviceNet™	
No. of channels	1
Connection method	TWIN COMBICON
Number of positions	10
Transmission speed	125 kbps ... 500 kbps

### Input data

Digital:	
Input name	Digital inputs
Description of the input	IEC 61131-2 type 1
Number of inputs	16
Connection method	Spring-cage connection
Connection technology	3-conductor
Input voltage	24 V DC
Input voltage range "0" signal	-30 V DC ... 5 V DC
Input voltage range "1" signal	15 V DC ... 30 V DC
Nominal input voltage $U_{IN}$	24 V DC
Nominal input current at $U_{IN}$	5 mA
Total sensor current	max. 2 A
Typical response time	approx. 500 $\mu$ s
Protective circuit	Short-circuit protection, overload protection of the sensor supply

# ILB DN 24 DI16 DO16 - I/O module



2862602

<https://www.phoenixcontact.com/us/products/2862602>

## Output data

Digital:

Output name	Digital outputs
Connection method	Spring-cage connection
Connection technology	3-conductor
Number of outputs	16
Protective circuit	Short-circuit and overload protection
Output voltage	24 V DC
Maximum output current per channel	500 mA
Maximum output current per module / terminal block	8 A
Maximum output current per module	8 A
Nominal output voltage	24 V DC
Nominal load, inductive	12 VA
Nominal load, lamp	12 W
Nominal load, ohmic	12 W

## Product properties

Product type	I/O component
Product family	Inline
Type	Stand-alone Inline
Scope of supply	including Inline connector
No. of channels	32

## Electrical properties

Potentials: Communications power ( $U_L$ )

Supply voltage	24 V DC
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)
Power supply	max. 8 A
Current draw	25 mA

Potentials

Power supply	max. 8 A
Current draw	2 A

Potentials: Power supply to the actuator ( $U_{A1}$ )

Supply voltage	24 V DC
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)
Power supply	max. 8 A
Current draw	4 A

Potentials: Power supply to the actuator ( $U_{A2}$ )

Supply voltage	24 V DC
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)

# ILB DN 24 DI16 DO16 - I/O module



2862602

<https://www.phoenixcontact.com/us/products/2862602>

Power supply	max. 8 A
Current draw	4 A

## Potentials

Power supply	max. 8 A
Current draw	25 mA

## Potentials

Power supply	max. 8 A
Current draw	2 A

## Electrical isolation/isolation of the voltage ranges

Test voltage: I/Os / logic	500 V AC, 50 Hz, 1 min
Test voltage: I/Os / FE	500 V AC, 50 Hz, 1 min
Test voltage: Logic/functional ground	500 V AC, 50 Hz, 1 min

## Connection data

### Connection technology

Connection name	Inline connector
-----------------	------------------

### Inline connector

Connection method	Spring-cage connection
Conductor cross-section, rigid	0.08 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section, flexible	0.08 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section AWG	28 ... 16
Stripping length	8 mm

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-25 °C ... 60 °C
Degree of protection	IP20
Air pressure (operation)	80 kPa ... 108 kPa (up to 2000 m above sea level)
Air pressure (storage/transport)	66 kPa ... 108 kPa (up to 3500 m above sea level)
Ambient temperature (storage/transport)	-25 °C ... 85 °C
Permissible humidity (operation)	85 % (non-condensing)
Permissible humidity (storage/transport)	95 % (non-condensing)

## Standards and regulations

Noise emission	Industrial environment
----------------	------------------------

## Mounting

Mounting type	NS 35/7,5
	DIN rail mounting


# ILB DN 24 DI16 DO16 - I/O module

2862602

<https://www.phoenixcontact.com/us/products/2862602>


## Drawings

Dimensional drawing



The figure shows the general dimensional drawing of the Inline Block IO product family

Connection diagram




# ILB DN 24 DI16 DO16 - I/O module

2862602

<https://www.phoenixcontact.com/us/products/2862602>

Block diagram



# ILB DN 24 DI16 DO16 - I/O module



2862602

<https://www.phoenixcontact.com/us/products/2862602>

## Classifications

### ECLASS

ECLASS-13.0	27242604
ECLASS-15.0	27242604

### ETIM

ETIM 9.0	EC001599
----------	----------

2862602

<https://www.phoenixcontact.com/us/products/2862602>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)