

# IBS OPTOSUB-F/L-LK-OPC - Fiber optic adapter



2864008

<https://www.phoenixcontact.com/us/products/2864008>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



INTERBUS fiber optic adapter, for converting the remote IN interface to fiber optics, FO output left, correction of the optical transmission power

## Commercial data

Item number	2864008
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	DREDDA
GTIN	4046356046398
Weight per piece (including packing)	58.7 g
Weight per piece (excluding packing)	49.64 g
Customs tariff number	85176200
Country of origin	DE

# IBS OPTOSUB-F/L-LK-OPC - Fiber optic adapter



2864008

<https://www.phoenixcontact.com/us/products/2864008>

## Technical data

### Product properties

Product type	Media converter
--------------	-----------------

### Interfaces

Signal	INTERBUS
--------	----------

#### Data: optical FO

Connection method	F-SMA
Wavelength	660 nm
Transmission medium	FO

#### Data: Incoming remote bus

Bus system	INTERBUS
Transmission speed	500 kbps
Connection method	D-SUB 9 plug
Transmission length	35 m (50 m system without optical path diagnostics) 50 m (70 m system with optical path diagnostics)

### Dimensions

Width	65 mm
Height	16 mm
Depth	59 mm

### Material specifications

Color	green
-------	-------

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP20
----------------------	------

# IBS OPTOSUB-F/L-LK-OPC - Fiber optic adapter

2864008

<https://www.phoenixcontact.com/us/products/2864008>



## Classifications

### UNSPSC

UNSPSC 21.0	32151700
-------------	----------

# IBS OPTOSUB-F/L-LK-OPC - Fiber optic adapter



2864008

<https://www.phoenixcontact.com/us/products/2864008>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)