

MACX MCR-SL-2NAM-RO - Isolation switch amplifier



2865049

<https://www.phoenixcontact.com/us/products/2865049>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



NAMUR 2-channel signal conditioner for operating proximity sensors and switches. The signals are transferred to the control level using relay outputs (N/O contact). Line fault detection, 3-way electrical isolation, SIL 2, screw connection.

Your advantages

- Power supply and error indication possible via DIN rail connector
- Up to SIL 2 in accordance with EN 61508
- Installation in zone 2, protection type "n" (EN 60079-15) permitted
- Line fault detection (LFD), can be activated/deactivated, error indicated by flashing red LED with de-excitation of output relay
- LED indicators for supply voltage, switching state, and malfunction in accordance with NAMUR NE 44
- Relay signal output (N/O contact)
- Direction of operation can be selected (operating or closed circuit current behavior)
- Input for NAMUR proximity sensors (EN 60947-5-6), floating contacts or contacts with resistance circuit
- 2-channel
- 3-way electrical isolation

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2865049 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | C402 |
| Product key | DK1113 |
| GTIN | 4046356492072 |
| Weight per piece (including packing) | 186.5 g |
| Weight per piece (excluding packing) | 140 g |
| Customs tariff number | 85365019 |
| Country of origin | DE |

2865049

<https://www.phoenixcontact.com/us/products/2865049>

Technical data

Product properties

| | |
|-----------------|----------------------------|
| Product type | Isolating switch amplifier |
| Product family | MACX Analog |
| Application | Digital IN |
| No. of channels | 2 |
| Configuration | DIP switches |

System properties

Functionality

| | |
|---------------|--------------|
| Configuration | DIP switches |
|---------------|--------------|

Electrical properties

| | |
|---|-----------------|
| Electrical isolation | 3-way isolation |
| Electrical isolation between input and output | yes |
| Maximum power dissipation for nominal condition | < 1 W |

Electrical isolation Input/output IEC/EN 60079-11

| | |
|--------------------------|---------------------|
| Standards/regulations | IEC/EN 60079-11 |
| Rated insulation voltage | 375 V _{PP} |
| Overvoltage category | III |
| Pollution degree | 2 |

Electrical isolation Input/supply, DIN rail connector IEC/EN 60079-11

| | |
|--------------------------|---------------------|
| Standards/regulations | IEC/EN 60079-11 |
| Rated insulation voltage | 375 V _{PP} |
| Overvoltage category | II |
| Pollution degree | 2 |

Electrical isolation Input/supply, DIN rail connector IEC/EN 61010-1

| | |
|--------------------------|----------------------|
| Standards/regulations | IEC/EN 61010-1 |
| Rated insulation voltage | 300 V _{rms} |
| Overvoltage category | II |
| Pollution degree | 2 |
| Insulation | Safe isolation |

Electrical isolation Output 1/output 2/input, power supply, DIN rail connector IEC/EN 61010-1

| | |
|--------------------------|----------------------|
| Standards/regulations | IEC/EN 61010-1 |
| Rated insulation voltage | 300 V _{rms} |
| Overvoltage category | III |
| Pollution degree | 2 |
| Insulation | Safe isolation |

Electrical isolation Output 1/output 2/input/power supply, DIN rail connector

MACX MCR-SL-2NAM-RO - Isolation switch amplifier



2865049

<https://www.phoenixcontact.com/us/products/2865049>

| | |
|----------------------|-------------------------|
| Test voltage | 2.5 kV AC (50 Hz, 60 s) |
| Overvoltage category | III |
| Pollution degree | 2 |

Supply

| | |
|--------------------------|-------------------------|
| Nominal supply voltage | 24 V DC -20 % ... +25 % |
| Supply voltage range | 19.2 V DC ... 30 V DC |
| Max. current consumption | 35 mA (24 V DC) |
| Power dissipation | < 1 W |
| Power consumption | < 1 W |

Input data

Signal: NAMUR

| | |
|---|---|
| Number of inputs | 2 |
| Available input sources | NAMUR proximity sensors (IEC/EN 60947-5-6) floating switch contacts Switch contacts with resistance circuit |
| Switching threshold "0" signal current | < 1.2 mA (blocking) |
| Switching threshold "1" signal, current | > 2.1 mA (conductive) |
| Short-circuit current | 8 mA |
| Switching hysteresis | < 0.2 mA |
| Line fault detection | < 0.05 mA ... 0.35 mA (Line break) < 100 Ω ... 360 Ω (Short circuit) Activated /deactivated via DIP switch |
| Open-circuit voltage | 8 V DC |

Output data

Switching: Relay

| | |
|---------------------------|---|
| Contact switching type | 1 N/O contact per channel |
| Contact material | AgSnO ₂ , hard gold-plated |
| Maximum switching voltage | 250 V AC (2 A) 120 V DC (0.2 A) 30 V DC (2 A) |
| Maximum switching power | 500 VA |
| Recommended minimum load | 5 V / 10 mA |
| Switching frequency | ≤ 20 Hz (without load) |

Signal

| | |
|-------------------|---|
| Number of outputs | 2 |
|-------------------|---|

Connection data

| | |
|-------------------|------------------|
| Connection method | Screw connection |
| Stripping length | 7 mm |
| Screw thread | M3 |

MACX MCR-SL-2NAM-RO - Isolation switch amplifier



2865049

<https://www.phoenixcontact.com/us/products/2865049>

| | |
|----------------------------------|---|
| Conductor cross-section rigid | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section flexible | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section AWG | 24 ... 14 |
| Tightening torque | 0.5 Nm ... 0.6 Nm |

Test socket

| | |
|---------------|------|
| Max. diameter | 2 mm |
|---------------|------|

Ex data

| | |
|-----------------------|--------|
| Ex installation (EPL) | Gc |
| | Div. 2 |

Interfaces


Data

| | |
|-----------------|---|
| No. of channels | 0 |
|-----------------|---|

Signaling

| | |
|----------------|------------------------------|
| Status display | Green LED (supply voltage) |
| | LED yellow (switching state) |
| | Red LED (line errors) |

Dimensions

| | |
|---------------------|--|
| Dimensional drawing |  |
| Width | 12.5 mm |
| Height | 112.5 mm |
| Depth | 113.7 mm |
| Depth NS 35/7,5 | 114.5 mm (Snapped onto DIN rail NS 35/7,5 in accordance with EN 60715) |

Material specifications

| | |
|--|-----------------|
| Color | gray (RAL 7042) |
| Flammability rating according to UL 94 (Housing) | V0 (Housing) |
| Housing material | PA 6.6-FR |

Characteristics

Safety data

| | |
|------------------------------|---|
| Safety Integrity Level (SIL) | 2 |
|------------------------------|---|

Safety data: IEC 61508 - Low demand

2865049

<https://www.phoenixcontact.com/us/products/2865049>

| | |
|-------------------------------------|---|
| Safety Integrity Level (SIL) | 2 |
| Safety data: IEC 61508 - Low demand | |
| Safety Integrity Level (SIL) | 2 |

Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Degree of protection | IP20 (not assessed by UL) |
| Ambient temperature (operation) | -40 °C ... 60 °C (Any mounting position) -40 °C ... 70 °C (Derating) |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C |
| Permissible humidity (operation) | 5 % ... 95 % (non-condensing) |

Altitude range (≤ 2000 m)

| | |
|---------------------------------|--|
| Altitude | ≤ 2000 m (The technical data refers to altitudes ≤2000 m above mean sea level. For altitudes >2000 m above mean sea level, refer to the data sheet.) |
| Ambient temperature (operation) | -40 °C ... 60 °C -40 °C ... 70 °C (Derating) |
| Rated insulation voltage | 253 V AC (Power supply, input / output) 125 V DC (Power supply, input / output) |

Altitude range (≤ 3000 m)

| | |
|---------------------------------|--|
| Height range | > 2000 m ... 3000 m |
| Ambient temperature (operation) | -40 °C ... 54 °C -40 °C ... 63 °C (Derating) |
| Rated insulation voltage | 190 V AC (Power supply, input / output) 110 V DC (Power supply, input / output) |

Altitude range (≤ 4000 m)

| | |
|---------------------------------|---|
| Height range | > 3000 m ... 4000 m |
| Ambient temperature (operation) | -40 °C ... 48 °C -40 °C ... 56 °C (Derating) |
| Rated insulation voltage | 60 V AC/DC (Power supply, input / output) |

Altitude range (≤ 5000 m)

| | |
|---------------------------------|---|
| Height range | > 4000 m ... 5000 m |
| Ambient temperature (operation) | -40 °C ... 42 °C |
| Rated insulation voltage | 60 V AC/DC (Power supply, input / output) |

Approvals

CE

| | |
|-------------|----------------|
| Certificate | CE-compliant |
| Note | and EN 61326-1 |

ATEX

| | |
|----------------|----------------------------|
| Identification | Ⓜ II 3G Ex ec nC IIC T4 Gc |
|----------------|----------------------------|

MACX MCR-SL-2NAM-RO - Isolation switch amplifier



2865049

<https://www.phoenixcontact.com/us/products/2865049>

| | |
|-------------|----------------------|
| Certificate | IBExU 07 ATEX 1069 X |
|-------------|----------------------|

IECEX

| | |
|----------------|--------------------|
| Identification | Ex ec nC IIC T4 Gc |
| Certificate | IBE 08.0001 X |

CCC / China-Ex

| | |
|----------------|--------------------|
| Identification | Ex ec nC IIC T4 Gc |
| Certificate | 2021122304114179 |

UL, USA/Canada

| | |
|----------------|---------------------------------------|
| Identification | UL 508 Listed |
| | UL 61010 Listed |
| | Class I, Div. 2, Groups A, B, C, D T4 |
| | Class I, Zone 2, Group IIC T4 |

Shipbuilding approval

| | |
|-------------|-------------------|
| Certificate | DNV GL TAA00000AG |
|-------------|-------------------|

Safety Integrity Level (SIL, IEC 61508)

| | |
|----------------|-----------------------|
| Identification | 2 |
| Certificate | IN-AT-AS-MRL-24-00163 |

Systematic Capability

| | |
|----------------|---|
| Identification | 3 |
|----------------|---|

INMETRO

| | |
|----------------|--------------------|
| Identification | Ex ec nC IIC T4 Gc |
| Certificate | DNV 18.0114 X |

EAC Ex

| | |
|----------------|---------------------------------|
| Identification | Ex ec nC IIC T4 Gc |
| Certificate | BY/112 02.01 TP012 103.01 00078 |

Shipbuilding data

| | |
|-------------|---|
| Temperature | B |
| Humidity | B |
| Vibration | A |
| EMC | B |
| Enclosure | Required protection according to the Rules shall be provided upon installation on board |

EMC data

| | |
|-------------------------------|--------------------------------|
| Electromagnetic compatibility | Conformance with EMC directive |
| Noise immunity | EN 61000-6-2 |
| | EN 61326 |

Noise emission

| | |
|-----------------------|--------------|
| Standards/regulations | EN 61000-6-4 |
|-----------------------|--------------|

MACX MCR-SL-2NAM-RO - Isolation switch amplifier



2865049

<https://www.phoenixcontact.com/us/products/2865049>

Electromagnetic HF field

| | |
|-----------------------|--------------------------|
| Designation | Electromagnetic RF field |
| Standards/regulations | EN 61000-4-3 |
| Evaluation criterion | A |

Fast transients (burst)

| | |
|-----------------------|-------------------------|
| Designation | Fast transients (burst) |
| Standards/regulations | EN 61000-4-4 |
| Evaluation criterion | A |

Conducted interference

| | |
|-----------------------|-------------------------|
| Designation | Conducted interferences |
| Standards/regulations | EN 61000-4-6 |
| Evaluation criterion | A |

Standards and regulations

| | |
|----------------------|-----------------|
| Electrical isolation | 3-way isolation |
|----------------------|-----------------|

GB Standard

| | |
|-----------------------|-------------|
| Standards/regulations | GB/T 3836.1 |
| | GB/T 3836.3 |
| | GB/T 3836.8 |

Mounting

| | |
|---------------|-------------------|
| Mounting type | DIN rail mounting |
|---------------|-------------------|

MACX MCR-SL-2NAM-RO - Isolation switch amplifier



2865049

<https://www.phoenixcontact.com/us/products/2865049>

Drawings

Dimensional drawing




MACX MCR-SL-2NAM-RO - Isolation switch amplifier



2865049

<https://www.phoenixcontact.com/us/products/2865049>

Block diagram




2865049

<https://www.phoenixcontact.com/us/products/2865049>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2865049>


 **UL Listed**
Approval ID: E330267

 **cUL Listed**
Approval ID: E330267


Functional Safety
Approval ID: 07-06-39 R005 V2R2

DNV
Approval ID: TAA00000AG

TUEV Austria FS
Approval ID: IN-AT-AS-24-00163


 **IECEX**
Approval ID: IECEX IBE 08.0001X

 **cUL Listed**
Approval ID: E199827

 **UL Listed**
Approval ID: FILE E 199827

 **ATEX**
Approval ID: IBExU07ATEX1069

INMETRO
Approval ID: DNV 18.0114 X

 **CCC**
Approval ID: 2021122304114179

2865049

<https://www.phoenixcontact.com/us/products/2865049>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27210121 |
| ECLASS-15.0 | 27210121 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001485 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121000 |
|-------------|----------|

2865049

<https://www.phoenixcontact.com/us/products/2865049>

Environmental product compliance

EU RoHS

| | |
|---|--------------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 7(a), 7(c)-I |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|--|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| | 2,2',6,6'-tetrabromo-4,4'-isopropylidenediphenol(CAS: 79-94-7) |
| SCIP | bfff540a-2390-4ba7-9dfe-999c26e8e443 |

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 4.465 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
 586 Fulling Mill Road
 Middletown, PA 17057, United States
 (+717) 944-1300
info@phoenixcon.com