

# RIF-2-BPT/4X21 - Relay base



2900934

<https://www.phoenixcontact.com/us/products/2900934>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Relay base RIF-2..., for industrial relay with 2 or 4 changeover contacts, Push-in connection, plug-in option for input/interference suppression modules, for mounting on NS 35/7,5



## Commercial data

Item number	2900934
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	C465
Product key	DK6523
GTIN	4046356733175
Weight per piece (including packing)	69.15 g
Weight per piece (excluding packing)	62.825 g
Customs tariff number	85366990
Country of origin	CN

# RIF-2-BPT/4X21 - Relay base



2900934

<https://www.phoenixcontact.com/us/products/2900934>

## Technical data

### Product properties

Product type	Relay socket
Product family	RIFLINE complete
Set comprises	2903304 RIF-2-RPT-LV-230AC/4X21
	2903305 RIF-2-RPT-LV-120AC/4X21
	2903306 RIF-2-RPT-LV-24AC/4X21
	2903308 RIF-2-RPT-LDP-24DC/4X21
	2903310 RIF-2-RPT-LV-230AC/2X21
	2903311 RIF-2-RPT-LV-120AC/2X21
	2903313 RIF-2-RPT-LV-24AC/2X21
	2903315 RIF-2-RPT-LDP-24DC/2X21
	2908332 RIF-2-RPT-LDP-24DC/4X21 AU
	1188200 RIF-2-RPT-LV-230AC/4X21AU
1577412 RIF-2-RPT-PHS-LDP-24DC/2X21	

### Electrical properties

Nominal voltage $U_N$	250 V AC/DC
Nominal current $I_N$	max. 12 A (Depends on application/assembly)
Protective circuit	depending on the selected input/suppressor modules

### Connection data

Connection method	Push-in connection
Stripping length	8 mm
Conductor cross-section rigid	0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section flexible	0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
	0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> (Ferrule with plastic sleeve)
	0.14 mm <sup>2</sup> ... 1 mm <sup>2</sup> (Ferrule with plastic sleeve, two conductors on double terminal block)
Conductor cross-section AWG	26 ... 16 (solid)
	26 ... 16 (flexible)

### Dimensions

#### Item dimensions

Width	31 mm
Height	96 mm
Depth (Retaining bracket)	75 mm (with retaining bracket)

#### Drill hole

Diameter	3.2 mm
----------	--------

### Material specifications

Color	gray (RAL 7042)
-------	-----------------

# RIF-2-BPT/4X21 - Relay base



2900934

<https://www.phoenixcontact.com/us/products/2900934>

Flammability rating according to UL 94 (Housing)	V2 (Housing)
--	--------------

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C (Depends on application/assembly)
Ambient temperature (storage/transport)	-40 °C ... 85 °C

## Approvals

### Corrosive gas test

Identification	ISA-S71.04. G3 Harsh Group
	EN 60068-2-60

## Mounting

Mounting type	DIN rail mounting
Mounting position	any

# RIF-2-BPT/4X21 - Relay base



2900934

<https://www.phoenixcontact.com/us/products/2900934>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2900934>



**CSA**

Approval ID: 76787



**UL Recognized**

Approval ID: FILE E 113228



**EAC**

Approval ID: RU D-DE.B\*00573/18

**DNV**

Approval ID: TAA000018V

# RIF-2-BPT/4X21 - Relay base



2900934

<https://www.phoenixcontact.com/us/products/2900934>

## Classifications

### ECLASS

ECLASS-13.0	27371603
ECLASS-15.0	27371603

### ETIM

ETIM 10.0	EC001456
-----------	----------

### UNSPSC

UNSPSC 21.0	39122300
-------------	----------

# RIF-2-BPT/4X21 - Relay base



2900934

<https://www.phoenixcontact.com/us/products/2900934>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)