

# PSI-CAB-GSM/UMTS- 5M - Antenna cable



2900980

<https://www.phoenixcontact.com/us/products/2900980>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cellular antenna cable, 5 m in length, SMA (male) -> SMA (female), 50 ohm impedance



## Commercial data

Item number	2900980
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN25
Product key	DNC4Z1
GTIN	4046356568906
Weight per piece (including packing)	278 g
Weight per piece (excluding packing)	278 g
Customs tariff number	85442000
Country of origin	PL

# PSI-CAB-GSM/UMTS- 5M - Antenna cable



2900980

<https://www.phoenixcontact.com/us/products/2900980>

## Technical data

### Product properties

Product type	Coaxial cable
--------------	---------------

### Electrical properties

Frequency range	850 MHz
	900 MHz
	1800 MHz
	1900 MHz
	2100 MHz
	2600 MHz
Impedance	50 $\Omega$

### Connection data

#### Connector connection

Connection method	SMA (male)
-------------------	------------

#### Connector connection

Connection method	SMA (female)
-------------------	--------------

### Material specifications

Color (Outer sheath)	black (RAL 9005)
Outer sheath, material	LSFH

### Cable/line

Cable length	5 m
External cable diameter	5.50 mm
Outer sheath, material	LSFH
Bending radius, long-term	82.00 mm

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C

# PSI-CAB-GSM/UMTS- 5M - Antenna cable



2900980

<https://www.phoenixcontact.com/us/products/2900980>

## Classifications

### ECLASS

ECLASS-13.0

27060310

### ETIM

ETIM 9.0

EC001682

### UNSPSC

UNSPSC 21.0

26121600

# PSI-CAB-GSM/UMTS- 5M - Antenna cable



2900980

<https://www.phoenixcontact.com/us/products/2900980>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-25
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	2ba68983-1191-414a-9f44-1a0dd332146c

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)