MINI-BAT/24DC/0.8AH - Battery module

2866666

https://www.phoenixcontact.com/us/products/2866666

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Battery module (device with battery), lead AGM, VRLA technology, 24 V DC, 0.8 Ah.

Product description

MINI-BAT – battery module with lead AGM technology for maximum buffer times.

Your advantages

- Maximum buffer times

ELEKTROGERÄTE RÜCKNAHME

Commercial data

Item number	2866666
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	CM24
Product key	CMUEV3
GTIN	4046356152129
Weight per piece (including packing)	835 g
Weight per piece (excluding packing)	764 g
Customs tariff number	85072080
Country of origin	CN

Technical data

Notes

General

Note on the battery	This product contains a battery with a limited shelf life that must be charged every few months. The product packaging indicates when the battery must be started up or recharged. The general shelf life can be found in the energy storage devices area under “Latest startup”.

Input data

Input voltage	24 V DC
Buffer period	20 min (1 A)
	7 min (2 A)

Output data

Nominal output voltage	24 V DC
Output current I_{max}	5 A
Output fuse	5 A
Connection in parallel	5
Connection in series	no

Battery operation

Nominal output voltage	24 V DC
Nominal output current (I_N)	5 A

Energy storage

End-of-charge voltage	27.6 V
Charging current	1 A
Nominal capacity	0.8 Ah
Service life	3 Years (20 °C)
Latest startup (battery only) - range	3 Months (0 °C ... 20 °C)
	3 Months ... 1 Months (20 °C ... 30 °C)
	1 Months (30 °C ... 40 °C)
Battery technology	VRLA-AGM
Memory medium	Lead rechargeable battery module
Accumulator type	YUASA NP0.8-12
	YUCEL Y0.8-12
	YUVOLT 0.8-12
Number of cells	1
Size designation	Block
Battery pack	yes
IQ technology	no
Suitable for fast charging	yes

Product properties

Product type	Battery module
Product family	Battery module (device with battery)
Application	for MINI DC-UPS
Disposal	Used batteries must not be thrown away with household waste, they should instead be disposed of in accordance with applicable national regulations.
IQ technology	no

Insulation characteristics

Protection class	III

Dimensions

Width	67.5 mm
Height	99 mm
Depth	107 mm

Installation dimensions

Installation distance right/left	0 mm / 0 mm
Installation distance top/bottom	30 mm / 30 mm

Material specifications

Housing material	Plastic
Type of housing	Polyamide PA, color: green

Environmental and real-life conditions

Ambient conditions


Degree of protection	IP20
Ambient temperature (operation)	0 °C ... 40 °C
Ambient temperature (storage/transport)	0 °C ... 40 °C
Max. permissible relative humidity (operation)	95 %

Ex data

Suited for EX-applications	no

Drawings

Block diagram



Graphic

Load Current	Buffertime for 24 V DC system										
	Minutes										Hour
	8	9	10	15	20	25	30	40	45	50	1
0.5 A											
1 A											
1.5 A											
2 A											

The data is based on an ambient temperature of +25 °C at the start of use.

2866666 MINI-BAT/24DC/0.8AH **1394729** TRIO-BAT/PB/24DC/1.2AH

Buffer times for MINI DC UPS for 24 V systems

Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/2866666

EAC
Approval ID: RU S-DE.BL08.W.00764

EAC
Approval ID: RU*DE*01.B.78948/21

Classifications

ECLASS

ECLASS-13.0	27050403
ECLASS-15.0	27050403

ETIM

ETIM 10.0	EC003893

UNSPSC

UNSPSC 21.0	26111700

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-3
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	2abd164f-925d-4663-b647-68c5e5ff90d2

EF3.1 Climate Change

CO2e kg	31.568 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com