

# FLKM-2KS40/PMT/SI/YCS - Passive module



2901034

<https://www.phoenixcontact.com/us/products/2901034>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

VARIOFACE interface module for Yokogawa I/O AAI135 and AAI835 modules.



The figure shows the version with spring-cage connection

## Commercial data

Item number	2901034
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	DK218N
GTIN	4046356563697
Weight per piece (including packing)	266 g
Weight per piece (excluding packing)	259 g
Country of origin	DE

## Technical data

### Product properties

Product type	Interface module
No. of channels	8
Operating mode	100% operating factor

### Insulation characteristics: Air clearances and creepage distances

Insulation	Functional insulation
Overvoltage category	II
Pollution degree	2

### Electrical properties

Operating voltage (DC)	≤ 30 V DC
Fuse	0.05 A TR5 (slow-blow) (F1 ... F16)
Current (per branch)	≤ 0.05 A (T <sub>U</sub> = 23 °C)

### Air clearances and creepage distances

Rated insulation voltage	50 V
Rated surge voltage	0.5 kV (1.2/50 μs)

### Supported controller: YOKOGAWA CS3000 CentumVP

Suitable I/O card	AAI135
	AAI835

### Supported controller: YOKOGAWA STARDOM

Suitable I/O card	NFAI135
	NFAI835

## Connection data

### Connection 1 (control level)

Connection method	Yokogawa, KS compatible
Number of connections	2
Number of positions	40
Note	Usable system cables: Phoenix Contact YUC40, Yokogawa KS1
Tightening torque	0.5 Nm
Pitch	2.54 mm

### Connection 2 (field level)

Connection method	Screw connection with disconnect knife
Stripping length	8 mm
Screw thread	M3
Number of positions	16
Conductor cross-section rigid	0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>
Conductor cross-section rigid (2 conductors with same cross	0.2 mm <sup>2</sup> ... 1 mm <sup>2</sup>

# FLKM-2KS40/PMT/SI/YCS - Passive module



2901034

<https://www.phoenixcontact.com/us/products/2901034>

section)	
Conductor cross-section flexible	0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>
	0.25 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> (Ferrule without plastic sleeve)
	0.25 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> (Ferrule with plastic sleeve)
Conductor cross-section flexible (2 conductors with same cross section)	0.2 mm <sup>2</sup> ... 1 mm <sup>2</sup>
	0.25 mm <sup>2</sup> ... 0.75 mm <sup>2</sup> (Ferrule without plastic sleeve)
	0.5 mm <sup>2</sup> ... 1 mm <sup>2</sup> (TWIN ferrule with plastic sleeve)
Conductor cross-section AWG	24 ... 12
Tightening torque	0.5 Nm ... 0.6 Nm
Pitch	5.08 mm

## Signaling

Status display present	no
------------------------	----

## Dimensions

### Item dimensions

Width	91.6 mm
Height	111.8 mm
Depth	49.7 mm

## Environmental and real-life conditions

### Ambient conditions

Degree of protection (Module)	IP00
Degree of protection (Installation location)	≤ IP54
Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Altitude	≤ 2000 m

## Approvals

### UKCA

Certificate	UKCA-compliant
-------------	----------------

## Standards and regulations

### Air clearances and creepage distances

Standards/regulations	EN IEC 60664-1
-----------------------	----------------

## Mounting

Mounting type	DIN rail mounting
Mounting position	any

## Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning
--------------------	------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

# FLKM-2KS40/PMT/SI/YCS - Passive module



2901034

<https://www.phoenixcontact.com/us/products/2901034>

instructions of the respective third-party manufacturer must also be met.

# FLKM-2KS40/PMT/SI/YCS - Passive module




2901034

<https://www.phoenixcontact.com/us/products/2901034>

## Drawings

Dimensional drawing




# FLKM-2KS40/PMT/SI/YCS - Passive module



2901034

<https://www.phoenixcontact.com/us/products/2901034>

Circuit diagram



Connection to AAI 835


# FLKM-2KS40/PMT/SI/YCS - Passive module



2901034

<https://www.phoenixcontact.com/us/products/2901034>

Circuit diagram



Connection to AAI 135

# FLKM-2KS40/PMT/SI/YCS - Passive module



2901034

<https://www.phoenixcontact.com/us/products/2901034>

## Classifications

### ECLASS

ECLASS-13.0	27141152
ECLASS-15.0	27141152

### ETIM

ETIM 10.0	EC002780
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

2901034

<https://www.phoenixcontact.com/us/products/2901034>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)