


FLKM-2KS50/32DO/YCS/ZFKDS - Passive module



2901200

<https://www.phoenixcontact.com/us/products/2901200>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



32-channel output module with spring-cage connection. The voltage supply and the 50-pos. system connection are designed redundantly. Suitable for Yokogawa ADV551 card.

Commercial data

Item number	2901200
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	DK218N
GTIN	4046356576475
Weight per piece (including packing)	427 g
Weight per piece (excluding packing)	427 g
Country of origin	DE

Technical data

Product properties

Product type	Interface module
Operating mode	100% operating factor

Insulation characteristics: Air clearances and creepage distances between the power circuits

Insulation	Functional insulation
Overvoltage category	II
Pollution degree	2

Electrical properties

Max. permissible operating voltage	30 V DC
Max. permissible current	100 mA (per path)
Max. permissible total current	4 A (Protected by slow-blow fuse 4 A, 5x20 (short-circuit protection only))
Nominal voltage U_N	24 V DC
Max. total current of all branches	4 A

Air clearances and creepage distances between the power circuits

Rated insulation voltage	50 V
Rated surge voltage	0.5 kV

Supported controller: YOKOGAWA CS3000 CentumVP

Suitable I/O card	ADV551
-------------------	--------

Connection data

Field level

Connection method	Spring-cage connection
Stripping length	8 mm
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 12

Controller level

Connection method	Yokogawa, KS compatible
Number of connections	2
Number of positions	50
Tightening torque	0.5 Nm

Signaling

Status display present	yes
Operating voltage display	Green LED

Dimensions

2901200

<https://www.phoenixcontact.com/us/products/2901200>

Item dimensions

Width	180 mm
Height	90 mm
Depth	77 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP00
Degree of protection (Installation location)	≥ IP54 (Installation location)
Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Altitude	≤ 2000 m

Standards and regulations

Air clearances and creepage distances between the power circuits

Standards/regulations	EN IEC 60664-1
-----------------------	----------------

Mounting

Mounting type	DIN rail mounting
Assembly note	in rows with zero spacing
Mounting position	any

Notes

Notes on operation	No additional touch protection is required when using a SELV/PELV voltage (≤ 25 V AC or 60 V DC).
Notes on operation	At least one functional insulation against adjacent modules is complied with (in the support rail direction). If the application has stricter requirements for the insulation (basic insulation or reinforced insulation), they must be realized by applying suitable measures (e. g. partition plates).
Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.

FLKM-2KS50/32DO/YCS/ZFKDS - Passive module




2901200

<https://www.phoenixcontact.com/us/products/2901200>

Drawings

Circuit diagram



FLKM-2KS50/32DO/YCS/ZFKDS - Passive module



2901200

<https://www.phoenixcontact.com/us/products/2901200>

Classifications

ECLASS

ECLASS-13.0	27141152
ECLASS-15.0	27141152

ETIM

ETIM 9.0	EC002780
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

2901200

<https://www.phoenixcontact.com/us/products/2901200>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Hexahydromethylphthalic anhydride(CAS: n/a)
	Lead(CAS: 7439-92-1)
SCIP	881fe814-79f9-47e3-a494-12eeef7adcc5

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
 586 Fulling Mill Road
 Middletown, PA 17057, United States
 (+717) 944-1300
info@phoenixcon.com