

RAD-ISM-2400-HOP-EU-10 - Hopkey



2867898

<https://www.phoenixcontact.com/us/products/2867898>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The HOPKEY contains information such as the transmission frequencies used and the hop sequence. This information is required when installing an additional transceiver/repeater in an existing bidirectional RAD Line IO system, for example.

Product description

When the supply voltage is switched on, the information is transmitted to a non-volatile memory in the module from a plugged in HOPKEY. Then this HOPKEY can be used to "train" other receivers. In the last receiver, the HOPKEY can be preserved. If no HOPKEY is plugged in, the information in the module is used.

Your advantages

- Trusted Wireless technology with frequency hopping method
- No parameterization or programming required
- Up to eight I/O extension modules can be connected via bus foot
- License-free 2.4 GHz ISM band

Commercial data

Item number	2867898
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	DN26
Product key	DNC652
GTIN	4046356142489
Weight per piece (including packing)	22.3 g
Weight per piece (excluding packing)	20.6 g
Customs tariff number	85423261
Country of origin	CA

RAD-ISM-2400-HOP-EU-10 - Hopkey

2867898

<https://www.phoenixcontact.com/us/products/2867898>



Technical data

Product properties

Product type	Storage medium
--------------	----------------

RAD-ISM-2400-HOP-EU-10 - Hopkey



2867898

<https://www.phoenixcontact.com/us/products/2867898>

Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com