

FLKM-PA-D37/HW/DIO/C300 - Front adapter



2901423

<https://www.phoenixcontact.com/us/products/2901423>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE front adapter, for Honeywell C300, Series C I/O, maximum of 1x 16 channels can be connected (37-pos. D-SUB connector). Specifically for connecting digital, redundant I/O cards.

Your advantages

- Specifically for redundant digital I/O cards
- Connection of a maximum of 16 digital channels
- Preassembled system cables are connected directly to I/O modules using the front adapters
- Front adapter with D-SUB connector

Commercial data

Item number	2901423
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	C421
Product key	DK231H
GTIN	4046356592192
Weight per piece (including packing)	93 g
Weight per piece (excluding packing)	95.5 g
Customs tariff number	85366990
Country of origin	DE

2901423

<https://www.phoenixcontact.com/us/products/2901423>

Technical data

Product properties

Product type	Front adapter
Product family	VARIOFACE

Insulation characteristics: Air clearances and creepage distances

Insulation	Functional insulation
Overvoltage category	II
Pollution degree	2

Electrical properties

Operating voltage (AC)	≤ 30 V AC
Operating voltage (DC)	≤ 60 V DC
Current (per branch)	≤ 2 A

Air clearances and creepage distances

Rated insulation voltage	63 V
Rated surge voltage	0.6 kV (1.2/50 μs)

Supported controller: HONEYWELL Experion PKS C300/C-Series

Suitable I/O card	TDIL01 (non-redundant)
	TDIL11 (redundant)
	TDIL51 (non-redundant)
	TDIL61 (redundant)
	TDI110 (non-redundant)
	TDI120 (redundant)
	TDOB01 (non-redundant)
	TDOB11 (redundant)
	TDOB51 (non-redundant)
	TDOB61 (redundant)
	TAID01 (non-redundant)
	TAID11 (redundant)
	TAOX01 (non-redundant)
	TAOX11 (redundant)
	TAOX51 (non-redundant)
	TAOX61 (redundant)
	TAON01 (non-redundant)
TAON11 (redundant)	

Connection data

Connection 1 (control level)

Connection method	Plug-in connection
Number of connections	2

FLKM-PA-D37/HW/DIO/C300 - Front adapter



2901423

<https://www.phoenixcontact.com/us/products/2901423>

Number of positions	16
Pitch	5.08 mm

Connection 2 (field level)

Connection in acc. with standard	IEC 60807-2
Connection method	D-SUB pin strip
Screw thread	UNC 4-40
Number of connections	1
Number of positions	37
Insertion/withdrawal cycles	> 500
Pitch	2.77 mm

Connection 3 (shield)

Connection method	Spade connection
Number of positions	1
Note	2,8 x 0,8

Dimensions

Item dimensions

Width	93.8 mm
Height	28 mm
Depth	46.74 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection (Module)	IP00
Degree of protection (Installation location)	≥ IP54
Ambient temperature (operation)	-20 °C ... 70 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Altitude	≤ 2000 m

Standards and regulations

Air clearances and creepage distances

Standards/regulations	EN IEC 60664-1
-----------------------	----------------

Mounting

Mounting type	Plug-in mounting
Mounting position	any

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

FLKM-PA-D37/HW/DIO/C300 - Front adapter




2901423

<https://www.phoenixcontact.com/us/products/2901423>

Drawings

Circuit diagram



Connection scheme: FLKM-PA-D37/HW/DIO/C300

FLKM-PA-D37/HW/DIO/C300 - Front adapter





2901423

<https://www.phoenixcontact.com/us/products/2901423>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2901423>

 cUL Recognized Approval ID: E238705				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	125 V	1 A	30 - 12	-

 UL Recognized Approval ID: E238705				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	125 V	1 A	30 - 12	-

FLKM-PA-D37/HW/DIO/C300 - Front adapter



2901423

<https://www.phoenixcontact.com/us/products/2901423>

Classifications

ECLASS

ECLASS-13.0	27242292
ECLASS-15.0	27242292

ETIM

ETIM 10.0	EC002584
-----------	----------

UNSPSC

UNSPSC 21.0	32151600
-------------	----------

FLKM-PA-D37/HW/DIO/C300 - Front adapter



2901423

<https://www.phoenixcontact.com/us/products/2901423>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com