

EM-CAN-GATEWAY-IFS - Data interface



2901504

<https://www.phoenixcontact.com/us/products/2901504>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Gateway for the connection of up to 32 Interface system devices to a higher-level controller via CANopen®. The Interface system devices are connected to the gateway via DIN rail connectors. The DIN rail connectors are provided.

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2901504 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | C477 |
| Product key | DK7722 |
| GTIN | 4046356607100 |
| Weight per piece (including packing) | 155.05 g |
| Weight per piece (excluding packing) | 99.99 g |
| Customs tariff number | 85176200 |
| Country of origin | DE |

2901504

<https://www.phoenixcontact.com/us/products/2901504>

Technical data

Notes

Utilization restriction

| | |
|----------|---|
| EMC note | EMC: class A product, see manufacturer's declaration in the download area |
|----------|---|

Product properties

| | |
|----------------|-----------------------|
| Product type | Gateways/Proxies |
| Operating mode | 100% operating factor |

Insulation characteristics

| | |
|----------------------|-----|
| Overvoltage category | III |
| Pollution degree | 2 |

Input data

Digital

| | |
|-------------------------------|---|
| Number | 8 |
| Rated actuating voltage U_C | 24 V DC ± 20 % |
| Rated actuating current I_C | 3 mA |
| Protective circuit | Reverse polarity protection Surge protection |

Output data

Digital: Switching outputs

| | |
|---------------------------|--|
| Number | 4 |
| Residual voltage | 1 V |
| Maximum switching voltage | 23 V DC ($U_B - U_{resid.}$ of the output) |
| Max. switching current | 500 mA |
| Protective circuit | Parallel protection against polarity reversal, pay attention to the fuse (Fusing with max. 8 A F-fuse) |

Connection data

Supply

| | |
|----------------------------------|---|
| Connection method | Push-in connection |
| Stripping length | 10 mm |
| Conductor cross-section rigid | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section flexible | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section AWG | 24 ... 12 |

Input

| | |
|-------------------|--------------------|
| Connection method | Push-in connection |
| Stripping length | 10 mm |

EM-CAN-GATEWAY-IFS - Data interface



2901504

<https://www.phoenixcontact.com/us/products/2901504>

| | |
|----------------------------------|---|
| Conductor cross-section rigid | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section flexible | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section AWG | 24 ... 12 |

Output

| | |
|----------------------------------|---|
| Connection method | Push-in connection |
| Stripping length | 10 mm |
| Conductor cross-section rigid | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section flexible | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section AWG | 24 ... 12 |

Programming connection

| | |
|-----------------------|-----------------|
| Connection method | S-PORT (socket) |
| Number of connections | 1 |
| Number of positions | 12 |

INTERFACE system

| | |
|-----------------------|------------------------|
| Connection method | DIN rail bus connector |
| Number of connections | 1 |
| Number of positions | 5 |

CANopen®

| | |
|----------------------------------|---|
| Connection method | Push-in connection |
| Stripping length | 10 mm |
| Number of connections | 1 |
| Number of positions | 4 |
| Conductor cross-section rigid | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section flexible | 0.2 mm ² ... 2.5 mm ² |

Interfaces

Data: Network interface

| | |
|--------------------------|--------------------|
| Communication protocol | CANopen® |
| Connection method | Screw connection |
| Number of connections | 1 |
| Number of positions | 4 |
| Transmission speed range | 10 kbps ... 1 Mbps |

Data: Service interface

| | |
|------------------------|------------------|
| Communication protocol | Interface-System |
| Connection method | S-PORT (socket) |
| Number of connections | 1 |
| Number of positions | 12 |

Data: Device bus

| | |
|------------------------|------------------------|
| Communication protocol | Interface-System |
| Connection method | DIN rail bus connector |

2901504

<https://www.phoenixcontact.com/us/products/2901504>

| | |
|-----------------------|-----------|
| Number of connections | 1 |
| Number of positions | 5 |
| Transmission speed | 76.8 kbps |

Dimensions

| | |
|--------|----------|
| Width | 22.5 mm |
| Height | 107.8 mm |
| Depth | 113.8 mm |

Material specifications

| | |
|------------------|-----------------------------|
| Color | gray (RAL 7042) |
| Housing material | Polyamide PA non-reinforced |

Environmental and real-life conditions

Ambient conditions

| | |
|---|------------------|
| Degree of protection | IP20 |
| Ambient temperature (operation) | -25 °C ... 50 °C |
| Ambient temperature (storage/transport) | -35 °C ... 80 °C |

Standards and regulations

| | |
|-----------------------|--------------|
| Standards/regulations | EN 61000-6-2 |
| | EN 61000-6-4 |

Mounting

| | |
|-------------------|---------------------------|
| Mounting type | DIN rail mounting |
| Assembly note | in rows with zero spacing |
| Mounting position | any |


EM-CAN-GATEWAY-IFS - Data interface




2901504

<https://www.phoenixcontact.com/us/products/2901504>

Drawings



Block diagram



EM-CAN-GATEWAY-IFS - Data interface



2901504

<https://www.phoenixcontact.com/us/products/2901504>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2901504>



EAC

Approval ID: RU C-DE.A*30.B.01082



UL Listed

Approval ID: E140324



cUL Listed

Approval ID: E140324

2901504

<https://www.phoenixcontact.com/us/products/2901504>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27242608 |
| ECLASS-15.0 | 27242608 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001604 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 32151600 |
|-------------|----------|

2901504

<https://www.phoenixcontact.com/us/products/2901504>

Environmental product compliance

EU RoHS

| | |
|---|--------------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 7(a), 7(c)-I |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|--|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| | 2,2',6,6'-tetrabromo-4,4'-isopropylidenediphenol(CAS: 79-94-7) |
| SCIP | 1fc3a01b-fd0b-4fd1-822e-746b2dc6d7d7 |

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com