


# FOC-KDHEAVY-1011/IP20/... - FO patch cable



2901553

<https://www.phoenixcontact.com/us/products/2901553>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



POF installation cable for assembly (IP20 heads only) for installation in stationary systems and machines with individual elements made of polyamide (PA), halogen-free, ozone and UV resistant, with a polyurethane (PUR) outer sheath

## Your advantages

- Universal installation cable for installation in stationary systems and machines
- For indoors
- Rugged polyurethane (PUR) outer sheath
- 2.2 mm individual wires made from extremely hard-wearing polyamide (PA)
- Halogen-free, ozone, and UV resistant

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 2901553                        |
| Packing unit                         | 1 pc                           |
| Minimum order quantity               | 1 pc                           |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | DN35                           |
| Product key                          | DNC241                         |
| Weight per piece (including packing) | 100 g                          |
| Weight per piece (excluding packing) | 100 g                          |
| Customs tariff number                | 85447000                       |
| Country of origin                    | CZ                             |

# FOC-KDHEAVY-1011/IP20/... - FO patch cable



2901553

<https://www.phoenixcontact.com/us/products/2901553>

## Technical data

### Product properties

|                     |                         |
|---------------------|-------------------------|
| Product type        | Data cable preassembled |
| Application         | Standard                |
| Number of positions | 2                       |

### Interfaces

|        |          |
|--------|----------|
| Signal | Modbus   |
|        | PROFIBUS |

### Electrical properties

|                    |          |
|--------------------|----------|
| Transmission speed | 100 Mbps |
|--------------------|----------|

### Cable/line

|   |                             |
|---|-----------------------------|
| Cable length                            | Free input (0.4 ... 100 m)  |
| Cable weight                            | 33 kg/km                    |
| Outer sheath, material                  | PUR                         |
| External sheath, strain relief elements | Non-metallic, aramide fiber |
| Single wire, material                   | PA                          |
| Individual wire diameter                | 2.2 mm ±0.07 mm             |
| Tensile strength short-term/long-term   | 600 N / 100 N               |
| Lateral pressure short term             | 200 N/cm                    |
| Lateral pressure, long-term             | 20 N/cm                     |
| Impact strength                         | 2 Nm / 10 x                 |
| Bending radius, single element          | 30 mm (Short-term)          |
|   | 30 mm (Short-term)          |
| Bending radius, entire cable            | 30 mm (Short-term)          |
|   | 30 mm (Short-term)          |
| 660 nm                                  | 230 dB/km                   |
| Halogen-free                            | According to IEC 60754-2    |

### Environmental and real-life conditions

#### Ambient conditions

|          |        |
|----------|--------|
| Altitude | 5000 m |
|----------|--------|

# FOC-KDHEAVY-1011/IP20/... - FO patch cable



2901553

<https://www.phoenixcontact.com/us/products/2901553>

## Classifications

### ECLASS

ECLASS-13.0

27061803

### UNSPSC

UNSPSC 21.0

26121600

# FOC-KDHEAVY-1011/IP20/... - FO patch cable



2901553

<https://www.phoenixcontact.com/us/products/2901553>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)