

YOKOGAWA FCN-RTU-12VDC FUSED - Interface module



2901762

<https://www.phoenixcontact.com/us/products/2901762>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Commercial data

Item number	2901762
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	C429
Product key	DK2BZZ
GTIN	4046356955782
Weight per piece (including packing)	99.99 g
Weight per piece (excluding packing)	99.99 g
Customs tariff number	85369080
Country of origin	US

YOKOGAWA FCN-RTU-12VDC FUSED - Interface module



2901762

<https://www.phoenixcontact.com/us/products/2901762>

Technical data

Product properties

Product type	Interface module
--------------	------------------

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

Utilization restriction

EMC note	EMC: class A product, see manufacturer's declaration in the download area
----------	---

YOKOGAWA FCN-RTU-12VDC FUSED - Interface module



2901762

<https://www.phoenixcontact.com/us/products/2901762>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-50 An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
--	--

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com