

BC 17-REL/1/MSTB/R3,3K/R680 - Relay module



2901881

<https://www.phoenixcontact.com/us/products/2901881>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Relay module, standard interface for fire alarm systems, with miniature relay securely soldered in, 1 N/O contact, input voltage: 24 V AC

Commercial data

Item number	2901881
Packing unit	10 pc
Minimum order quantity	30 pc
Product key	DK617Y
GTIN	4046356638593
Weight per piece (including packing)	200 g
Weight per piece (excluding packing)	200 g
Country of origin	DE

Technical data

Notes

Utilization restriction

EMC note	EMC: class A product, see manufacturer's declaration in the download area
----------	---

Product properties

Product type	Relay Module
--------------	--------------

Insulation characteristics: Air clearances and creepage distances, input/output

Insulation	Basic insulation
Overvoltage category	III
Pollution degree	2

Data management status

Date of last data management	12.09.2025
------------------------------	------------

Electrical properties

Air clearances and creepage distances, input/output

Rated insulation voltage	250 V
Rated surge voltage	4 kV (1.2/50 μ s)

Input data

Coil side

Nominal input voltage U_N	24 V AC
Input voltage range in reference to U_N	0.8 ... 1.1
Typical input current at U_N	10 mA
Protective circuit	Bridge rectifier; Bridge rectifier, varistor Capacitor; Capacitor
Operating voltage display	LED

Output data

Switching

Contact switching type	1 N/O contact
Contact material	AgSnO ₂ , gold-plated
Note	A 660 Ω resistor is connected in series and a 3.3 k Ω resistor is connected in parallel with the output
Maximum switching voltage	30 V AC
Limiting continuous current	max. 3 A

Connection data

Input

BC 17-REL/1/MSTB/R3,3K/R680 - Relay module



2901881

<https://www.phoenixcontact.com/us/products/2901881>

Connection method	Screw connection
Conductor cross-section rigid	0.14 mm ² ... 2.5 mm ²
Conductor cross-section flexible	0.14 mm ² ... 2.5 mm ²
Conductor cross-section AWG	26 ... 14

Output

Connection method	Screw connection
Conductor cross-section rigid	0.14 mm ² ... 2.5 mm ²
Conductor cross-section flexible	0.14 mm ² ... 2.5 mm ²
Conductor cross-section AWG	26 ... 14

Dimensions

Width	17.8 mm
Height	90 mm
Depth	61 mm

Material specifications

Color	gray (RAL 7042)
-------	-----------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Degree of protection (Installation location)	≥ IP54 (Installation location)
Ambient temperature (operation)	-20 °C ... 50 °C

Standards and regulations

Air clearances and creepage distances, input/output

Standards/regulations	EN 50178
-----------------------	----------

Mounting

Mounting type	DIN rail mounting
Assembly note	in rows with zero spacing
Mounting position	any

2901881

<https://www.phoenixcontact.com/us/products/2901881>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com