

FLT-CP-3S-BE - Base element



2880914

<https://www.phoenixcontact.com/us/products/2880914>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Base element for type 1+2 special combined lightning current and surge arrester from the FLASHTRAB compact product series. Version for 3-phase power supplies with separate cable routing of N and PE.

Commercial data

Item number	2880914
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	CL1211
GTIN	4046356049160
Weight per piece (including packing)	778.9 g
Weight per piece (excluding packing)	594.53 g
Country of origin	DE

Technical data

Product properties

Product type	Base element
IEC test classification	I + II T1 + T2
Surge protection fault message	Remote indication contact
Number of ports	One

Insulation characteristics

Overvoltage category	III
Pollution degree	2

Electrical properties

Nominal frequency f_N	50 Hz (60 Hz)
Nominal voltage U_N	240 V AC

Indicator/remote signaling

Connection name	Remote fault indicator contact
Switching function	Changeover contact
Operating voltage	12 V AC ... 250 V AC 125 V DC (200 mA DC)
Operating current	10 mA AC ... 1 A AC 1 A DC (30 V DC)

Connection data

Connection method	Screw terminal blocks
Screw thread	M5
Tightening torque	4.5 Nm
Stripping length	18 mm
Conductor cross-section flexible	2.5 mm ² ... 25 mm ²
Conductor cross-section rigid	2.5 mm ² ... 35 mm ²
Conductor cross-section AWG	13 ... 2

Remote fault indicator contact

Connection method	Plug-in/screw connection via COMBICON
Screw thread	M2
Tightening torque	0.25 Nm
Stripping length	7 mm
Conductor cross-section flexible	0.14 mm ² ... 1.5 mm ²
Conductor cross-section rigid	0.14 mm ² ... 1.5 mm ²
Conductor cross-section AWG	28 ... 16

Material specifications

Flammability rating according to UL 94	V - 0
--	-------

FLT-CP-3S-BE - Base element



2880914

<https://www.phoenixcontact.com/us/products/2880914>

CTI value of material	600
Insulating material	PBT
Material group	I
Housing material	PBT

Protective circuit

Direction of action	3L-N/PE
Nominal frequency f_N	50 Hz (60 Hz)
Maximum continuous operating voltage U_C (L-N)	350 V AC
Maximum continuous operating voltage U_C (N-PE)	350 V AC
Rated load current I_L	125 A (< 55 °C)
Short-circuit current rating I_{SCCR}	25 kA
Max. backup fuse with V-type through wiring	125 A (gG)
Max. backup fuse with branch wiring	315 A (gG)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20 (only when all terminal points are used)
Ambient temperature (operation)	-40 °C ... -80 °C
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Altitude	≤ 2000 m (asml)
Permissible humidity (operation)	5 % ... 95 %
Shock (operation)	25g
Vibration (operation)	5g (10 Hz ... 500 Hz)

Approvals

UL specifications

Maximum continuous operating voltage MCOV (L-N)	264 V AC
Maximum continuous operating voltage MCOV (N-G)	264 V AC
Nominal frequency	50/60 Hz

UL indicator/remote signaling

Operating voltage	125 V AC
AC operating current	1.5 A AC

UL connection data

Tightening torque	40 lb _F in.
Conductor cross-section AWG	12 ... 2

Standards and regulations

Standards/specifications	IEC 61643-11
Note	2011
Standards/specifications	EN 61643-11
Note	2012

FLT-CP-3S-BE - Base element



2880914

<https://www.phoenixcontact.com/us/products/2880914>

Mounting

Mounting type

DIN rail: 35 mm

FLT-CP-3S-BE - Base element



2880914

<https://www.phoenixcontact.com/us/products/2880914>

Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com