

# IL MII BK DI8 DO4-PAC - Bus coupler



2884619

<https://www.phoenixcontact.com/us/products/2884619>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Inline, Bus coupler, Mechatrolink, USB type A, socket, Digital inputs: 8, 24 V DC, connection technology: 3-conductor, Digital outputs: 4, 24 V DC, 500 mA, connection technology: 3-conductor, transmission speed in the local bus: 500 kbps, degree of protection: IP20, including Inline connectors and marking fields

## Product description

The bus coupler for the Mechatrolink protocol has 4 digital outputs and 8 digital inputs. This package contains all the necessary Inline connectors for connecting the supply and the I/Os.

The Inline terminals can be labeled using pull-out labeling fields. The fields have insert cards that can be labeled individually to suit the application. Additionally, there is the ZBFM-6... Zack marker strip for labeling the terminal points.

## Your advantages

- Data transmission speed: 10 Mbps (MII) and 4 Mbps (MI)
- Supports high-speed I/O scanner
- Slave address, baud rate, and Mechatrolink data width can be set via DIP switches
- Mechatrolink network connection
- Meets Mechatrolink II intelligent I/O specification

## Commercial data

Item number	2884619
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	DR01
Product key	DRI116
GTIN	4046356137836
Weight per piece (including packing)	335.13 g
Weight per piece (excluding packing)	335.13 g
Customs tariff number	85389091
Country of origin	DE

# IL MII BK DI8 DO4-PAC - Bus coupler




2884619

<https://www.phoenixcontact.com/us/products/2884619>

## Technical data

### Dimensions

Dimensional drawing	
Width	80 mm
Height	119.8 mm
Depth	71.5 mm
Note on dimensions	Specifications with connectors

### Material specifications

Color	green
-------	-------

### Interfaces

#### Mechatrolink

No. of channels	2
Connection method	USB type A, socket
Transmission speed	max. 10 Mbps

#### Inline local bus

Connection method	Inline data jumper
Transmission speed	500 kbps

#### Fieldbus: Local bus gateway

Max. number of local bus devices	61 (The on-board I/Os are two devices)
----------------------------------	--

### System properties

#### System limits

Number of supported devices	max. 63 (per station)
Number of local bus devices that can be connected	max. 61 (The on-board I/Os are two devices)
Number of devices with parameter channel	max. 16
Number of supported branch terminals with remote bus branch	0

#### Programming data

Register length (bus)	16 bit
Register length (master)	510 Byte

### Input data

Digital:

# IL MII BK DI8 DO4-PAC - Bus coupler



2884619

<https://www.phoenixcontact.com/us/products/2884619>

Input name	Digital inputs
Description of the input	EN 61131-2 type 1
Number of inputs	8
Connection method	Inline connector
Connection technology	3-conductor
Input voltage	24 V DC
Input voltage range "0" signal	-30 V DC ... 5 V DC
Input voltage range "1" signal	15 V DC ... 30 V DC
Nominal input voltage $U_{IN}$	24 V DC
Nominal input current at $U_{IN}$	typ. 3 mA
Current flow	Limited to 3 mA, maximum
Typical input current per channel	typ. 3 mA
Typical response time	approx. 500 $\mu$ s
Delay at signal change from 0 to 1	1.2 ms
Delay at signal change from 1 to 0	1.2 ms
Protective circuit	Reverse polarity protection; Suppressor diode

## Output data

Digital:

Output name	Digital outputs
Connection method	Inline connector
Connection technology	3-conductor
Number of outputs	4
Protective circuit	Short-circuit and overload protection; Freewheeling circuit in the output driver
Output voltage	24 V DC -1 V (At nominal current)
Max. current carrying capacity per output	max. 500 mA
Maximum output current per module	max. 2 A
Nominal output voltage	24 V DC
Output current when switched off	max. 10 $\mu$ A (When not loaded, a voltage can be measured even at an output that is not set.)
Nominal load, inductive	12 VA (1.2 H, 48 $\Omega$ )
Nominal load, lamp	12 W
Nominal load, ohmic	12 W
Reverse voltage resistance to short pulses	Reverse voltage proof
Behavior with overload	Auto restart
Behavior with inductive overload	Output can be destroyed
Behavior at voltage switch-off	The output follows the power supply without delay
Signal delay	typ. 1.2 ms
Overcurrent shut-down	min. 0.7 A

## Product properties

Product type	I/O component
Product family	Inline

# IL MII BK DI8 DO4-PAC - Bus coupler



2884619

<https://www.phoenixcontact.com/us/products/2884619>

Type	modular
	Inline
Scope of supply	including Inline connectors and marking fields
No. of channels	12
Diagnostics messages	Short-circuit or overload of the digital outputs yes
	Sensor supply failure yes
	Failure of the actuator supply yes

## Electrical properties

Potentials: Bus coupler supply  $U_{BK}$ ; Communications power  $U_L$  (7.5 V) and the analog supply  $U_{ANA}$  (24 V) are generated from the bus coupler supply.

Supply voltage	24 V DC (via Inline connector)
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)
Current draw	max. 0.9 A

Potentials: Communications power ( $U_L$ )

Supply voltage	7.5 V DC
Power supply	max. 0.8 A DC

Potentials: Supply of analog modules ( $U_{ANA}$ )

Supply voltage	24 V DC
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)
Power supply	max. 0.5 A DC

Potentials: Main circuit supply ( $U_M$ )

Supply voltage	24 V DC (via Inline connector)
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)
Power supply	max. 8 A DC (sum of $U_M + U_S$ )
Current draw	max. 8 A DC

Potentials: Segment circuit supply ( $U_S$ )

Supply voltage	24 V DC (via Inline connector)
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)
Power supply	max. 8 A DC (sum of $U_M + U_S$ )
Current draw	max. 8 A DC

## Connection data

Connection technology

Connection name	Inline connector
-----------------	------------------

Inline connector

Connection method	Spring-cage connection
Conductor cross-section, rigid	0.08 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section, flexible	0.08 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section AWG	28 ... 16
Stripping length	8 mm

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	0 °C ... 55 °C
Degree of protection	IP20
Air pressure (operation)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Air pressure (storage/transport)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Ambient temperature (storage/transport)	-25 °C ... 85 °C
Permissible humidity (operation)	10 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	10 % ... 95 % (according to DIN EN 61131-2)

### Mechanical test

Vibration resistance in accordance with EN 60068-2-6/IEC 60068-2-6	5g
Shock in accordance with EN 60068-2-27/IEC 60068-2-27	Operation: 25g, 11 ms duration, semi-sinusoidal shock impulse

## Standards and regulations

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

## Mounting

Mounting type	DIN rail mounting
---------------	-------------------

# IL MII BK DI8 DO4-PAC - Bus coupler




2884619

<https://www.phoenixcontact.com/us/products/2884619>

## Drawings

Dimensional drawing




# IL MII BK DI8 DO4-PAC - Bus coupler


2884619

<https://www.phoenixcontact.com/us/products/2884619>

Dimensional drawing



Connection diagram



# IL MII BK DI8 DO4-PAC - Bus coupler

2884619

<https://www.phoenixcontact.com/us/products/2884619>



## Classifications

### UNSPSC

UNSPSC 21.0	32151602
-------------	----------

# IL MII BK DI8 DO4-PAC - Bus coupler



2884619

<https://www.phoenixcontact.com/us/products/2884619>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)