

RAD-ISM-2400-ANT-OMNI-5-0 - Antenna



2884923

<https://www.phoenixcontact.com/us/products/2884923>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Omnidirectional antenna, 2.4 GHz, gain: 5 dBi, polarization: linear, opening angle: h/v 360°/45°, degree of protection: IP55, connection: SMA (male)

Your advantages

- For freely mobile applications
- For multipoint or mesh connections

Commercial data

Item number	2884923
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	DN23
Product key	DNN2Z1
GTIN	4046356173131
Weight per piece (including packing)	39 g
Weight per piece (excluding packing)	38.6 g
Customs tariff number	85177000
Country of origin	TW

Technical data

Product properties

Product type	Antenna
Gain	5 dBi
Vertical beamwidth	45 °
Horizontal beamwidth	360 °
Polarization	Linear vertical

Electrical properties

Frequency band	2.4 GHz
Frequency range	2.4 GHz
Impedance	50 Ω
Voltage standing wave ratio VSWR in a 50 Ω system	≤ 2.00

Connection data

Connection technology

Connection method	SMA (male)
-------------------	------------

Dimensions

Width	13 mm
Height	187 mm

Material specifications

Material	Polyurethane
----------	--------------

Cable/line

Connecting cable	no
------------------	----

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP55
Ambient temperature (operation)	-20 °C ... 65 °C
Ambient temperature (storage/transport)	-20 °C ... 65 °C

Mounting

Mounting type	Panel mounting
	Mast mounting

RAD-ISM-2400-ANT-OMNI-5-0 - Antenna


2884923

<https://www.phoenixcontact.com/us/products/2884923>



Drawings

Schematic diagram



Installation example

RAD-ISM-2400-ANT-OMNI-5-0 - Antenna



2884923

<https://www.phoenixcontact.com/us/products/2884923>

Classifications

UNSPSC

UNSPSC 21.0	43223100
-------------	----------

2884923

<https://www.phoenixcontact.com/us/products/2884923>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-25
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com