

RAD-CON-MCX-RPSMA-EX - Antenna cable



2885621

<https://www.phoenixcontact.com/us/products/2885621>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Antenna barrier, installation: Class I, Div. 1, Grps. A, B, C, D; Class II, Div. 1, Grps. F, G, frequency range: 0.3G Hz ... 6 GHz, connection: RSMA (male) -> MCX (male), incl. 0.7 m / 2.3 ft. connection cable, UL HazLoc approval

Your advantages

- Universal use (frequency range of 0.3 ... 6 GHz)
- Use of standard antennas in the hazardous area of zone 0, 1, and 2

Commercial data

Item number	2885621
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	DN23
Product key	DNC6A3
GTIN	4046356149495
Weight per piece (including packing)	199.6 g
Weight per piece (excluding packing)	199.6 g
Customs tariff number	85442000
Country of origin	US

RAD-CON-MCX-RPSMA-EX - Antenna cable



2885621

<https://www.phoenixcontact.com/us/products/2885621>

Technical data

Product properties

Product type	Adapter cable
Screw connection	3/4" NPT

Electrical properties

Frequency range	0.3 GHz ... 6 GHz
Impedance	50 Ω
Maximum error voltage U_m	250 V DC
Maximum HF output power P	2 W
Maximum capacity	5.64 nF

Connection data

Connection method	MCX (male)
Connection method	RSMA (male)

Material specifications

Outer material connection	Stainless steel
---------------------------	-----------------

Cable/line

Cable length	0.76 m
--------------	--------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP66
Ambient temperature (operation)	-40 °C ... 75 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C

Approvals

Conformity/Approvals

UL, USA / Canada	Class I, Div. 1, 2, Groups A, B, C, D Class II, Div. 1, 2, Groups F, G
------------------	---


RAD-CON-MCX-RPSMA-EX - Antenna cable

2885621


<https://www.phoenixcontact.com/us/products/2885621>

Drawings

Dimensional drawing



Application drawing



RAD-CON-MCX-RPSMA-EX - Antenna cable



2885621

<https://www.phoenixcontact.com/us/products/2885621>

Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com