

# RAD-80211-XD - Access point



2885728

<https://www.phoenixcontact.com/us/products/2885728>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



WLAN access point, 24 V DC; IEEE 802.11 a/b/g; 2.4 GHz; 5 GHz, client adapter, bridge; antenna diversity; Wi-Fi compliant; web-based management; 802.11i, DIN rail mounting, without antenna

## Commercial data

Item number	2885728
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	DN23
Product key	DNN2W2
GTIN	4046356155199
Weight per piece (including packing)	300 g
Weight per piece (excluding packing)	300 g
Customs tariff number	85176200
Country of origin	CA

# RAD-80211-XD - Access point



2885728

<https://www.phoenixcontact.com/us/products/2885728>

## Technical data

### Product properties

Product type	Wireless module
--------------	-----------------

### Electrical properties

Supply: Module electronics

Connection method	Via COMBICON
Supply voltage	24 V DC
Supply voltage range	12 V DC ... 30 V DC
Supply current	500 mA

### Interfaces

Ethernet

Number	1
Connection method	RJ45 jack

Antenna

Number	1
--------	---

Functions

Operating modes	Access point, client, bridge
Configuration	Web-based management
Automatic channel selection	yes
Security	WEP 64 bit/128 bit WPA TKIP 802.11i WPA2 (AES)
Wireless licenses	USA, Canada
Connection method	D-SUB-9, COMBICON
Protocols supported	RS-232, RS-485, RS-422

Wireless

Antenna connection method	MCX (female)
Frequency band	2.4 GHz 5 GHz
Wireless standard	IEEE 802.11 a b g h
Transmission power	20 dBm (EIRP)
Number of wireless interfaces	1 IEEE 802.11 a/b/g

### Dimensions

# RAD-80211-XD - Access point



2885728

<https://www.phoenixcontact.com/us/products/2885728>

Width	45 mm
Height	99 mm
Depth	115 mm

## Material specifications

Color	green
-------	-------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	0 °C ... 65 °C
Air pressure (operation)	795 hPa ... 1080 hPa (up to 2000 m above sea level)
Permissible humidity (operation)	5 % ... 90 % (non-condensing)

## Approvals

### Conformity/Approvals

UL, USA / Canada	Class I, Div. 2, Groups A, B, C, D
------------------	------------------------------------

## Mounting

Mounting type	DIN rail mounting
Assembly note	Antenna not included

# RAD-80211-XD - Access point



2885728

<https://www.phoenixcontact.com/us/products/2885728>

## Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	
-------------------------------------	--

	No substance above 0.1 wt%
--	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)