

# FL SWITCH SFNT 5TX - Industrial Ethernet Switch



2891003

<https://www.phoenixcontact.com/us/products/2891003>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Wide-temperature Ethernet switch, 5 TP RJ45 ports, automatic detection of data transmission speed of 10/100 Mbps (RJ45), autocrossing function, reads QoS priority messages, accepts security frames

One port is located on the bottom

## Your advantages

- Wide operating temperature range of -40 °C ... 75 °C
- QoS-prioritized (Quality of Service) messages
- RJ45 ports support a transmission speed of 10/100 Mbps
- Fiber-optic ports support 100 Mbps
- Local diagnostic indicators with LEDs
- Alarm contact for power supply and link status diagnostics
- The switch also offers cable locking and port blocking
- Auto negotiation and autocrossing detection simplifies installation and setup

## Commercial data

Item number	2891003
Packing unit	1 pc
Sales key	DN19
Product key	DNN113
GTIN	4046356457187
Weight per piece (including packing)	491 g
Weight per piece (excluding packing)	275 g
Customs tariff number	85176200
Country of origin	TW

# FL SWITCH SFNT 5TX - Industrial Ethernet Switch



2891003

<https://www.phoenixcontact.com/us/products/2891003>

## Technical data

### Dimensions

Width	30 mm
Height	130 mm
Depth	100 mm

### Notes

#### Utilization restriction

CCCex note	Use in potentially explosive areas is not permitted in China.
------------	---

### Material specifications

Housing material	Aluminum
------------------	----------

### Mounting

Mounting type	DIN rail mounting
---------------	-------------------

### Interfaces

#### Ethernet (RJ45)

Connection method	RJ45
Note on the connection method	Auto negotiation and autocrossing
Transmission speed	10/100 Mbps
Transmission physics	Ethernet in RJ45 twisted pair
No. of channels	5 (RJ45 ports)

### Product properties

Product type	Switch
Product family	Unmanaged Switch SFNT
Type	Block design
MTTF	134.2 Years (MIL-HDBK-217F standard, temperature 25°C, operating cycle 100%)

#### Switch functions

Basic functions	Unmanaged switch / autonegotiation, complies with IEEE 802.3, store and forward switching mode, includes QoS and alarm contact
Status and diagnostic indicators	LEDs: U <sub>S1</sub> , U <sub>S2</sub> (redundant voltage supply), link and activity per port
Additional functions	Autonegotiation

#### Security functions

Basic functions	Unmanaged switch / autonegotiation, complies with IEEE 802.3, store and forward switching mode, includes QoS and alarm contact
-----------------	--

### Electrical properties

# FL SWITCH SFNT 5TX - Industrial Ethernet Switch



2891003

<https://www.phoenixcontact.com/us/products/2891003>

Local diagnostics	US Supply voltage Green LED
	LNK/ACT Link status/data transmission Green LED
	100 Data transmission speed Yellow LED
Maximum power dissipation for nominal condition	3 W
Transmission medium	Copper

## Supply

Supply voltage (DC)	24 V DC (redundant)
Supply voltage range	9 V DC ... 32 V DC
Power supply connection	Via COMBICON, max. conductor cross-section 2.5 mm <sup>2</sup>
Residual ripple	3.6 V <sub>PP</sub> (within the permitted voltage range)
Max. current consumption	345 mA (@9 V DC)
Typical current consumption	125 mA (at U <sub>S</sub> = 24 V DC)

## Connection data

Connection method	Screw connection
Conductor cross-section, rigid	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section, flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 14
Stripping length	7 mm

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 75 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	5 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 95 % (non-condensing)
Air pressure (operation)	62 kPa ... 108 kPa (up to 4160 m above mean sea level)
Air pressure (storage/transport)	62 kPa ... 108 kPa (up to 4160 m above mean sea level)

## Approvals

### Conformity/Approvals

Conformance	CE-compliant
ATEX	Ⓜ II 3 G Ex nA nC IIC T4 Gc
EU-type examination certificate	DEMKO 16 ATEX 1617X
IECEX	Ex nA nC IIC T4 Gc
IECEX certificate	IECEX UL 16.0093X
UL, USA / Canada	Class I, Div. 2, Groups A, B, C, D

## EMC data

Electromagnetic compatibility	Conformance with EMC Directive 2004/108/EC
Noise immunity	EN 61000-6-2

# FL SWITCH SFNT 5TX - Industrial Ethernet Switch



2891003

<https://www.phoenixcontact.com/us/products/2891003>

## Noise emission

Standards/regulations

EN 61000-6-4

## System properties

### Functionality

Basic functions

Unmanaged switch / autonegotiation, complies with IEEE 802.3, store and forward switching mode, includes QoS and alarm contact

## Signaling

Status display

LEDs: U<sub>S1</sub>, U<sub>S2</sub> (redundant voltage supply), link and activity per port

# FL SWITCH SFNT 5TX - Industrial Ethernet Switch



2891003

<https://www.phoenixcontact.com/us/products/2891003>

## Classifications

### UNSPSC

UNSPSC 21.0	43222600
-------------	----------

2891003

<https://www.phoenixcontact.com/us/products/2891003>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-10
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)