

# EEM-MA600-24DC - Measuring device



2902352

<https://www.phoenixcontact.com/us/products/2902352>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Energy measurement device to measure electrical parameters in low voltage installations up to 700 V, acquisition of individual harmonic oscillations - can be extended with communication and special functional modules

## Commercial data

Item number	2902352
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	C446
Product key	CMMC11
GTIN	4046356657136
Weight per piece (including packing)	813.1 g
Weight per piece (excluding packing)	813.1 g
Customs tariff number	90303100
Country of origin	TN

# EEM-MA600-24DC - Measuring device



2902352

<https://www.phoenixcontact.com/us/products/2902352>

## Technical data

### Product properties

Product type	Energy measuring device
--------------	-------------------------

### Electrical properties

Electrical isolation	EN 61010-1 (Safe isolation)
	See extension module
	See extension module
Test voltage	3.5 kV AC (50 Hz, 1 min.)
Mains type	3-phase (3 or 4-conductor), 2-phase (2-conductor), and single-phase (1-conductor)

### Electrical isolation

Overvoltage category	III (For mains voltage <300 V AC (L/N))
	II (for mains voltage >300 V AC ... 600 V AC (L/N))
Pollution degree	2

### Supply

Supply voltage	24 V DC
Supply voltage range	12 V DC ... 48 V DC -6 % ... +20 %
Nominal power consumption	10 VA
Power consumption	20 VA (with max. number of extension modules)

### Input data

#### Measuring data acquisition

Measuring principle	True r.m.s. value measurement
Measured value	AC sine (50 Hz/60 Hz)
Acquisition of harmonics	up to 63rd harmonic

#### Measurement: Voltage

Input name	Voltage measuring input V1, V2, V3
Input voltage	500 kV AC (Primary (via external voltage transducers))
	Secondary: 60, 100, 110, 115, 120, 173, 190 V AC
Input voltage range	18 V AC ... 700 V AC (Phase/Phase)
	11 V AC ... 404 V AC (Phase/neutral conductor)
Precision	0.2 %

#### Measurement: Current

Input name	Current measuring input I1, I2, I3
Input current range	via external transformers
Input current	9999 A (primary)
	1 A and 5 A, secondary
Measuring range	0 A ... 9999 A
Overload capacity	6 A (Permanent)

# EEM-MA600-24DC - Measuring device



2902352

<https://www.phoenixcontact.com/us/products/2902352>

Response threshold from measuring range nominal value	10 mA
Precision	0.2 %
Current overload	10 x I <sub>N</sub> for 1 s

## Measurement: Power

Messbereich_Leistung	0 MW ... 8000 MW
	0 Mvar ... 8000 Mvar
	0 MVA ... 8000 MVA
Precision	0.5 %
Active energy (IEC 62053-22)	Class 0.5 S
Reactive power (IEC 62053-23)	Class 2

## Digital

Voltage input signal	Via extension module
----------------------	----------------------

## Output data

Output description	via extension module
--------------------	----------------------

## Connection data

Connection method	COMBICON plug-in screw terminal block
Stripping length	6 mm
Note	Voltage and other connections
Conductor cross-section rigid	0.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section flexible	0.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section AWG	20 ... 14
Tightening torque	0.4 Nm ... 0.4 Nm
Connection method	Screw connection
Stripping length	7 mm
Note	Current connection
Conductor cross-section rigid	0.5 mm <sup>2</sup> ... 6 mm <sup>2</sup>
Conductor cross-section flexible	0.5 mm <sup>2</sup> ... 6 mm <sup>2</sup>
Conductor cross-section AWG	20 ... 8

## Dimensions

Width	96 mm
Height	96 mm
Depth	82 mm
	80 mm (Installation depth with extension module)
	60 mm (Installation depth without extension module)

## Material specifications

Color	black (RAL 9005)
-------	------------------

## Environmental and real-life conditions

### Ambient conditions

# EEM-MA600-24DC - Measuring device



2902352

<https://www.phoenixcontact.com/us/products/2902352>

Degree of protection	(Front) IP30 (Back side)
Ambient temperature (operation)	-10 °C ... 55 °C (14 °F ... 131 °F)
Ambient temperature (storage/transport)	-20 °C ... 85 °C (-4 °F ... 185 °F)
Max. permissible relative humidity (operation)	≤ 95 %
Max. salt spray content	≤ 2.5 %

## Approvals

### CE

Certificate	CE-compliant
-------------	--------------

### UL data

Nominal supply voltage range	12 V DC ... 48 V DC -6 % ... +20 %
Power consumption	10 VA
Altitude	≤ 2000 m
Operating mode	Indoor use
Surge voltages	transient overvoltage according to installation classes
Overvoltage category	I, II, III
Overvoltage category of the supply	Min. II
Ambient temperature (operation)	0 °C ... 40 °C
Max. permissible relative humidity (operation)	80 % (up to 31 °C) 50 % (at 40 °C)

### UL data

Nominal supply voltage range	12 V DC ... 48 V DC -6 % ... +20 %
Power consumption	10 VA
Altitude	≤ 2000 m
Operating mode	Indoor use
Ambient temperature (operation)	0 °C ... 40 °C
Max. permissible relative humidity (operation)	80 % (up to 31 °C) 50 % (at 40 °C)
Surge voltages	transient overvoltage according to installation classes
Overvoltage category	I, II, III
Overvoltage category of the supply	Min. II

## Mounting

Mounting position	Front panel installation, horizontal
-------------------	--------------------------------------

# EEM-MA600-24DC - Measuring device



2902352

<https://www.phoenixcontact.com/us/products/2902352>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)