

RAD-ISM-900-SET-XD-BUS-2 - Wireless set



2902756

<https://www.phoenixcontact.com/us/products/2902756>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Bidirectional, 900 MHz transmission system for the Americas, consists of three transceivers and one I/O module operating as a master and two slaves

Commercial data

Item number	2902756
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	DN26
Product key	DNC651
GTIN	4046356694193
Weight per piece (including packing)	839 g
Weight per piece (excluding packing)	839 g
Customs tariff number	85176200
Country of origin	CA

RAD-ISM-900-SET-XD-BUS-2 - Wireless set

2902756

<https://www.phoenixcontact.com/us/products/2902756>

Set consists of

RAD-ISM-900-XD-BUS - Wireless module

2885605

<https://www.phoenixcontact.com/us/products/2885605>



Transceiver (transmitter and receiver) for expanding multipoint to point connections for 900 MHz bidirectional wireless transmission system (American version)

RAD-IN+OUT-2D-1A-I - Extension module

2867322

<https://www.phoenixcontact.com/us/products/2867322>



Analog /digital module for 2 digital inputs/outputs and 1 analog input/output

Technical data

Product properties

Product type	Wireless module
--------------	-----------------

Electrical properties

Supply

Supply voltage	24 V DC
Supply voltage range	9 V DC ... 30 V DC
Typical current consumption	75 mA
Max. current consumption	24 mA

Input data

Digital

Input voltage range	5 V AC/DC ... 30 V AC/DC
Switching threshold "0" signal, voltage	max. 1.5 V DC
Switching threshold "1" signal voltage	min. 5 V DC

Analog

Description of the input	Current input (analog input)
Current input signal	4 mA ... 20 mA
Input resistance current input	< 170 Ω

Analog

Description of the input	Voltage input (digital input)
--------------------------	-------------------------------

Output data

Digital

Output name	2x relay output + 1 x RF link
Number of outputs	3
Contact switching type	3 floating N/O contacts
Contact material	Ag, gold-plated
Maximum switching voltage	30 V DC
	250 V AC
Limiting continuous current	2 A

Analog

Output name	Current output
Number of outputs	1
Load/output load current output	700 Ω (at $U_B = 24\text{ V}$, $R_B = [U_B - 10\text{ V}] / 20\text{ mA}$)

Connection data

Connection method	Screw connection
Stripping length	8 mm

RAD-ISM-900-SET-XD-BUS-2 - Wireless set



2902756

<https://www.phoenixcontact.com/us/products/2902756>

Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Cross section AWG	24 ... 14
Screw thread	M3

Interfaces

Wireless

Direction	Bi-directional
Frequency	900 MHz
Frequency range	902 MHz ... 928 MHz
Channel distance	22 kHz
Number of channel groups	4
Number of channels per group	63
Transmission power	1 W

Wireless

Frequency band	900 MHz
----------------	---------

Dimensions

Width	22.5 mm
Height	99 mm
Depth	114.5 mm

Material specifications

Color	green
Housing material	Polyamide PA non-reinforced

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C

Approvals

Conformity/Approvals

Conformance	FCC Directive, Part 15.247
	ISC Directive RSS 210

Mounting

Assembly note	DIN rail NS 35
Mounting position	any

2902756

<https://www.phoenixcontact.com/us/products/2902756>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com