

FL SWITCH 4824E-4GC - Industrial Ethernet Switch



2891072

<https://www.phoenixcontact.com/us/products/2891072>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Rack-mount managed Ethernet switch meets IEC 61850-3 and IEEE 1613. Provides 24 RJ45 ports at 10/100 Mbps and four gigabit combo ports (10/100/1000 Mbps RJ45 connection; 1000 Mbps fiber optic connection requires 1000 Mbps SFP module)



Product description

Developed according to IEC 61850-3 (Ambient conditions)

Your advantages

- Network structure according to IEC 61850
- IEEE 1613

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2891072 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | DN17 |
| Product key | DNN125 |
| GTIN | 4046356764360 |
| Weight per piece (including packing) | 5,037 g |
| Weight per piece (excluding packing) | 3,601 g |
| Customs tariff number | 85176200 |
| Country of origin | TW |

FL SWITCH 4824E-4GC - Industrial Ethernet Switch



2891072

<https://www.phoenixcontact.com/us/products/2891072>

Technical data

Dimensions

| | |
|--------|--------|
| Width | 442 mm |
| Height | 44 mm |
| Depth | 375 mm |

Notes

Note on application

| | |
|---------------------|-------------------------|
| Note on application | Only for industrial use |
|---------------------|-------------------------|

Material specifications

| | |
|-----------------|------------------|
| Color (Housing) | black (RAL 9005) |
|-----------------|------------------|

Mounting

| | |
|---------------|-----------------------------|
| Mounting type | Rack mounting (with holder) |
| Holder system | 19" rack |

Interfaces

Ethernet (RJ45)

| | |
|-------------------------------|-----------------------------------|
| Connection method | RJ45 |
| Note on the connection method | Auto negotiation and autocrossing |
| Transmission speed | 10/100 Mbps |
| Transmission physics | Ethernet in RJ45 twisted pair |
| Transmission length | 100 m |
| No. of channels | 24 (RJ45 ports) |

Ethernet (RJ45/FO combo)

| | |
|-------------------------------|---|
| Connection method | SFP/RJ45 |
| Note on the connection method | Auto negotiation and autocrossing (RJ45 interface) |
| Transmission speed | 10/100/1000 Mbps |
| Transmission physics | Ethernet RJ45 (10/100/1000 Mbps) or SFP (1000 Mbps) |
| No. of channels | 4 (Combo ports) |

Product properties

| | |
|----------------|--|
| Product type | Switch |
| Product family | Managed Switch 4000 |
| Type | Block design |
| MTTF | 17.2 Years (MIL-HDBK-217F standard, temperature 25°C, operating cycle 100%) |
| | 278 Years (SN 29500 standard, temperature 25°C, operating cycle 21%) |
| | 269.5 Years (Telcordia standard, 25°C temperature, 21% operating cycle (5 days a week, 8 hours a day)) |

Switch functions

| | |
|----------------------------------|--|
| Basic functions | Store and forward switch, Extended Ring and IEEE redundancy, Multicast control, IGMP snooping, trunking, Port and Tagging VLANs, Port and IEEE 802.1x security, SNMP V3 and Https security, SNTP, web customization, user accounts |
| Redundancy | ERR (Extended ring redundancy) |
| Status and diagnostic indicators | LEDs: U _{S1} , U _{S2} (redundant voltage supply), link and activity per port |

Security functions

| | |
|-----------------|--|
| Basic functions | Store and forward switch, Extended Ring and IEEE redundancy, Multicast control, IGMP snooping, trunking, Port and Tagging VLANs, Port and IEEE 802.1x security, SNMP V3 and Https security, SNTP, web customization, user accounts |
|-----------------|--|

Electrical properties

| | |
|---------------------|---|
| Current consumption | 359 mA (115 V AC from FL SWITCH 4800E-P5) |
| Transmission medium | Copper FO |

Supply

| | |
|-------------------------|---|
| Supply voltage | Based on modular power supplies used |
| Power supply connection | From FL SWITCH 4800E-P... |
| Inrush current | 18.8 A (48 V DC from FL SWITCH 4800E-P1) 20.7 A (115 V AC from FL SWITCH 4800E-P5) |
| Current consumption | 359 mA (115 V AC from FL SWITCH 4800E-P5) |

Environmental and real-life conditions

Ambient conditions

| | |
|--|--|
| Degree of protection | IP20 |
| Ambient temperature (operation) | -40 °C ... 70 °C |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C |
| Permissible humidity (operation) | 5 % ... 95 % (non-condensing) |
| Permissible humidity (storage/transport) | 5 % ... 95 % (non-condensing) |
| Air pressure (operation) | 57 kPa ... 108 kPa (up to 4850 m above mean sea level) |
| Air pressure (storage/transport) | 57 kPa ... 108 kPa (up to 4850 m above mean sea level) |

Standards and regulations

| | |
|--------------------------|--------------------|
| Standard designation | Ambient conditions |
| Standards/specifications | IEC 61850-3 |

EMC data

| | |
|----------------|--|
| Noise immunity | IEC 61850-3, IEEE 1613, EN 61000-6-2: 2005 |
|----------------|--|

Noise emission

| | |
|-----------------------|--------------|
| Standards/regulations | EN 61000-6-4 |
|-----------------------|--------------|

2891072

<https://www.phoenixcontact.com/us/products/2891072>

System properties

Functionality

Basic functions

Store and forward switch, Extended Ring and IEEE redundancy, Multicast control, IGMP snooping, trunking, Port and Tagging VLANs, Port and IEEE 802.1x security, SNMP V3 and Https security, SNTP, web customization, user accounts

Signaling

Status display

LEDs: U_{S1}, U_{S2} (redundant voltage supply), link and activity per port

FL SWITCH 4824E-4GC - Industrial Ethernet Switch



2891072

<https://www.phoenixcontact.com/us/products/2891072>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 19170401 |
| ECLASS-15.0 | 19170401 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000734 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 43222600 |
|-------------|----------|

2891072

<https://www.phoenixcontact.com/us/products/2891072>

Environmental product compliance

EU RoHS

| | |
|---|---------------------------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 15(a), 6(c), 7(a), 7(c)-I |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-10 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | 01bc8e3a-2db8-4dbb-87ac-e7ac142e491b |

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com