

# PSR-SPP- 24DC/RSM4/4X1-KOC - Safety relay module



2903243

<https://www.phoenixcontact.com/us/products/2903243>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



2-channel over-speed and zero-speed safety relay up to SIL 3 or Cat. 4, PL e in accordance with EN ISO 13849, 4 N/O contacts, suitable for connecting initiators, width: 45 mm, plug-in Push-in terminal block

The figure shows version PSR-SCP-24DC/RSM4/4X1

## Commercial data

Item number	2903243
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	DNA242
GTIN	4046356728782
Weight per piece (including packing)	361.3 g
Weight per piece (excluding packing)	361.3 g
Customs tariff number	90328900
Country of origin	DE

# PSR-SPP- 24DC/RSM4/4X1-KOC - Safety relay module



2903243

<https://www.phoenixcontact.com/us/products/2903243>

## Technical data

### Notes

#### Utilization restriction

EMC note	EMC: class A product, see manufacturer's declaration in the download area
----------	---

### Product properties

Product type	Safety device
Application	Over-speed safety relay
	Zero-speed safety relay
Control	2-channel
Mechanical service life	> 50x 10 <sup>6</sup> cycles
Relay type	Electromechanical relay with force-guided contacts in accordance with IEC/EN 61810-3

#### Insulation characteristics: Air clearances and creepage distances between the power circuits

Overvoltage category	III
Degree of pollution	2

### Electrical properties

Maximum power dissipation for nominal condition	2.4 W
Nominal operating mode	100% operating factor
Interfaces	Encoder
	Initiator connection

#### Air clearances and creepage distances between the power circuits

Rated insulation voltage	250 V
Rated surge voltage/insulation	4 kV / Basic isolation, (safe isolation, reinforced insulation and 6 kV between input circuit and enabling current paths.)

### Input data

#### General

Nominal input voltage $U_N$	24 V DC
Input voltage range in reference to $U_N$	0.85 ... 1.1
Typical input current at $U_N$	100 mA
Voltage at input/start and feedback circuit	24 V DC
Typical response time	15 ms
Typical release time	12 ms
Recovery time	1 s
Limit frequency	1 kHz (IN1, IN2)
	400 kHz (RJ45)
Status display	LED (green)

# PSR-SPP- 24DC/RSM4/4X1-KOC - Safety relay module



2903243

<https://www.phoenixcontact.com/us/products/2903243>

## Output data

Contact switching type	4 enabling current paths
Contact material	AgNi10, + 5 µm Au
Maximum switching voltage	250 V AC/DC (when the gold layer is destroyed) 60 V AC/DC (with gold layer existing)
Minimum switching voltage	100 mV AC/DC
Limiting continuous current	5 A 100 mA (alarm outputs)
Maximum inrush current	6 A
Inrush current, minimum	1 mA
Sq. Total current	$42.25 \text{ A}^2 (I_{TH}^2 = I_1^2 + I_2^2 + I_3^2 + I_4^2)$
Interrupting rating (ohmic load) max.	67 W (24 V DC, $\tau = 0 \text{ ms}$ ) 36 W (48 V DC, $\tau = 0 \text{ ms}$ ) 43 MW (110 V DC, $\tau = 0 \text{ ms}$ ) 68 MW (220 V DC, $\tau = 0 \text{ ms}$ )
Switching power min.	1 mW
Switching capacity (3600/h cycles)	2 A (24 V (DC13)) 3 A (230 V (AC15))
Output fuse	6 A gL

## Connection data

### Connection technology

pluggable	yes
-----------	-----

### Conductor connection

Connection method	Push-in connection
Conductor cross-section, rigid	0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section, flexible	0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 16
Stripping length	8 mm

## Dimensions

Width	45 mm
Height	112 mm
Depth	114.5 mm

## Material specifications

Color	yellow
-------	--------

## Characteristics

### Safety data

Stop category (EN 60204-1)	0
----------------------------	---

Safety data: EN ISO 13849

# PSR-SPP- 24DC/RSM4/4X1-KOC - Safety relay module



2903243

<https://www.phoenixcontact.com/us/products/2903243>

Performance level (PL)	e
Safety data: IEC 61508 - High demand	
Safety Integrity Level (SIL)	3
Safety data: IEC 61508 - Low demand	
Safety Integrity Level (SIL)	3
Safety data	
Safety Integrity Level (SIL)	3

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
Min. degree of protection of inst. location	IP54
Ambient temperature (operation)	-20 °C ... 55 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Maximum altitude	≤ 2000 m (Above sea level)

## Standards and regulations

### Air clearances and creepage distances between the power circuits

Standards/regulations	EN 60664/VDE 0110
-----------------------	-------------------

## Mounting

Mounting type	DIN rail mounting
Assembly note	in rows with zero spacing
Mounting position	any

# PSR-SPP- 24DC/RSM4/4X1-KOC - Safety relay module



2903243

<https://www.phoenixcontact.com/us/products/2903243>

## Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	
-------------------------------------	--

	No substance above 0.1 wt%
--	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)