

# FL MC 2000T ST - FO converters



2891316

<https://www.phoenixcontact.com/us/products/2891316>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



FO converter with ST fiber optic connection (1300 nm), for converting 100Base-TX to multi-mode fiberglass. Auto MDI(X) function and comprehensive link diagnostics. DIN rail mountable with wide operating temperature range.

## Product description

The FL MC 2000T media converter comes with one 10/100 Mbps twisted-pair RJ45 port and one 100 Mbps multimode fiber optics port with an ST connector



## Commercial data

Item number	2891316
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN06
Product key	DNC312
GTIN	4046356869584
Weight per piece (including packing)	310.3 g
Weight per piece (excluding packing)	304.8 g
Customs tariff number	85176200
Country of origin	TW

## Technical data

### Notes

#### Note on application

Note on application	Only for industrial use
---------------------	-------------------------

### Product properties

Product type	Media converter
MTTF	77.82 Years (MIL-HDBK-217F standard, temperature 25°C, operating cycle 100%)
Signal delay	865 ns (Pass-through mode)
	835 ns (Auto converter mode, 100 Mbps, static)

### Electrical properties

Electrical isolation	VCC // FE // Ethernet
Test voltage data interface/power supply	1500 V AC (500 V AC, 1 minute)

#### Supply

Supply voltage range	12 V DC ... 48 V DC
Nominal supply voltage	24 V DC
Typical current consumption	110 mA (24 V DC)

### Output data

#### Switching

Output name	Relay output
Output description	Alarm output
Number of outputs	1
Contact switching type	N/C contact
Maximum switching voltage	24 V DC
Max. switching current	100 mA

### Connection data

#### Supply

Connection method	Plug-in screw terminal block (COMBICON), redundancy possible
-------------------	--

### Interfaces

Signal	Ethernet
--------	----------

#### Data: optical FO

Transmit capacity, minimum	-19 dBm
Transmit capacity, maximum	-14 dBm
Transmission length incl. 3 dB system reserve	8 km (fiberglass with F-G 62.5/125 0.7 dB/km F1000)
	3.3 km (fiberglass with F-G 62.5/125 2.6 dB/km F600)
	9.6 km (fiberglass with F-G 50/125 0.7 dB/km F1200)

# FL MC 2000T ST - FO converters



2891316

<https://www.phoenixcontact.com/us/products/2891316>

	5.3 km (fiberglass with F-G 50/125 1.6 dB/km F800)
Connection method	B-FOC (ST®)
Wavelength	1310 nm
Minimum receiver sensitivity	-32 dBm
Maximum receiver sensitivity	-14 dBm
Transmission medium	Multi-mode fiberglass GI-HCS fiber

Data: Ethernet interface, 10/100Base-T(X) in accordance with IEEE 802.3

Data rate	10/100 Mbps
Serial transmission speed	10/100 Mbps
Connection method	RJ45 jack, shielded
No. of channels	1
Transmission length	100 m (twisted pair, shielded)
Transmission medium	Copper
Signal LEDs	LNK/ACT, 100
Auto-negotiation modes	Auto
Link through	Link fault pass through
MDI-/MDI-X switchover	Auto-MDI(X)

## Dimensions

Width	28 mm
Height	110 mm
Depth	70 mm

## Material specifications

Housing material	Aluminum
------------------	----------

## Mechanical tests

Vibration resistance in accordance with EN 60068-2-6/IEC 60068-2-6	: 5g, 150 Hz, Criterion 3
Shock in accordance with EN 60068-2-27/IEC 60068-2-27	: 30g, 11 ms half-sine shock pulse

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 75 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Altitude	4850 m
Permissible humidity (operation)	5 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 95 % (non-condensing)
Shock	300 m/s <sup>2</sup> , 11 ms (IEC 60068-2)
Air pressure (operation)	86 kPa ... 108 kPa
Air pressure (storage/transport)	66 kPa ... 108 kPa

# FL MC 2000T ST - FO converters



2891316

<https://www.phoenixcontact.com/us/products/2891316>

## Approvals

### Conformity/Approvals

Conformance	CE-compliant
UL, USA / Canada	Class I, Div. 2, Groups A, B, C, D

## EMC data

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
-------------------------------	---

### Electrostatic discharge

Standards/regulations	EN 61000-4-2
-----------------------	--------------

### Electrostatic discharge

Comments	Criterion B
----------	-------------

### Electromagnetic HF field

Standards/regulations	EN 61000-4-3
-----------------------	--------------

### Electromagnetic HF field

Comments	Criterion A
----------	-------------

### Fast transients (burst)

Standards/regulations	EN 61000-4-4
-----------------------	--------------

### Fast transients (burst)

Comments	Criterion A
----------	-------------

### Surge current load (surge)

Standards/regulations	EN 61000-4-5
-----------------------	--------------

### Surge current load (surge)

Comments	Criterion B
----------	-------------

### Conducted interference

Standards/regulations	EN 61000-4-6
-----------------------	--------------

### Conducted interference

Comments	Criterion A
----------	-------------

### Emitted interference

Standards/regulations	EN 55032
-----------------------	----------

## Mounting

Mounting type	DIN rail mounting
Mounting position	on horizontal DIN rail NS 35 in acc. with EN 60715

# FL MC 2000T ST - FO converters



2891316

<https://www.phoenixcontact.com/us/products/2891316>

## Classifications

### ECLASS

ECLASS-13.0	19170411
ECLASS-15.0	19170411

### ETIM

ETIM 10.0	EC001467
-----------	----------

### UNSPSC

UNSPSC 21.0	43201500
-------------	----------

# FL MC 2000T ST - FO converters



2891316

<https://www.phoenixcontact.com/us/products/2891316>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-10
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)