

FL SWITCH SFN 4TX/FX ST - Industrial Ethernet Switch



2891453

<https://www.phoenixcontact.com/us/products/2891453>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ethernet switch, 4 TP RJ45 ports, 1 FO port, 100 Mbps full duplex in ST-D format, automatic detection of data transmission speed of 10 or 100 Mbps (RJ45), autocrossing function

Your advantages

- RJ45 ports support a transmission speed of 10/100 Mbps
- Fiber-optic ports support 100 Mbps
- QoS-prioritized (Quality of Service) messages
- Local diagnostic indicators with LEDs
- The switch also offers cable locking and port blocking
- Auto negotiation and autocrossing detection simplifies installation and setup

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2891453 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | DN19 |
| Product key | DNN113 |
| GTIN | 4046356100816 |
| Weight per piece (including packing) | 417.1 g |
| Weight per piece (excluding packing) | 265 g |
| Customs tariff number | 85176200 |
| Country of origin | TW |

FL SWITCH SFN 4TX/FX ST - Industrial Ethernet Switch



2891453

<https://www.phoenixcontact.com/us/products/2891453>

Technical data

Dimensions

| | |
|--------|--------|
| Width | 30 mm |
| Height | 131 mm |
| Depth | 70 mm |

Notes

Note on application

| | |
|---------------------|-------------------------|
| Note on application | Only for industrial use |
|---------------------|-------------------------|

Material specifications

| | |
|------------------|----------|
| Housing material | Aluminum |
|------------------|----------|

Mounting

| | |
|---------------|-------------------|
| Mounting type | DIN rail mounting |
|---------------|-------------------|

Interfaces

Ethernet (RJ45)

| | |
|-------------------------------|-----------------------------------|
| Connection method | RJ45 |
| Note on the connection method | Auto negotiation and autocrossing |
| Transmission speed | 10/100 Mbps |
| Transmission physics | Ethernet in RJ45 twisted pair |
| Transmission length | 100 m (per segment) |
| Signal LEDs | Data receive, link status |
| No. of channels | 4 (RJ45 ports) |

Fiber optic interface

| | |
|----------------------|--|
| Connection method | ST |
| Transmission speed | 100 Mbps (full duplex) |
| Transmission physics | multi-mode fiberglass |
| Transmission length | 2000 m (Fiberglass 50/125) 2000 m (Fiberglass 62.5/125) |
| Wavelength | 1300 nm |
| No. of channels | 1 (ST multi-mode) |

Product properties

| | |
|----------------|--|
| Product type | Switch |
| Product family | Unmanaged Switch SFN |
| Type | Block design |
| MTTF | 193 Years (MIL-HDBK-217F standard, temperature 25°C, operating cycle 100%) |

Insulation characteristics

FL SWITCH SFN 4TX/FX ST - Industrial Ethernet Switch



2891453

<https://www.phoenixcontact.com/us/products/2891453>

| | |
|----------------------------------|---|
| Protection class | III (IEC 61140, EN 61140, VDE 0140-1) |
| Switch functions | |
| Basic functions | Unmanaged switch / auto negotiation, complies with IEEE 802.3, store and forward switching mode |
| Status and diagnostic indicators | LEDs: U _S , link and activity per port |
| Additional functions | Autonegotiation |
| Security functions | |
| Basic functions | Unmanaged switch / auto negotiation, complies with IEEE 802.3, store and forward switching mode |

Electrical properties

| | |
|---|---|
| Local diagnostics | US Supply voltage Green LED |
| | LNK/ACT Link status/data transmission Green LED |
| | 100 Data transmission speed Yellow LED |
| Maximum power dissipation for nominal condition | 3.36 W |
| Test section | 500 V DC 1 min |
| Transmission medium | Copper |
| | FO |

Supply

| | |
|-----------------------------|--|
| Supply voltage (DC) | 24 V DC |
| Supply voltage range | 9 V DC ... 32 V DC |
| Residual ripple | 3.6 V _{pp} (within the permitted voltage range) |
| Typical current consumption | 140 mA (at U _S = 24 V DC) |

Connection data

Power supply

| | |
|-----------------------------------|---|
| Connection method | Screw connection |
| pluggable | yes |
| Conductor cross-section, rigid | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section, flexible | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section AWG | 24 ... 12 |
| Stripping length | 7 mm |

Environmental and real-life conditions

Ambient conditions

| | |
|--|---|
| Degree of protection | IP20 |
| Ambient temperature (operation) | 0 °C ... 60 °C |
| Ambient temperature (storage/transport) | -20 °C ... 70 °C |
| Permissible humidity (operation) | 5 % ... 95 % (non-condensing) |
| Permissible humidity (storage/transport) | 5 % ... 95 % (non-condensing) |
| Vibration (operation) | in acc. with IEC 60068-2-6: 5g, 150 Hz |
| Air pressure (operation) | 86 kPa ... 108 kPa (up to 1500 m above sea level) |

FL SWITCH SFN 4TX/FX ST - Industrial Ethernet Switch



2891453

<https://www.phoenixcontact.com/us/products/2891453>

| | |
|--|---|
| Air pressure (storage/transport) | 66 kPa ... 108 kPa (up to 3500 m above sea level) |
| Resistance to gases that may endanger the functions, in acc. with DIN 40046-36, DIN 40046-37 | Sulfur dioxide (SO ₂) 10 ±0.3 cm ³ /m ³ , hydrogen sulfide (H ₂ S) 1 ±0.3 cm ³ /m ³ , at 25°C and 75% humidity and exposure of four days |

EMC data

| | |
|-------------------------------|--|
| Electromagnetic compatibility | Conformance with EMC Directive 2004/108/EC |
| Noise immunity | EN 61000-6-2:2005 |

Noise emission

| | |
|-----------------------|--------------|
| Standards/regulations | EN 61000-6-4 |
|-----------------------|--------------|

System properties

Functionality

| | |
|-----------------|---|
| Basic functions | Unmanaged switch / auto negotiation, complies with IEEE 802.3, store and forward switching mode |
|-----------------|---|

Signaling

| | |
|----------------|---|
| Status display | LEDs: U _S , link and activity per port |
|----------------|---|

FL SWITCH SFN 4TX/FX ST - Industrial Ethernet Switch



2891453

<https://www.phoenixcontact.com/us/products/2891453>

Classifications

ECLASS

ECLASS-13.0

19170402

ETIM

ETIM 9.0

EC000734

UNSPSC

UNSPSC 21.0

43222600

FL SWITCH SFN 4TX/FX ST - Industrial Ethernet Switch



2891453

<https://www.phoenixcontact.com/us/products/2891453>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 6(c), 7(a), 7(c)-I |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-10 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|----------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
|-------------------------------------|----------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com