

FL SWITCH SFNT 14TX/2FX - Industrial Ethernet Switch



2891954

<https://www.phoenixcontact.com/us/products/2891954>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Wide temperature Ethernet switch, 14 TP RJ45 ports, automatic detection of data transmission speed of 10 or 100 Mbps (RJ45), autocrossing function. Two FO ports in SC format.

Product description

Standard function Ethernet switch with 14 RJ45 ports and 2 SC-D fiber optic ports for extreme environments (-40°C ... +75°C). Provides automatic detection of data transmission speed of 10 or 100 Mbps (RJ45), autocrossing function, 12 V DC ... 48 V DC input voltage, redundant power supply capable with remote alarming.

Your advantages

- RJ45 ports support a transmission speed of 10/100 Mbps
- Fiber-optic ports support 100 Mbps
- 16 ports in a narrow metal housing with redundant input voltage
- Security options with cable locking
- Local diagnostic indicators with LEDs
- Devices are available for the standard temperature range (0 °C ... 60 °C) and wide temperature range (-40 °C ... 75 °C)
- Auto negotiation and autocrossing detection simplifies installation and setup

Commercial data

Item number	2891954
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	DN19
Product key	DNN113
GTIN	4046356551632
Weight per piece (including packing)	1,191.2 g
Weight per piece (excluding packing)	1,175.2 g
Customs tariff number	85176200
Country of origin	TW

FL SWITCH SFNT 14TX/2FX - Industrial Ethernet Switch



2891954

<https://www.phoenixcontact.com/us/products/2891954>

Technical data

Dimensions

Width	70 mm
Height	135 mm
Depth	110 mm

Notes

Utilization restriction

CCCex note	Use in potentially explosive areas is not permitted in China.
------------	---

Material specifications

Housing material	Aluminum
------------------	----------

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

Interfaces

Ethernet (RJ45)

Connection method	RJ45
Note on the connection method	Auto negotiation and autocrossing
Transmission speed	10/100 Mbps
Transmission physics	Ethernet in RJ45 twisted pair
Transmission length	100 m (per segment)
Signal LEDs	Data receive, link status
No. of channels	14 (RJ45 ports)

Fiber optic interface

Connection method	SC
Transmission speed	100 Mbps (full duplex)
Transmission physics	multi-mode fiberglass
Transmission length	12.1 km (fiberglass with F-G 62.5/125 0.7 dB/km F1000) 7.1 km (fiberglass with F-G 50/125 0.7 dB/km F1200)
Wavelength	1300 nm
No. of channels	2 (SC multi-mode)

Product properties

Product type	Switch
Product family	Unmanaged Switch SFNT
Type	Block design
MTTF	39.8 Years (MIL-HDBK-217F standard, temperature 25°C, operating cycle 100%)

Insulation characteristics

FL SWITCH SFNT 14TX/2FX - Industrial Ethernet Switch



2891954

<https://www.phoenixcontact.com/us/products/2891954>

Protection class	III (VDE 0106, IEC 60536)
Switch functions	
Basic functions	Unmanaged switch / auto negotiation, complies with IEEE 802.3, store-and-forward switching mode, includes alarm contacts
Status and diagnostic indicators	LEDs: U _{S1} , U _{S2} (redundant voltage supply), link and activity per port
Additional functions	Autonegotiation
Security functions	
Basic functions	Unmanaged switch / auto negotiation, complies with IEEE 802.3, store-and-forward switching mode, includes alarm contacts

Electrical properties

Local diagnostics	US Supply voltage Green LED
	LNK/ACT Link status/data transmission Green LED
	100 Data transmission speed Yellow LED
Maximum power dissipation for nominal condition	8.4 W
Test section	500 V DC 1 min
Transmission medium	Copper
	FO

Supply

Supply voltage (DC)	24 V DC (redundant)
Supply voltage range	12 V DC ... 48 V DC
Power supply connection	Via COMBICON, max. conductor cross-section 2.5 mm ²
Residual ripple	3.6 V _{PP} (within the permitted voltage range)
Max. current consumption	700 mA (at 12 V DC)
Typical current consumption	350 mA (at U _S = 24 V DC)

Connection data

Connection method	Screw connection
Conductor cross-section, rigid	0.2 mm ² ... 2.5 mm ²
Conductor cross-section, flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	30 ... 12
Stripping length	7 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 75 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	5 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 95 % (non-condensing)
Shock	25g, in accordance with IEC 60068-2-27
Vibration (operation)	in acc. with IEC 60068-2-6: 5g, 150 Hz

FL SWITCH SFNT 14TX/2FX - Industrial Ethernet Switch



2891954

<https://www.phoenixcontact.com/us/products/2891954>

Air pressure (operation)	62 kPa ... 108 kPa (up to 4160 m above mean sea level)
Air pressure (storage/transport)	62 kPa ... 108 kPa (up to 4160 m above mean sea level)

Approvals

Conformity/Approvals

Conformance	CE-compliant
ATEX	Ⓜ II 3 G Ex nA nC IIC T4 Gc
EU-type examination certificate	DEMKO 16 ATEX 1617X
IECEX	Ex nA nC IIC T4 Gc
IECEX certificate	IECEX UL 16.0093X
UL, USA / Canada	Class I, Div. 2, Groups A, B, C, D

EMC data

Electromagnetic compatibility	Conformance with EMC Directive 2004/108/EC
Conformance with EMC directives	IEC 61000-6-2
Noise immunity	EN 61000-6-2

Noise emission

Standards/regulations	EN 61000-6-4
-----------------------	--------------

System properties

Functionality

Basic functions	Unmanaged switch / auto negotiation, complies with IEEE 802.3, store-and-forward switching mode, includes alarm contacts
-----------------	--

Signaling

Status display	LEDs: U _{S1} , U _{S2} (redundant voltage supply), link and activity per port
----------------	--

FL SWITCH SFNT 14TX/2FX - Industrial Ethernet Switch



2891954

<https://www.phoenixcontact.com/us/products/2891954>

Classifications

UNSPSC

UNSPSC 21.0	43222600
-------------	----------

FL SWITCH SFNT 14TX/2FX - Industrial Ethernet Switch



2891954

<https://www.phoenixcontact.com/us/products/2891954>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	15(a), 6(c), 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-10
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	667acaa9-3e2b-41b8-9919-7bde9f0b2cdd

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com