

ST-REL7-HW 24/4X21 - Relay connectors



2892562

<https://www.phoenixcontact.com/us/products/2892562>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Relay connector, equipped with Hengstler miniature round relay, contacts (AgCdO+Au): small to large loads, 4 changeover contacts, input voltage 24 V AC, with LED display, pluggable into basic terminal blocks

The figure shows version ST-REL 7-HG 24/4X21

Commercial data

Item number	2892562
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	DK6126
GTIN	4017918078744
Weight per piece (including packing)	105.81 g
Weight per piece (excluding packing)	92.98 g
Customs tariff number	85364190
Country of origin	DE

ST-REL7-HW 24/4X21 - Relay connectors



2892562

<https://www.phoenixcontact.com/us/products/2892562>

Technical data

Product properties

Product type	Relay Module
Operating mode	100% operating factor
Mechanical service life	approx. 10^7 cycles

Insulation characteristics

Overvoltage category	II
Pollution degree	2

Data management status

Date of last data management	12.09.2025
------------------------------	------------

Electrical properties

Test voltage (Winding/contact)	2 kV AC (50 Hz, 1 min., winding/contact)
Test voltage (Changeover contact/changeover contact)	2 kV AC (50 Hz, 1 min., changeover contact/changeover contact)

Input data

Coil side

Nominal input voltage U_N	24 V AC
Input voltage range	19.2 V AC ... 26.4 V AC
Input voltage range in reference to U_N	0.8 ... 1.1
Typical input current at U_N	72 mA
Typical response time	4 ms ... 15 ms (with AC)
Typical release time range	4 ms ... 15 ms (with AC)
Operating voltage display	yes

Output data

Switching

Contact switching type	Single contact, 4 changeover contacts
Type of switch contact	Single contact
Contact material	AgCdO, hard gold-plated
Maximum switching voltage	250 V AC/DC
Limiting continuous current	6 A
Maximum inrush current	6 A
Interrupting rating (ohmic load) max.	120 W (at 24 V DC) 180 W (at 48 V DC) 105 W (at 60 V DC) 60 W (at 110 V DC) 90 W (at 220 V DC) 1250 VA (for 250 V AC)

Dimensions

ST-REL7-HW 24/4X21 - Relay connectors



2892562

<https://www.phoenixcontact.com/us/products/2892562>

Width	45.6 mm
Height	33 mm
Depth	66.5 mm

Material specifications

Color	green (RAL 6021)
-------	------------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 60 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

Standards and regulations


Standards/regulations	IEC 60664
	IEC 60664A
	DIN VDE 0110
	DIN VDE 0109-11, draft
	DIN VDE 0160 (in relevant parts)

Mounting

Mounting type	Plug-in mounting
---------------	------------------

Drawings

Circuit diagram



ST-REL7-HW 24/4X21 - Relay connectors



2892562

<https://www.phoenixcontact.com/us/products/2892562>

Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	
-------------------------------------	--

	No substance above 0.1 wt%
--	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com