

BC 17,6 BS U22 KMGY - Filler plug



2896199

<https://www.phoenixcontact.com/us/products/2896199>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail housing for use in distribution boards in accordance with DIN 43880, Filler plug for unoccupied terminal points (U22), width: 17.6 mm, height: 29.78 mm, depth: 22.35 mm, color: light gray (similar RAL 7035)

Your advantages

- Easy, tool-free mounting
- Flammability rating V0 in accordance with UL 94

Commercial data

Item number	2896199
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	AC10
Product key	ACHBAZ
GTIN	4046356096591
Weight per piece (including packing)	3.74 g
Weight per piece (excluding packing)	3.219 g
Customs tariff number	84879090
Country of origin	DE

BC 17,6 BS U22 KMGY - Filler plug



2896199

<https://www.phoenixcontact.com/us/products/2896199>

Technical data

Notes

Assembly note	Please observe the application note in the download area.
---------------	---

Product properties

Product type	Filler plug
Housing type	DIN rail housing for use in distribution boards in accordance with DIN 43880
Housing type	Modular building installation housings
Housing series	BC
Product family	BC 17,8..
Ventilation openings present	no

Dimensions

Width	17.6 mm
Height	29.78 mm
Depth	22.35 mm
Horizontal pitch	1 Div.

Material specifications

Color (Filler plug)	light gray (RAL 7035)
Material Filler plug	PC
Flammability rating according to UL 94	V0

Environmental and real-life conditions

Vibration test

Specification	IEC 60068-2-6:2007-12
Frequency	10 - 150 - 10 Hz
Sweep speed	1 octave/min
Amplitude	0.15 mm (10 Hz ... 58.1 Hz)
Acceleration	2g (58.1 Hz ... 150 Hz)
Test duration per axis	2.5 h
Test directions	X-, Y- and Z-axis

Glow-wire test

Specification	IEC 60695-2-11:2014-02
Temperature	850 °C
Time of exposure	30 s

Mechanical strength / tumbling barrel

Specification	IEC 60068-2-31:2008-05
Height of fall	50 cm
Frequency	50

BC 17,6 BS U22 KMGY - Filler plug



2896199

<https://www.phoenixcontact.com/us/products/2896199>

Shocks

Specification	IEC 60068-2-27:2008-02
Pulse shape	Half-sine
Acceleration	15g
Shock duration	11 ms
Number of shocks per direction	3
Test directions	X-, Y- and Z-axis (pos. and neg.)

Degree of protection (IP code)

Specification	IEC 60529:1989-11 + AMD 1:1999-11 + AMD 2:2013-08
---------------	---

Ambient conditions

Max. IP code to attain	IP20
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	95 %

Mounting

Mounting type	Latching with upper housing part
---------------	----------------------------------

BC 17,6 BS U22 KMGY - Filler plug



2896199

<https://www.phoenixcontact.com/us/products/2896199>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2896199>



UL Recognized

Approval ID: E240868

BC 17,6 BS U22 KMGY - Filler plug



2896199

<https://www.phoenixcontact.com/us/products/2896199>

Classifications

ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

ETIM

ETIM 10.0	EC002779
-----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

BC 17,6 BS U22 KMGY - Filler plug



2896199

<https://www.phoenixcontact.com/us/products/2896199>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.023 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com