

CABLE-FCN40/1X50/ 8,0M/IM/MEL - Cable



2903474

<https://www.phoenixcontact.com/us/products/2903474>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Round cable set; controller: Mitsubishi Electric MELSEC L, MELSEC Q, Honeywell MasterLogic ML200; connection 1: Fujitsu connector (1x 40-position); connection 2: IDC/FLK socket strip (1x 50-position); cable length: 8 m

Commercial data

Item number	2903474
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	C421
Product key	DK226M
GTIN	4046356742887
Weight per piece (including packing)	1,134.7 g
Weight per piece (excluding packing)	333.33 g
Customs tariff number	85444290
Country of origin	DE

CABLE-FCN40/1X50/ 8,0M/IM/MEL - Cable



2903474

<https://www.phoenixcontact.com/us/products/2903474>

Technical data

Product properties

Product type	System cable
--------------	--------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP00
Degree of protection (Installation location)	≥ IP54 (Installation location)
Ambient temperature (operation) (fixed installation)	-40 °C ... 70 °C (fixed installation)
Ambient temperature (operation) (flexible installation)	-10 °C ... 70 °C (flexible installation)
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Altitude	≤ 2000 m

Electrical properties

Operating voltage (AC)	≤ 30 V AC
Operating voltage (DC)	≤ 60 V DC
Nominal operating mode	100% operating factor
Current (Per path, 50°C)	≤ 1 A (Uncoiled, see derating)
Current (Per path, 70°C)	≤ 0.6 A (Uncoiled, see derating)

Supported controller: MITSUBISHI MELSEC Q

Suitable I/O card	QX41
	QX41-S1
	QX42
	QX42-S1
	QX71
	QX72
	QY41P
	QY42P
	QY71
	QH42P
	QY82P

Supported controller: MITSUBISHI MELSEC L

Suitable I/O card	LX41C4
	LX42C4
	LY41NT1P
	LY42NT1P
	LY41PT1P
	LY42PT1P

Supported controller: HONEYWELL MasterLogic 200

2MLQ-TR4A

CABLE-FCN40/1X50/ 8,0M/IM/MEL - Cable



2903474

<https://www.phoenixcontact.com/us/products/2903474>

Suitable I/O card	2MLQ-TR8A
	2MLQ-TR4B
	2MLQ-TR8B

Cable/line

Cable length	8 m
--------------	-----

40X0.14 [PVC]

UL AWM Style	2464/1061
Number of positions	40
Shielded	no
Cable type	40X0.14 [PVC]
Conductor type	Round cable set
Conductor structure signal line	7x 0.16 mm
AWG signal line	26
Conductor cross-section	40x 0.14 mm ²
Wire diameter incl. insulation	1 mm ±0.03 mm
External cable diameter	9.90 mm ±0.4 mm
Outer sheath, material	Semi-rigid PVC
External sheath, color	gray
Conductor material	Tin-plated Cu litz wires
Cable resistance	≤ 145 Ω/km (20 °C)
Insulation resistance	≥ 20 MΩ*km (20 °C)
Smallest bending radius, fixed installation	82 mm
Smallest bending radius, movable installation	155 mm
Dynamic load capacity (bending)	Max. bending cycles: 5000 (at a radius of ≥ 15x outside diameter)
Halogen-free	no
Flame resistance	IEC 60332-1-2 (raw cable)
	VDE 0842, Part 332-1-2 (raw cable)
	IEC 60332-3-22 (raw cable)
	UL VW-1
	CSA FT-1
Resistance to oil	can withstand occasional splashes (raw cable)
Cable type	Cable for one module

Color code: Single-core wire

black	Fujitsu40 (A1) = IDC/FLK50 (11)
brown	Fujitsu40 (B1) = IDC/FLK50 (1)
red	Fujitsu40 (A2) = IDC/FLK50 (48)
orange	Fujitsu40 (B2) = IDC/FLK50 (38)
yellow	Fujitsu40 (A5) = IDC/FLK50 (46)
green	Fujitsu40 (B5) = IDC/FLK50 (22)
blue	Fujitsu40 (A6) = IDC/FLK50 (45)
violet	Fujitsu40 (B6) = IDC/FLK50 (21)

CABLE-FCN40/1X50/ 8,0M/IM/MEL - Cable



2903474

<https://www.phoenixcontact.com/us/products/2903474>

gray	Fujitsu40 (A7) = IDC/FLK50 (44)
white	Fujitsu40 (B7) = IDC/FLK50 (20)
white-black	Fujitsu40 (A8) = IDC/FLK50 (43)
white-brown	Fujitsu40 (B8) = IDC/FLK50 (19)
white-red	Fujitsu40 (A9) = IDC/FLK50 (42)
white-orange	Fujitsu40 (B9) = IDC/FLK50 (18)
white-yellow	Fujitsu40 (A10) = IDC/FLK50 (41)
white-green	Fujitsu40 (B10) = IDC/FLK50 (17)
white-blue	Fujitsu40 (A11) = IDC/FLK50 (40)
white-violet	Fujitsu40 (B11) = IDC/FLK50 (16)
white-gray	Fujitsu40 (A12) = IDC/FLK50 (39)
brown-black	Fujitsu40 (B12) = IDC/FLK50 (15)
brown-red	Fujitsu40 (A13) = IDC/FLK50 (34)
brown-orange	Fujitsu40 (B13) = IDC/FLK50 (10)
brown-yellow	Fujitsu40 (A14) = IDC/FLK50 (33)
brown-green	Fujitsu40 (B14) = IDC/FLK50 (9)
brown-blue	Fujitsu40 (A15) = IDC/FLK50 (32)
brown-violet	Fujitsu40 (B15) = IDC/FLK50 (8)
brown-gray	Fujitsu40 (A16) = IDC/FLK50 (31)
brown-white	Fujitsu40 (B16) = IDC/FLK50 (7)
green-black	Fujitsu40 (A17) = IDC/FLK50 (30)
green-brown	Fujitsu40 (B17) = IDC/FLK50 (6)
green-red	Fujitsu40 (A18) = IDC/FLK50 (29)
green-orange	Fujitsu40 (B18) = IDC/FLK50 (5)
green-blue	Fujitsu40 (A19) = IDC/FLK50 (28)
green-violet	Fujitsu40 (B19) = IDC/FLK50 (4)
green-gray	Fujitsu40 (A20) = IDC/FLK50 (27)
green-white	Fujitsu40 (B20) = IDC/FLK50 (3)

Connection data

Connection 1

Connection method	Fujitsu connector
Type	FCN 367
Number of connections	1
Number of positions	40
Insertion/withdrawal cycles	> 50
Pitch	2.54 mm

Connection 2

Connection in acc. with standard	IEC 60603-13 (in compliance)
Connection method	IDC/FLK socket strip
Number of connections	1
Number of positions	50
Insertion/withdrawal cycles	> 50

CABLE-FCN40/1X50/ 8,0M/IM/MEL - Cable



2903474

<https://www.phoenixcontact.com/us/products/2903474>

Pitch	2.54 mm
-------	---------

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

Drawings

Connection diagram

Fujitsu FCN 40	FLK 50	Fujitsu FCN 40	FLK 50
PIN A1	PIN 11	PIN B16	PIN 7
PIN B1	PIN 1	PIN A17	PIN 30
PIN A2	PIN 48	PIN B17	PIN 6
PIN B2	PIN 38	PIN A18	PIN 29
PIN A3		PIN B18	PIN 5
PIN B3		PIN A19	PIN 28
PIN A4		PIN B19	PIN 4
PIN B4		PIN A20	PIN 27
PIN A5	PIN 46	PIN B20	PIN 3
PIN B5	PIN 22		PIN 2 <input type="checkbox"/>
PIN A6	PIN 45		PIN 13 <input type="checkbox"/>
PIN B6	PIN 21		PIN 12 <input type="checkbox"/>
PIN A7	PIN 44		PIN 23 <input type="checkbox"/>
PIN B7	PIN 20		PIN 14 <input type="checkbox"/>
PIN A8	PIN 43		PIN 25 <input type="checkbox"/>
PIN B8	PIN 19		PIN 24 <input type="checkbox"/>
PIN A9	PIN 42		PIN 35 <input type="checkbox"/>
PIN B9	PIN 18		PIN 26 <input type="checkbox"/>
PIN A10	PIN 41		PIN 37 <input type="checkbox"/>
PIN B10	PIN 17		PIN 36 <input type="checkbox"/>
PIN A11	PIN 40		PIN 47 <input type="checkbox"/>
PIN B11	PIN 16		
PIN A12	PIN 39		
PIN B12	PIN 15		
PIN A13	PIN 34		
PIN B13	PIN 10		
PIN A14	PIN 33		
PIN B14	PIN 9		
PIN A15	PIN 32		
PIN B15	PIN 8		
PIN A16	PIN 31		

2903474

<https://www.phoenixcontact.com/us/products/2903474>

Diagram



Maximum permissible current per path in uncoiled state

CABLE-FCN40/1X50/ 8,0M/IM/MEL - Cable



2903474

<https://www.phoenixcontact.com/us/products/2903474>

Classifications

ECLASS

ECLASS-13.0

27242220

ETIM

ETIM 9.0

EC000237

UNSPSC

UNSPSC 21.0

26121600

CABLE-FCN40/1X50/ 8,0M/IM/MEL - Cable



2903474

<https://www.phoenixcontact.com/us/products/2903474>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	fbaa4922-4a8c-42ca-b507-fe785976e6d7

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com