

# FLKM-M12/F/5P/SCO - Termination board




2903610

<https://www.phoenixcontact.com/us/products/2903610>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

VARIOFACE module, with spring-cage terminal blocks and M12-SAC socket, 5-pos.



## Commercial data

Item number	2903610
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	C499
Product key	DK2A89
GTIN	4046356753043
Weight per piece (including packing)	53.922 g
Weight per piece (excluding packing)	52.28 g
Customs tariff number	85369010
Country of origin	DE

# FLKM-M12/F/5P/SCO - Termination board



2903610

<https://www.phoenixcontact.com/us/products/2903610>

## Technical data

### Product properties

Product type	Interface module
Product family	VARIOFACE
Number of positions	5

### Insulation characteristics: Air clearances and creepage distances

Insulation	Functional insulation
Overvoltage category	II
Pollution degree	2

### Electrical properties

Operating voltage (AC)	≤ 30 V AC
Operating voltage (DC)	≤ 30 V DC
Current (per branch)	≤ 4 A

### Air clearances and creepage distances

Rated insulation voltage	50 V
Rated surge voltage	0.5 kV (1.2/50 μs)

### Connection data

#### Connection 1

Connection in acc. with standard	IEC 61076-2-101
Connection method	Female
Type	M12
Number of connections	1
Number of positions	5

#### Connection 2

Connection method	Spring-cage connection
Stripping length	7.5 mm
Number of positions	6
Conductor cross-section rigid	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section flexible	0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
	0.25 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> (Ferrule without plastic sleeve)
	0.25 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> (Ferrule with plastic sleeve)
Conductor cross-section AWG	24 ... 14
Pitch	5.08 mm

### Signaling

Status display present	no
------------------------	----

### Dimensions

# FLKM-M12/F/5P/SCO - Termination board



2903610

<https://www.phoenixcontact.com/us/products/2903610>

## Item dimensions

Width	26 mm
Height	89.6 mm
Depth	60.5 mm

## Material specifications

Color	green (RAL 6021)
-------	------------------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection (Module)	IP00
Degree of protection (Installation location)	≥ IP54
Ambient temperature (operation)	-20 °C ... 55 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Altitude	≤ 2000 m

## Approvals

### UKCA

Certificate	UKCA-compliant
-------------	----------------

## Standards and regulations

### Air clearances and creepage distances

Standards/regulations	EN IEC 60664-1
-----------------------	----------------

## Mounting

Mounting type	DIN rail mounting
Mounting position	any

## Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

# FLKM-M12/F/5P/SCO - Termination board





2903610

<https://www.phoenixcontact.com/us/products/2903610>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2903610>

 <b>cUL Recognized</b> Approval ID: E238705				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	24 V	4 A	-	-

 <b>UL Recognized</b> Approval ID: E238705				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	24 V	4 A	-	-

# FLKM-M12/F/5P/SCO - Termination board



2903610

<https://www.phoenixcontact.com/us/products/2903610>

## Classifications

### ECLASS

ECLASS-13.0	27141152
ECLASS-15.0	27141152

### ETIM

ETIM 10.0	EC002780
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# FLKM-M12/F/5P/SCO - Termination board



2903610

<https://www.phoenixcontact.com/us/products/2903610>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	419b8be7-6371-43d2-9dfb-3f6aa5388c88

### EF3.1 Climate Change

CO2e kg	0.347 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)