

# REL-IR4/L- 24AC/4X21AU - Single relay



2903683

<https://www.phoenixcontact.com/us/products/2903683>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Plug-in industrial relay with power contacts and additional hard gold plating, 4 changeover contacts, test button, status LED, mechanical switching position indicator, coil voltage: 24 V AC

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2903683       |
| Packing unit                         | 10 pc         |
| Minimum order quantity               | 10 pc         |
| Sales key                            | C460          |
| Product key                          | DK694A        |
| GTIN                                 | 4046356758963 |
| Weight per piece (including packing) | 33 g          |
| Weight per piece (excluding packing) | 32.84 g       |
| Customs tariff number                | 85364190      |
| Country of origin                    | PL            |

# REL-IR4/L- 24AC/4X21AU - Single relay



2903683

<https://www.phoenixcontact.com/us/products/2903683>

## Technical data

### Product properties

|                         |                                |
|-------------------------|--------------------------------|
| Product type            | Single relay                   |
| Operating mode          | 100% operating factor          |
| Mechanical service life | approx. $2 \times 10^7$ cycles |

### Insulation characteristics

|                      |                  |
|----------------------|------------------|
| Insulation           | Basic insulation |
| Overvoltage category | II               |
| Pollution degree     | 2                |

### Data management status

|                              |            |
|------------------------------|------------|
| Date of last data management | 01.04.2026 |
|------------------------------|------------|

### Electrical properties

|  |  |
|--|--|
| Service life electrical                              | see diagram  |
| Maximum power dissipation for nominal condition      | 1.58 W   |
| Test voltage (Winding/contact)                       | 2.5 kV <sub>rms</sub> (50 Hz, 1 min., winding/contact)                     |
| Test voltage (Changeover contact/changeover contact) | 2 kV <sub>rms</sub> (50 Hz, 1 min., changeover contact/changeover contact) |
| Rated insulation voltage                             | 250 V AC   |
| Rated surge voltage                                  | 2.5 kV   |

### Input data

#### Coil side

|                                |  |
|--------------------------------|--|
| Nominal input voltage $U_N$    | 24 V AC                                      |
| Input voltage range            | 18.7 V AC ... 33.1 V AC (20 °C)              |
| Mains frequency                | 50/60 Hz                                     |
| Drive and function             | monostable                                   |
| Drive (polarity)               | non-polarized                                |
| Typical input current at $U_N$ | 66 mA  |
| Typical response time          | 5 ms ... 15 ms (depending on phase relation) |
| Typical release time range     | 5 ms ... 20 ms (depending on phase relation) |
| Status display                 | LED (yellow)                                 |

### Output data

#### Switching

|                        |   |
|------------------------|---|
| Contact switching type | 4 changeover contacts   |
| Type of switch contact | Single contact  |
| Contact material       | AgNi, hard gold-plated  |
| Note                   | If the specified maximum values for multi-layer contact relays are exceeded, the gold plating is destroyed. The maximum values of the power contact relay are then valid. This can result in a shorter service life than with a pure power contact. |

# REL-IR4/L- 24AC/4X21AU - Single relay



2903683

<https://www.phoenixcontact.com/us/products/2903683>

|                                       |                    |
|---------------------------------------|--------------------|
| Maximum switching voltage             | 30 V AC            |
|                                       | 36 V DC            |
| Minimum switching voltage             | 2 V (At 24 mA)     |
| Limiting continuous current           | 50 mA              |
| Maximum inrush current                | 50 mA              |
| Min. switching current                | 2 mA (24 V DC)     |
| Interrupting rating (ohmic load) max. | 1.2 W (at 24 V DC) |
| Switching power min.                  | 48 mW              |
| Motor load according to UL 508        | 1/3 HP, 240 V AC   |

Switching: when the gold layer is destroyed

|                                       |  |
|---------------------------------------|--|
| Note                                  | the following values are applicable if a gold layer is destroyed |
| Contact material                      | AgNi   |
| Maximum switching voltage             | 250 V AC/DC  |
| Minimum switching voltage             | 5 V (At 24 mA)   |
| Limiting continuous current           | 6 A  |
| Maximum inrush current                | 16 A (20 ms, N/O contacts)                                       |
| Min. switching current                | 5 mA (at 24 V)   |
| Interrupting rating (ohmic load) max. | 144 W (at 24 V DC)   |
|                                       | 124 W (at 48 V DC)   |
|                                       | 108 W (at 60 V DC)   |
|                                       | 52 W (at 110 V DC)   |
|                                       | 48 W (at 220 V DC)   |
|                                       | 1500 VA (for 250 V AC)   |
| Switching capacity                    | 2 A (at 24 V, DC13)  |
|                                       | 0.22 A (at 120 V, DC13)  |
|                                       | 0.11 A (at 250 V, DC13)  |
|                                       | 1.5 A (at 24 V, AC15)  |
|                                       | 1.5 A (at 120 V, AC15)   |
|                                       | 1 A (at 240 V, AC15)   |

## Connection data

|                   |                    |
|-------------------|--------------------|
| Connection method | Plug-in connection |
|-------------------|--------------------|

## Dimensions

|        |         |
|--------|---------|
| Width  | 21.2 mm |
| Height | 27.5 mm |
| Depth  | 35.6 mm |

## Environmental and real-life conditions

### Ambient conditions

|                                 |                  |
|---------------------------------|------------------|
| Degree of protection            | RT I             |
| Ambient temperature (operation) | -40 °C ... 55 °C |

# REL-IR4/L- 24AC/4X21AU - Single relay



2903683

<https://www.phoenixcontact.com/us/products/2903683>

|   |                  |
|---|------------------|
| Ambient temperature (storage/transport) | -40 °C ... 85 °C |
|---|------------------|

## Approvals

### Corrosive gas test

|                |                            |
|----------------|----------------------------|
| Identification | ISA-S71.04. G3 Harsh Group |
|                | EN 60068-2-60              |

## Standards and regulations

|                       |           |
|-----------------------|-----------|
| Standards/regulations | IEC 60664 |
|                       | IEC 61810 |

## Mounting

|                   |     |
|-------------------|-----|
| Mounting position | any |
|-------------------|-----|

Drawings

Diagram



- ① DC coils
- ② AC coils

Operating voltage range

2903683

<https://www.phoenixcontact.com/us/products/2903683>



- ① AC, ohmic load
- ② DC, ohmic load

Interrupting rating

# REL-IR4/L- 24AC/4X21AU - Single relay



2903683

<https://www.phoenixcontact.com/us/products/2903683>

Diagram



① 250 V AC, Ohmic load


Electrical service life

Diagram



Service life reduction factor

Diagram



Permissible humidity for operation and storage.


The maximum permissible ambient temperature as specified in the data sheet must be observed.

Area A: Ice buildup at ambient temperatures  $\leq 0^\circ\text{C}$  must be prevented

Area B: Condensation at ambient temperatures  $> 0^\circ\text{C}$  must be prevented

On 30 full days that are naturally distributed across an entire year, a humidity level of 95% is permissible at an ambient temperature  $\leq 25^\circ\text{C}$ .

Circuit diagram



# REL-IR4/L- 24AC/4X21AU - Single relay



2903683

<https://www.phoenixcontact.com/us/products/2903683>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27371601 |
| ECLASS-15.0 | 27371601 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC001437 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39122300 |
|-------------|----------|

# REL-IR4/L- 24AC/4X21AU - Single relay



2903683

<https://www.phoenixcontact.com/us/products/2903683>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)