

VIP-3/PT/D25SUB/F - Termination board



2903782

<https://www.phoenixcontact.com/us/products/2903782>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE module, with push-in connections and D-SUB 25 socket connector, for mounting on NS 35 rails

Commercial data

Item number	2903782
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	C423
Product key	DK2122
GTIN	4046356796576
Weight per piece (including packing)	135.2 g
Weight per piece (excluding packing)	154.2 g
Customs tariff number	85366990
Country of origin	US

VIP-3/PT/D25SUB/F - Termination board



2903782

<https://www.phoenixcontact.com/us/products/2903782>

Technical data

Product properties

Product type	Interface module
Product family	VARIOFACE Professional
Number of positions	25
No. of channels	2
	4
	8
	16

Insulation characteristics

Overvoltage category	II
Pollution degree	2

Electrical properties

Nominal voltage U_N	25 V AC
	60 V DC
Max. current carrying capacity per branch	2 A
Rated surge voltage	1.2 kV

Supported controller: ABB S800 I/O

Suitable I/O card	DI810
	DI811
	DI814
	DI818
	DI830
	DI831
	DI840
	DI885
	DO810
	DO814
	DO818
	DO840
	DP820
	AI810
	AI815
	AI820
	AI830
	AI835
	AI845
	AO810
	AO815
	AO820

VIP-3/PT/D25SUB/F - Termination board



2903782

<https://www.phoenixcontact.com/us/products/2903782>

AO845

Connection data

Field level

Connection method	Push-in connection
Stripping length	8 mm
Conductor cross-section rigid	0.14 mm ² ... 2.5 mm ²
Conductor cross-section flexible	0.14 mm ² ... 2.5 mm ²
Conductor cross-section AWG	26 ... 14

Controller level

Connection method	D-SUB socket strip
Number of connections	1
Number of positions	25

Signaling

Status display	no
Status display present	no

Dimensions

Item dimensions

Width	57.1 mm
Height	75.8 mm
Depth	63 mm

Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V0
Housing insulation material	Polyamide PA non-reinforced

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

Standards and regulations

Standards/regulations	IEC 60664
	DIN EN 50178

Mounting

Mounting type	DIN rail mounting
Mounting position	any

Notes

VIP-3/PT/D25SUB/F - Termination board



2903782

<https://www.phoenixcontact.com/us/products/2903782>

Notes on operation

For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.

VIP-3/PT/D25SUB/F - Termination board

2903782

<https://www.phoenixcontact.com/us/products/2903782>



Drawings

Circuit diagram



VIP-3/PT/D25SUB/F - Termination board





2903782


<https://www.phoenixcontact.com/us/products/2903782>


Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2903782>

 CSA Approval ID: 2122203				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	105 V	2 A	26 - 14	-

 cUL Recognized Approval ID: E238705				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	125 V	2 A	26 - 14	-

 UL Recognized Approval ID: E238705				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	125 V	2 A	26 - 14	-

 CSAus Approval ID: 2122203				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	105 V	2 A	28 - 14	-

VIP-3/PT/D25SUB/F - Termination board



2903782

<https://www.phoenixcontact.com/us/products/2903782>

Classifications

ECLASS

ECLASS-13.0	27141152
ECLASS-15.0	27141152

ETIM

ETIM 10.0	EC002780
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

VIP-3/PT/D25SUB/F - Termination board



2903782

<https://www.phoenixcontact.com/us/products/2903782>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	14a1f4a3-e094-48db-a590-38e5c0730dfe

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com