

# VIP-2/PT/FLK16/LED - Termination board



2904250

<https://www.phoenixcontact.com/us/products/2904250>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE module, with push-in connection and flat-ribbon cable connector, for mounting on NS 35 rails, with pin strip and short and long locking latches for socket strips, 16-pos., with LED

## Commercial data

Item number	2904250
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	C423
Product key	DK2121
GTIN	4046356813617
Weight per piece (including packing)	119.9 g
Weight per piece (excluding packing)	119.9 g
Customs tariff number	85366990
Country of origin	US

2904250

<https://www.phoenixcontact.com/us/products/2904250>

## Technical data

### Product properties

Product type	Interface module
Product family	VARIOFACE Professional
Number of positions	16

### Insulation characteristics

Overvoltage category	II
Pollution degree	2

### Electrical properties

Nominal voltage $U_N$	24 V DC
Max. current carrying capacity per branch	1 A

### Connection data

#### Field level

Connection method	Push-in connection
Stripping length	8 mm
Conductor cross-section rigid	0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section flexible	0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section AWG	26 ... 14

#### Controller level

Connection method	IDC/FLK pin strip
Number of connections	1
Number of positions	16
Pitch	2.54 mm

### Signaling

Status display	LED
Status display present	yes

### Dimensions

#### Item dimensions

Width	46.9 mm
Height	72.1 mm
Depth	56 mm

### Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V0
Housing insulation material	Polyamide PA non-reinforced

# VIP-2/PT/FLK16/LED - Termination board



2904250

<https://www.phoenixcontact.com/us/products/2904250>

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

## Standards and regulations

Standards/regulations	IEC 60664
	DIN EN 50178

## Mounting

Mounting type	DIN rail mounting
Mounting position	any

## Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

# VIP-2/PT/FLK16/LED - Termination board



2904250

<https://www.phoenixcontact.com/us/products/2904250>

## Drawings

Circuit diagram



# VIP-2/PT/FLK16/LED - Termination board



2904250

<https://www.phoenixcontact.com/us/products/2904250>

## Classifications

### UNSPSC

UNSPSC 21.0

39121432

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

[info@phoenixcon.com](mailto:info@phoenixcon.com)