


VIP-2/PT/FLK50/S7/A-S400 - Passive module



2904289

<https://www.phoenixcontact.com/us/products/2904289>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE interface module, for I/Os of the SIMATIC® S7-400, with SIMATIC®-specific marking, only in conjunction with FLKM 50-PA-S400

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 2904289 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | C423 |
| Product key | DK212S |
| GTIN | 4046356813754 |
| Weight per piece (including packing) | 219.4 g |
| Weight per piece (excluding packing) | 219.4 g |
| Customs tariff number | 85366990 |
| Country of origin | US |

VIP-2/PT/FLK50/S7/A-S400 - Passive module



2904289

<https://www.phoenixcontact.com/us/products/2904289>

Technical data

Product properties

| | |
|---------------------|------------------------|
| Product type | Interface module |
| Product family | VARIOFACE Professional |
| Number of positions | 50 |
| No. of channels | 8 |
| | 16 |
| | 32 |

Insulation characteristics

| | |
|----------------------|----|
| Overvoltage category | II |
| Pollution degree | 2 |

Electrical properties

| | |
|---|---------|
| Max. permissible operating voltage | 25 V AC |
| | 60 V DC |
| Max. current carrying capacity per branch | 1 A |
| Rated surge voltage | 0.6 kV |

Supported controller: SIEMENS S7-400

| | |
|-------------------|--------------------|
| Suitable I/O card | 6ES7421-1BL01-0AA0 |
| | 6ES7421-7BH01-0AB0 |
| | 6ES7421-7DH00-0AA0 |
| | 6ES7422-1BL00-0AA0 |
| | 6ES7422-7BL00-0AB0 |

Connection data

Field level

| | |
|----------------------------------|--|
| Connection method | Push-in connection |
| Stripping length | 8 mm |
| Conductor cross-section rigid | 0.14 mm ² ... 2.5 mm ² |
| Conductor cross-section flexible | 0.14 mm ² ... 2.5 mm ² |
| Conductor cross-section AWG | 24 ... 12 |

Controller level

| | |
|-----------------------|-------------------|
| Connection method | IDC/FLK pin strip |
| Number of connections | 1 |
| Number of positions | 50 |
| Pitch | 2.54 mm |

Signaling

| | |
|------------------------|----|
| Status display | no |
| Status display present | no |

VIP-2/PT/FLK50/S7/A-S400 - Passive module



2904289

<https://www.phoenixcontact.com/us/products/2904289>

Dimensions

Item dimensions

| | |
|--------|----------|
| Width | 107.9 mm |
| Height | 72.1 mm |
| Depth | 56 mm |

Material specifications

| | |
|--|-----------------------------|
| Color | gray (RAL 7042) |
| Flammability rating according to UL 94 | V0 |
| Housing insulation material | Polyamide PA non-reinforced |

Environmental and real-life conditions

Ambient conditions

| | |
|---|------------------|
| Ambient temperature (operation) | -20 °C ... 50 °C |
| Ambient temperature (storage/transport) | -20 °C ... 70 °C |

Standards and regulations

| | |
|-----------------------|--------------|
| Standards/regulations | IEC 60664 |
| | DIN EN 50178 |

Mounting

| | |
|-------------------|-------------------|
| Mounting type | DIN rail mounting |
| Mounting position | any |

Notes

| | |
|--------------------|--|
| Notes on operation | For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met. |
|--------------------|--|

VIP-2/PT/FLK50/S7/A-S400 - Passive module




2904289

<https://www.phoenixcontact.com/us/products/2904289>

Drawings

Circuit diagram



VIP-2/PT/FLK50/S7/A-S400 - Passive module



2904289

<https://www.phoenixcontact.com/us/products/2904289>

Classifications

ECLASS

ECLASS-13.0

27141152

ETIM

ETIM 9.0

EC002780

UNSPSC

UNSPSC 21.0

39121400

VIP-2/PT/FLK50/S7/A-S400 - Passive module



2904289

<https://www.phoenixcontact.com/us/products/2904289>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com