

# BRIDGE-PT 4 - Bridge



2904492

<https://www.phoenixcontact.com/us/products/2904492>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

3-phase loop bridge for 4 CONTACTRON modules, with Push-in connection and 22.5 mm housing width, connecting cable: 3 m



## Your advantages

- Bridging of 2 to 10 devices with maximum module spacing of 22.5 mm
- Considerable reduction in wiring
- Up to 575 V AC/3 x 25 A

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2904492       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | C470          |
| Product key                          | DK74Z1        |
| GTIN                                 | 4046356845274 |
| Weight per piece (including packing) | 337.4 g       |
| Weight per piece (excluding packing) | 317.1 g       |
| Customs tariff number                | 85444290      |
| Country of origin                    | DE            |

# BRIDGE-PT 4 - Bridge



2904492

<https://www.phoenixcontact.com/us/products/2904492>

## Technical data

### Product properties

|                              |             |
|------------------------------|-------------|
| Product type                 | Loop bridge |
| Product family               | CONTACTRON  |
| Number of bridgeable modules | 4           |

### Electrical properties

|                         |                      |
|-------------------------|----------------------|
| Operating voltage range | 42 V AC ... 575 V AC |
| Operating current       | ≤ 25 A               |

### Material specifications

|       |                 |
|-------|-----------------|
| Color | gray (RAL 7042) |
|-------|-----------------|

### Cable/line

|                         |                     |
|-------------------------|---------------------|
| Connecting cable length | 3 m                 |
| Cable cross section     | 2.5 mm <sup>2</sup> |

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2904492>



**UL Listed**

Approval ID: FILE E 172140



**cUL Listed**

Approval ID: FILE E 172140



**cUL Listed**

Approval ID: E228652



**UL Listed**

Approval ID: E228652

# BRIDGE-PT 4 - Bridge

2904492

<https://www.phoenixcontact.com/us/products/2904492>



## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27371392 |
| ECLASS-15.0 | 27371392 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002886 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121100 |
|-------------|----------|

# BRIDGE-PT 4 - Bridge



2904492

<https://www.phoenixcontact.com/us/products/2904492>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)