

FLK 14/16/EZ-DR/HF/ 400/S7 - Cable



2904525

<https://www.phoenixcontact.com/us/products/2904525>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Assembled, halogen-free round cable; controller: SIMATIC® TOP connect; connection 1: IDC/FLK socket strip (1x 16-position); connection 2: IDC/FLK socket strip (1x 14-position); cable length: 4 m

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 2904525 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | NULL |
| Product key | DK221S |
| GTIN | 4046356859493 |
| Weight per piece (including packing) | 214.7 g |
| Weight per piece (excluding packing) | 202.4 g |
| Customs tariff number | 85444290 |
| Country of origin | DE |

Technical data

Product properties

| | |
|--------------|--------------|
| Product type | System cable |
|--------------|--------------|

Environmental and real-life conditions

Ambient conditions

| | |
|---|--|
| Degree of protection | IP00 |
| Degree of protection (Installation location) | ≥ IP54 (Installation location) |
| Ambient temperature (operation) (fixed installation) | -40 °C ... 70 °C (fixed installation) |
| Ambient temperature (operation) (flexible installation) | -10 °C ... 70 °C (flexible installation) |
| Ambient temperature (storage/transport) | -40 °C ... 80 °C |
| Altitude | ≤ 2000 m |

Electrical properties

| | |
|--------------------------|----------------------------------|
| Operating voltage (AC) | ≤ 30 V AC |
| Operating voltage (DC) | ≤ 60 V DC |
| Nominal operating mode | 100% operating factor |
| Current (Per path, 50°C) | ≤ 1 A (Uncoiled, see derating) |
| Current (Per path, 70°C) | ≤ 0.6 A (Uncoiled, see derating) |

Cable/line

| | |
|---|---|
| Cable length | 4 m |
| UL AWM Style | 21946 |
| Number of positions | 14 |
| Shielded | no |
| Conductor type | Assembled, halogen-free round cable |
| Conductor structure signal line | 7x 0.16 mm |
| AWG signal line | 26 |
| Conductor cross-section | 14x 0.14 mm ² |
| Wire diameter incl. insulation | 1 mm ±0.03 mm |
| External cable diameter | 5.80 mm ±0.4 mm |
| Outer sheath, material | halogen-free (type 2) |
| External sheath, color | gray |
| Conductor material | Tin-plated Cu litz wires |
| Cable resistance | ≤ 145 Ω/km (20 °C) |
| Insulation resistance | ≥ 20 MΩ*km (20 °C) |
| Smallest bending radius, fixed installation | 50 mm |
| Smallest bending radius, movable installation | 93 mm |
| Dynamic load capacity (bending) | Max. bending cycles: 5000 (at a radius of ≥ 15x outside diameter) |
| Halogen-free | yes |
| | IEC 60332-1-2 (raw cable) |

FLK 14/16/EZ-DR/HF/ 400/S7 - Cable



2904525

<https://www.phoenixcontact.com/us/products/2904525>

| | |
|-------------------|--|
| Flame resistance | VDE 0842, Part 332-1-2 (raw cable) IEC 60332-3-22 (raw cable) |
| Resistance to oil | can withstand occasional splashes (raw cable) |

Color code: Single-core wire

| | |
|--------------|---------------------------------|
| white | IDC/FLK16 (1) = IDC/FLK14 (10) |
| violet | IDC/FLK16 (2) = IDC/FLK14 (8) |
| white-brown | IDC/FLK16 (3) = IDC/FLK14 (12) |
| blue | IDC/FLK16 (4) = IDC/FLK14 (7) |
| white-orange | IDC/FLK16 (5) = IDC/FLK14 (14) |
| green | IDC/FLK16 (6) = IDC/FLK14 (6) |
| yellow | IDC/FLK16 (8) = IDC/FLK14 (5) |
| gray | IDC/FLK16 (9) = IDC/FLK14 (9) |
| orange | IDC/FLK16 (10) = IDC/FLK14 (4) |
| white-black | IDC/FLK16 (11) = IDC/FLK14 (11) |
| red | IDC/FLK16 (12) = IDC/FLK14 (3) |
| white-red | IDC/FLK16 (13) = IDC/FLK14 (13) |
| brown | IDC/FLK16 (14) = IDC/FLK14 (2) |
| black | IDC/FLK16 (16) = IDC/FLK14 (1) |

Connection data

Connection 1

| | |
|----------------------------------|------------------------------|
| Connection in acc. with standard | IEC 60603-13 (in compliance) |
| Connection method | IDC/FLK socket strip |
| Number of connections | 1 |
| Number of positions | 16 |
| Insertion/withdrawal cycles | > 50 |
| Pitch | 2.54 mm |

Connection 2

| | |
|----------------------------------|------------------------------|
| Connection in acc. with standard | IEC 60603-13 (in compliance) |
| Connection method | IDC/FLK socket strip |
| Number of connections | 1 |
| Number of positions | 14 |
| Insertion/withdrawal cycles | > 50 |
| Pitch | 2.54 mm |

Notes

| | |
|--------------------|--|
| Notes on operation | For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met. |
|--------------------|--|

2904525

<https://www.phoenixcontact.com/us/products/2904525>

Drawings

Connection diagram

| 14-pos. Socket strip PIN | 16-pos. Socket strip PIN | Wire color |
|--------------------------------|--------------------------------|--------------|
| 1 | 16 | Black |
| 2 | 14 | Brown |
| 3 | 12 | Red |
| 4 | 10 | Orange |
| 5 | 8 | Yellow |
| 6 | 6 | Green |
| 7 | 4 | Blue |
| 8 | 2 | Violet |
| 9 | 9 | Gray |
| 10 | 1 | White |
| 11 | 11 | White-black |
| 12 | 3 | White-brown |
| 13 | 13 | White-red |
| 14 | 5 | White-orange |
| | 7 | - |
| | 15 | - |

Pin assignment and color code

2904525

<https://www.phoenixcontact.com/us/products/2904525>

Diagram




Maximum permissible current per path in uncoiled state

Circuit diagram



Pin assignment Siemens S7 front connector modules 6ES7 921-3...

Circuit diagram



Pin assignment of digital Siemens S7 front plug-in modules 6ES7 921-5AB20-0AA0 or 6ES7 921-5AH20-0AA0

FLK 14/16/EZ-DR/HF/ 400/S7 - Cable



2904525

<https://www.phoenixcontact.com/us/products/2904525>

Classifications

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 26121600 |
|-------------|----------|

FLK 14/16/EZ-DR/HF/ 400/S7 - Cable



2904525

<https://www.phoenixcontact.com/us/products/2904525>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com