

TC-EC56F-DO16-ESD-A-TRC - Module carrier



2904679

<https://www.phoenixcontact.com/us/products/2904679>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Termination carrier for connecting 16 PSR-FSP modules to digital output cards of the Invensys Triconex controller via ELCO connector 8016, 56-pos. Solution for Emergency Shut Down (ESD) applications. Suitable for Invensys Triconex 3625 card.

Your advantages

- Mechanically decoupled PCB
- Robust aluminum profile with integrated DIN rail
- Side parts with integrated end clamps
- System connection, ELCO connector 8016 socket strip, 56-pos.
- Simple or redundant supply, decoupled from diode, protected against polarity reversal
- Error message in the event of power supply failure or fuse fault
- Relay output (N/O contact, floating) and flashing LED for error message
- Undervoltage monitoring at input at < 18 V DC
- Suitable for safe state off applications
- Cable sets for signal connection are not supplied as standard and must be ordered separately

Commercial data

Item number	2904679
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	DK2746
GTIN	4046356872492
Weight per piece (including packing)	1,460 g
Weight per piece (excluding packing)	1,460 g
Country of origin	DE

Technical data

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
Utilization restriction	
EMC note	EMC: class A product, see manufacturer's declaration in the download area

Product properties

Product type	Module carrier
Insulation characteristics: Air clearances and creepage distances	
Insulation	Basic insulation
Overvoltage category	II
Pollution degree	2

Electrical properties

Max. permissible current	1200 mA
Nominal voltage U_N	24 V DC (21.1 V ... 26.4 V)
Air clearances and creepage distances	
Rated insulation voltage	50 V
Rated surge voltage	0.5 kV
Supported controller: INVENYSY Triconex	
Suitable I/O card	3625

Supply

Designation	Device supply
Fuse	2.5 A on PCB, slow-blow (replaceable)
Input voltage range	21.1 V ... 26.4 V
Redundant supply	yes, decoupled from diodes
Polarization and surge protection	Yes
Output name	Switching output
Contact switching type	1 N/C contact (alarm = open)

Connection data

Power supply

Connection method	Screw connection
Stripping length	7 mm
Number of connections	1
Number of positions	6

TC-EC56F-DO16-ESD-A-TRC - Module carrier



2904679

<https://www.phoenixcontact.com/us/products/2904679>

Conductor cross-section rigid	0.14 mm ² ... 2.5 mm ²
Conductor cross-section flexible	0.14 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 12

Controller level

Connection method	ELCO connector
Coding	3-3
Number of connections	1
Number of positions	56

Signaling

Status display	2 x red LED (error)
	2x green LEDs (PWR1 and PWR2)

Dimensions

Width	304 mm
Height	170 mm
Depth	159.5 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP00
Ambient temperature (operation)	-20 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Permissible humidity (operation)	5 % ... 95 % (non-condensing)
Shock	15g, according to IEC 60068-2-27
Vibration (operation)	2g, according to IEC 60068-2-6

Approvals

UL, USA/Canada

Identification	UL 61010 Listed
	Class I, Div. 2, Groups A, B, C, D T4
	Class I, Zone 2, Group IIC

Standards and regulations

Air clearances and creepage distances

Standards/regulations	EN IEC 60664-1
-----------------------	----------------

Mounting


Mounting type	DIN rail mounting
Assembly note	No end clamp
Mounting position	vertical, horizontal


2904679


<https://www.phoenixcontact.com/us/products/2904679>


Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2904679>

 UL Listed Approval ID: E330267				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	50 V	1 A	-	-

 cUL Listed Approval ID: E330267				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	50 V	1 A	-	-

 cUL Listed Approval ID: E199827				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	50 V	1 A	-	-

 UL Listed Approval ID: E199827				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	50 V	1 A	-	-

TC-EC56F-DO16-ESD-A-TRC - Module carrier



2904679

<https://www.phoenixcontact.com/us/products/2904679>

Classifications

ECLASS

ECLASS-13.0	27141152
ECLASS-15.0	27141152

ETIM

ETIM 10.0	EC002780
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

2904679

<https://www.phoenixcontact.com/us/products/2904679>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	e4671f36-1a45-46a0-ba0a-4ed86bed8c96

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
 586 Fulling Mill Road
 Middletown, PA 17057, United States
 (+717) 944-1300
info@phoenixcon.com