

# PLC-OPT- 48DC/110DC/3RW - Solid-state relay module



2900393

<https://www.phoenixcontact.com/us/products/2900393>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



PLC-INTERFACE for railway applications, consisting of basic terminal block with push-in connection and integrated miniature solid-state relay, range:  $0.7 \times U_N$  to  $1.25 \times U_N$ , temperature range:  $-25^\circ\text{C}$  to  $+70^\circ\text{C}$ , 1 N/O contact, input: 48 V DC, output: 12 - 140 V DC/3 A

## Your advantages

- Shock resistance in accordance with DIN 50155 (requirements in accordance with EN 61373)
- Temperature range:  $-25^\circ\text{C}$  ...  $+70^\circ\text{C}$
- Input voltage range of  $0.7 - 1.25 \times U_N$

## Commercial data

Item number	2900393
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	C461
Product key	DK62AL
GTIN	4046356508988
Weight per piece (including packing)	35.82 g
Weight per piece (excluding packing)	31.89 g
Customs tariff number	85364190
Country of origin	DE

# PLC-OPT- 48DC/110DC/3RW - Solid-state relay module



2900393

<https://www.phoenixcontact.com/us/products/2900393>

## Technical data

### Product properties

Product type	Solid-state relay module
Product family	PLC-INTERFACE
Application	Railway applications
Operating mode	100% operating factor

Insulation characteristics: Air clearances and creepage distances, input/output

Insulation	Basic insulation
Overvoltage category	III
Pollution degree	2

Data management status

Date of last data management	01.04.2026
------------------------------	------------

### Electrical properties

Maximum power dissipation for nominal condition	0.26 W
Test voltage (Input/output)	2.5 kV AC (Input/output)

Air clearances and creepage distances, input/output

Rated insulation voltage	160 V
Rated surge voltage	4 kV

### Input data

Nominal input voltage $U_N$	48 V DC
Input voltage range in reference to $U_N$	0.7 ... 1.25 ( $t < 1$ s = 0.6 ... 1.4 x $U_N$ )
Input voltage range	33.6 V DC ... 60 V DC
Switching threshold "0" signal in reference to $U_N$	< 0.3
Switching threshold "1" signal in reference to $U_N$	> 0.6
Typical input current at $U_N$	5.5 mA
Typical response time	400 $\mu$ s
Typical turn-off time	800 $\mu$ s
Operating voltage display	Yellow LED
Protective circuit	Reverse polarity protection; Series polarity protection diode
	Surge protection
Surge voltage protection	> 150 V
Transmission frequency	50 Hz

### Output data

Contact switching type	1 N/O contact
Design of digital output	electronic
Output nominal voltage	110 V DC
Output voltage range	12 V DC ... 140 V DC ( $t < 1$ s = 1.40 x $U_N$ )
Limiting continuous current	3 A (see derating curve)

# PLC-OPT- 48DC/110DC/3RW - Solid-state relay module



2900393

<https://www.phoenixcontact.com/us/products/2900393>

Surge voltage protection	> 150 V
Voltage drop at max. limiting continuous current	< 150 mV
Output circuit	2-conductor, floating
Protective circuit	Reverse polarity protection; Parallel polarity protection diode Surge protection

## Connection data

Connection method	Push-in connection
Stripping length	10 mm
Conductor cross-section rigid	0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section flexible	0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> 0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> (Single ferrule) 2x 0.5 mm <sup>2</sup> ... 1 mm <sup>2</sup> (TWIN ferrule)
Conductor cross-section AWG	26 ... 14

## Dimensions

### Item dimensions

Width	6.2 mm
Height	80 mm
Depth	94 mm

## Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94 (Housing)	V0 (Housing)

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C

## Approvals

### CE

Certificate	CE-compliant
-------------	--------------

### UKCA

Certificate	UKCA-compliant
-------------	----------------

### Corrosive gas test

Identification	ISA-S71.04. G3 Harsh Group EN 60068-2-60
----------------	---

### Shipbuilding approval

Certificate	TAE0000196
-------------	------------

# PLC-OPT- 48DC/110DC/3RW - Solid-state relay module



2900393

<https://www.phoenixcontact.com/us/products/2900393>

## Shipbuilding data

Temperature	D
Humidity	A
Vibration	B
EMC	B
Enclosure	Required protection according to the Rules shall be provided upon installation on board

## EMC data

Electromagnetic compatibility	Conformance with EMC directive
Low Voltage Directive	Conformance with Low Voltage Directive

## Standards and regulations

### Air clearances and creepage distances, input/output

Standards/regulations	IEC 60947-5-1
-----------------------	---------------

### Railway standard

Standards/regulations	DIN EN 50155 (in relevant parts)
Standards/regulations	DNVGL-CG-0339

## Mounting

Mounting type	DIN rail mounting
Assembly note	in rows with zero spacing
Mounting position	any


# PLC-OPT- 48DC/110DC/3RW - Solid-state relay module

2900393


<https://www.phoenixcontact.com/us/products/2900393>

## Drawings

Diagram



Circuit diagram



# PLC-OPT- 48DC/110DC/3RW - Solid-state relay module



2900393

<https://www.phoenixcontact.com/us/products/2900393>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2900393>



**EAC**

Approval ID: RU\*C-DE.\*08.B.00010



**cULus Listed**

Approval ID: E140324



**cUL Recognized**

Approval ID: E238705



**UL Recognized**

Approval ID: E238705



**UL Listed**

Approval ID: FILE E 172140



**cUL Listed**

Approval ID: FILE E 172140



**cULus Listed**

Approval ID: E140324



**cULus Listed**

Approval ID: E140324

# PLC-OPT- 48DC/110DC/3RW - Solid-state relay module



2900393

<https://www.phoenixcontact.com/us/products/2900393>

## Classifications

### ECLASS

ECLASS-13.0	27371604
ECLASS-15.0	27371604

### ETIM

ETIM 10.0	EC001504
-----------	----------

### UNSPSC

UNSPSC 21.0	39122300
-------------	----------

# PLC-OPT- 48DC/110DC/3RW - Solid-state relay module



2900393

<https://www.phoenixcontact.com/us/products/2900393>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	87bdf099-2937-4f4c-b366-51276acf3c52

### EF3.1 Climate Change

CO2e kg	2.34 kg CO2e
---------	--------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)