# PLC-OPT- 72DC/110DC/3RW - Solid-state relay module

2900394

https://www.phoenixcontact.com/us/products/2900394

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



PLC-INTERFACE for railway applications, consisting of basic terminal block with push-in connection and integrated miniature solid-state relay, range: 0.7 x $U_N$ to 1.25 x $U_N$, temperature range: -25°C to +70°C, 1 N/O contact, input: 72 V DC, output: 12 - 140 V DC/3 A

## Your advantages

- Shock resistance in accordance with DIN 50155 (requirements in accordance with EN 61373)
- Input voltage range of 0.7 - 1.25 x UN
- Temperature range: -25 °C ... +70 °C

## Commercial data

| | |
|---|---|
| Item number | 2900394 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Note | Made to order (non-returnable) |
| Sales key | C461 |
| Product key | DK62AL |
| GTIN | 4046356581547 |
| Weight per piece (including packing) | 34.98 g |
| Weight per piece (excluding packing) | 31.89 g |
| Customs tariff number | 85364900 |
| Country of origin | DE |

## Technical data

### Product properties

| | |
|---|---|
| Product type | Solid-state relay module |
| Product family | PLC-INTERFACE |
| Application | Railway applications |
| Operating mode | 100% operating factor |

Insulation characteristics: Air clearances and creepage distances, input/output

| | |
|---|---|
| Insulation | Basic insulation |
| Overvoltage category | III |
| Pollution degree | 2 |

Data management status

| | |
|---|---|
| Date of last data management | 01.04.2026 |

### Electrical properties

| | |
|---|---|
| Maximum power dissipation for nominal condition | 0.4 W |
| Test voltage (Input/output) | 2.5 kV AC (Input/output) |

Air clearances and creepage distances, input/output

| | |
|---|---|
| Rated insulation voltage | 160 V |
| Rated surge voltage | 4 kV |

### Input data

| | |
|---|---|
| Nominal input voltage $U_N$ | 72 V DC |
| Input voltage range in reference to $U_N$ | 0.7 ... 1.25 (t < 1 s = 0.6 ... 1.4 x $U_N$) |
| Input voltage range | 50.4 V DC ... 90 V DC |
| Switching threshold "0" signal in reference to $U_N$ | < 0.3 |
| Switching threshold "1" signal in reference to $U_N$ | > 0.6 |
| Typical input current at $U_N$ | 5.5 mA |
| Typical response time | 400 µs |
| Typical turn-off time | 800 µs |
| Operating voltage display | Yellow LED |
| Protective circuit | Reverse polarity protection; Series polarity protection diode |
| | Surge protection |
| Surge voltage protection | > 150 V |
| Transmission frequency | 50 Hz |

### Output data

| | |
|---|---|
| Contact switching type | 1 N/O contact |
| Design of digital output | electronic |
| Output nominal voltage | 110 V DC |
| Output voltage range | 12 V DC ... 140 V DC (t < 1 s = 1.40 x $U_N$) |
| Limiting continuous current | 3 A (see derating curve) |

| | |
|---|---|
| Surge voltage protection | > 150 V |
| Voltage drop at max. limiting continuous current | < 150 mV |
| Output circuit | 2-conductor, floating |
| Protective circuit | Reverse polarity protection; Parallel polarity protection diode |
| | Surge protection |

## Connection data

| | |
|---|---|
| Connection method | Push-in connection |
| Stripping length | 10 mm |
| Conductor cross-section rigid | 0.14 mm² ... 2.5 mm² |
| Conductor cross-section flexible | 0.14 mm² ... 2.5 mm² |
| | 0.2 mm² ... 2.5 mm² (Single ferrule) |
| | 2x 0.5 mm² ... 1 mm² (TWIN ferrule) |
| Conductor cross-section AWG | 26 ... 14 |

## Dimensions

Item dimensions

| | |
|---|---|
| Width | 6.2 mm |
| Height | 80 mm |
| Depth | 94 mm |

## Material specifications

| | |
|---|---|
| Color | gray (RAL 7042) |
| Flammability rating according to UL 94 (Housing) | V0 (Housing) |

## Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Degree of protection | IP20 |
| Ambient temperature (operation) | -25 °C ... 70 °C |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C |

## Approvals

CE

| | |
|---|---|
| Certificate | CE-compliant |

UKCA

| | |
|---|---|
| Certificate | UKCA-compliant |

Corrosive gas test

| | |
|---|---|
| Identification | ISA-S71.04. G3 Harsh Group |
| | EN 60068-2-60 |

Shipbuilding approval

| | |
|---|---|
| Certificate | TAE0000196 |

Shipbuilding data

| | |
|---|---|
| Temperature | D |
| Humidity | A |
| Vibration | B |
| EMC | B |
| Enclosure | Required protection according to the Rules shall be provided upon installation on board |

## EMC data

| | |
|---|---|
| Electromagnetic compatibility | Conformance with EMC directive |
| Low Voltage Directive | Conformance with Low Voltage Directive |

## Standards and regulations

Air clearances and creepage distances, input/output

| | |
|---|---|
| Standards/regulations | IEC 60947-5-1 |

Railway standard


| | |
|---|---|
| Standards/regulations | DIN EN 50155 (in relevant parts) |
| Standards/regulations | DNVGL-CG-0339 |

## Mounting


| | |
|---|---|
| Mounting type | DIN rail mounting |
| Assembly note | in rows with zero spacing |
| Mounting position | any |

## Drawings

Diagram




Circuit diagram



## Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/2900394

**cULus Listed**
Approval ID: E140324

**cUL Recognized**
Approval ID: E238705

**UL Recognized**
Approval ID: E238705

**UL Listed**
Approval ID: FILE E 172140

**cUL Listed**
Approval ID: FILE E 172140

**cULus Listed**
Approval ID: E140324

**cULus Listed**
Approval ID: E140324

## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 27371604 |
| ECLASS-15.0 | 27371604 |

### ETIM

| | |
|---|---|
| ETIM 10.0 | EC001504 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 39122300 |

## Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 7(a), 7(c)-I |

China RoHS

| | |
|---|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | 8142587a-6be0-4fd6-abdd-9b7718b90a7b |

EF3.1 Climate Change

| | |
|---|---|
| CO2e kg | 2.462 kg CO2e |


Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com



Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com